

21546	Sulfinert Fitting	1/8" to 1/4" Tube End Reducer Sulfinert Coated
21547	Sulfinert Fitting	1/4" to 1/8" Tube End Reducer Sulfinert Coated
21548	Sulfinert Fitting	1/8" Port Connector Sulfinert Coated
21549	Sulfinert Fitting	1/4" Port Connector Sulfinert Coated
21550	Sulfinert Fitting	1/8" to 1/4" Port Connector Sulfinert Coated
21551	Sulfinert Fitting	1/8" to 1/8" NPT Male Connector Sulfinert Coated
21552	Sulfinert Fitting	1/4" to 1/4" NPT Male Connector Sulfinert Coated
21553	Sulfinert Fitting	1/16" to 1/8" NPT Male Connector Sulfinert Coated
21554	Sulfinert Fitting	1/8" to 1/4" NPT Male Connector Sulfinert Coated
21555	Sulfinert Fitting	1/4" to 1/8" NPT Male Connector Sulfinert Coated
21556	Sulfinert Fitting	1/8" to 1/8" NPT Female Connector Sulfinert Coated
21557	Sulfinert Fitting	1/4" to 1/4" NPT Female Connector Sulfinert Coated
21558	Sulfinert Fitting	1/4" to 1/8" NPT Female Connector Sulfinert Coated
21559	Sulfinert Fitting	1/8" to 1/4" NPT Female Connector Sulfinert Coated
21572	Regulator, Spectra/Linde	Mini SS High Purity, 0-30psi 1 Stage Regulator for 6A Cylinder CGA 180
21572-R100	Regulator, Spectra/Linde	Mini SS High Purity, 0-100psi 1 Stage Regulator for 6A Cylinder CGA 180
21581	Nickel Reaction Tube	For Hall 1000 ELCD Pack of 2
21582	Nickel Reaction Tube	For OI 4420 ELCD Pack of 2
21583	Sealing Ring	1/16"Vespel/Graphite Pack of 2 For Hall 1000 ELCD
21584	Nickel Reaction Tube	Nut, Pack of 2
21586	Valve, Sulfinert	Plug Valve, 2-Way, Straight 1/8" Fittings
21587	Valve, Sulfinert	Plug Valve, 2-Way, Straight 1/4" Fittings
21588	Valve, Sulfinert	Ball Valve, 2-Way, Straight 1/8" Fittings
21589	Valve, Sulfinert	Ball Valve, 2-Way, Straight 1/4" Fittings
21590	Tubing, Copper	1/8" OD x 0.065" ID 50ft Roll (0.030" wall)
21592	Tubing, Copper	1/4" OD x 0.190" ID 50ft (0.030" wall)
21593580	Switchover System, SS	Automatic Switchover System With Line Regulator For Use with N2, He, Ar (CGA
21595	Tubing, SilcoSmooth	Tubing, SilcoSmooth 3/16" OD x 3.2mm ID
21596	Tubing, SilcoSmooth	1/8" OD x 2mm ID
21601	Tool	File, Needle, MXT 2 pack
21610	Trap, Chemical	for HP 5890 GCs
21620	FID Jet	Siltek, Capillary Dedicated Jet for Agilent 6890/6850/7890 GCs, ea (0.011" ID Tip)
21621	FID Jet	Capillary Dedicated Jet for Agilent 6890/6850/7890 GCs, ea (0.011" ID Tip)
21626	Base Fitting	For Restek 5890 Injection Port
21630	Gold-Plated Base Screws	For Restek 5890 Injection Port Pack of 10
21631	Siltek Base Screws	For Restek 5890 Injection Port Pack of 10
21632	Siltek Base Screws	For Restek 5890 Injection Port Pack of 50
21642	Tool	Carbofrit, Insert/Puller
21646	Generator, Zero Air	Maintenance Kit for Catalog # 20684
21647	Generator, Zero Air	Maintenance Kit for Catalog # 20680 to 20683, Also for Parker TOC-1250
21648	Generator, Nitrogen	Maintenance Kit for Catalog # 21652 & 20677
21649	Generator, Nitrogen	Maintenance Kit for Catalog #21654 & 21653
21650	Inlet Adapter Kit	Packed Column, 1/4"-3/16"
21651	Inlet Adapter Kit	Packed Column, 1/4"-1/8"
21652	Generator, Nitrogen	General Purpose w/Oxygen Analyzer, N2-14A Domestic Orders Drop Ship from M
21653	Generator, Nitrogen	Ultra High Purity, HPN2-1100 Domestic Orders Drop Ship from Manufacturer, Shi
21653-551	Generator, Nitrogen	Ultra High Purity w/European Cord Set Domestic Orders Drop Shipped from Manu
21653-552	Generator, Nitrogen	Ultra High Purity, HPN2-1100 12-month warranty from date of purchase IEC Contr
21654	Generator, Nitrogen	High Purity, HPN2-2000 Does not Ship UPS or Fed Ex (Ships on Skid) Domestic
21655	Generator, Nitrogen	Maintenance Kit for Catalog # 20697
21657	Pressure Gauge	for Heated Purifier
21660	Purifier Tube	1/4" Fittings, Straight (Similar to Supelco #2-2398) HAZ FEES APPLY
21661	Purifier Tube	1/8" Fittings, Straight (Similar to Supelco #2-2396) HAZ FEES APPLY
21666	Line Regulator, Brass	Single Stage, Ultra High Purity Outlet Pressure: 0-50psig
21667	Regulator, Brass	Dual Stage, Ultra High Purity Inert Gas, CGA 580
21668	Regulator, Brass	Dual Stage, Ultra High Purity Hydrogen, CGA 350
21669	Regulator, Brass	Dual Stage, Ultra High Purity Air, CGA 590
21670	Deionizer Bag	for H2-90 Hydrogen Generator Parker/Balson Pack of 2
21671	Desiccant Cartridge	for H2-90 Hydrogen Generator Parker/Balson
21682	FID Jet	Capillary Dedicated Jet for Agilent 6890/6850/7890 GCs, 3pk (0.011" ID Tip)
21683	FID Jet	Siltek, Capillary Dedicated Jet for Agilent 6890/6850/7890 GCs, 3pk (0.011" ID Tip)
21685	O-Rings, Viton	For Septum Purged Packed Port 10pk
21686	FID Jet	Siltek, Packed Column Jet for Agilent 5890/6890/6850 GCs, ea (0.030" ID Tip)
21687	FID Jet	Siltek, Packed Column Jet for Agilent 5890/6890/6850 GCs 3pk (0.030" ID Tip)
21688	FID Jet	Packed Column Jet for Agilent 5890/6890/6850 GCs, ea (0.030" ID Tip)
21689	FID Jet	Packed Column Jet for Agilent 5890/6890/6850 GCs, 3pk (0.030" ID Tip)

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034

 HROMalytic +61(0)3 9762 2034 ECHnology Pty Ltd		Australian Distributors Importers & Manufacturers www.chromtech.net.au
Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA		

[Ctrl F]
> Cat.#s

> **Current System AUD Prices**

