

21690	Inlet Support Spring
21691	Weldment, Packed Column
21694	FID Jet
21695	FID Jet
21696	FID Jet
21697	FID Jet
21699	FID Collector Assembly
21700	Split/Splitless Metal Liner
21700-205	Split/Splitless Metal Liner
21700-209.5	Split/Splitless Liner
21700-213.5	Split/Splitless Metal Liner
21701	Split/Splitless Metal Liner
21701-205	Split/Splitless Metal Liner
21701-209.25	Split/Splitless Metal
21702	Single Gooseneck Metal Liner
21702-200.5	Single Gooseneck Metal Liner
21702-209.5	Single Gooseneck Metal Liner
21703	Single Gooseneck Metal Liner
21703-209.25	Single Gooseneck Metal Liner
21704	Baffled Glass Liner
21704-210.10	Baffled Glass Liner
21704-214.10	Baffled Glass Liner
21704-216.10	Baffled Glass Liner
21705	PTV Liner
21706	PTV Liner
21706-205	PTV Liner
21706-213.5	PTV Liner
21706-214.5	PTV Liner
21707	PTV Liner
21708	Split Liner w/Frit
21708-209.1	Split Liner w/Frit
21708-214.1	Split Liner w/Frit
21709	Split Liner w/Frit
21709-200.5	Split Liner w/Frit
21709-202.5	Split Liner w/Frit
21709-209.5	Split Liner w/Frit
21709-213.5	Split Liner w/Frit
21709-214.5	Split Liner w/Frit
21709-216.5	Split Liner w/Frit
21710	Inlet Seals, Washers
21711	Splitless Liner
21711-200.1	Splitless Liner
21711-209.1	Splitless Liner
21711-211.1	Splitless Liner
21711-213.1	Splitless Liner
21711-214.1	Splitless Liner
21711-216.1	Splitless Liner
21712	Splitless Liner
21712-200.5	Splitless Liner
21712-202.5	Splitless Liner
21712-209.5	Splitless Liner
21712-210.5	Splitless Liner
21712-211.5	Splitless Liner
21712-213.5	Splitless Liner
21712-214.5	Splitless Liner
21712-216.5	Splitless Liner
21713	Uniliner Liner
21713-205	Uniliner Liner
21713-211.1	Uniliner Liner
21713-213.1	Uniliner Liner
21714	Open Liner
21714-214.1	Open Liner
21715	Open Liner
21715-210.5	Open Liner
21715-214.5	Open Liner
21716	Open Liner

Page 74	Siltek Treated For Varian GC 3pk
> Current System AUD Prices	Septum Purged, Siltek For HP 5890 C
	Packed Column Jet for Agilent 5890/6890/6850 GCs, ea (0.018" ID Tip)
	Packed Column Jet for Agilent 5890/6890/6850 GCs, 3pk(0.018" ID Tip)
	Siltek, Packed Column Jet for Agilent 5890/6890/6850 GCs, ea (0.018" ID Tip)
	Siltek, Packed Column Jet for Agilent 5890/6890/6850 GCs 3pk (0.018" ID Tip)
	for Agilent 6890/6850/7890 GCs
	5.2mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., w/Deact. Wool, 5pk
	5.2mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., No Wool, 5pk
	5.2mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., w/CarboFrit, 5pk
	5.2mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., w/Deact. Wool, 5pk
	5.2mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., w/Deact. Wool, 25pk
	5.2mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., No Wool, 25pk
	Liner 5.2mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., w/CarboFrit, 25pk
	5.2mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., 5pk
	5.2mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., w/Deact. Wool, 5pk
	5.2mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., w/CarboFrit, 5pk
	5.2mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., 25pk
	5.2mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., w/CarboFrit, 25pk
	1.5mm x 3.0 x 71 for Agilent GCs IP Deact., 10pk
	1.5mm x 3.0 x 71 for Agilent GCs Base Deact., 10pk
	1.5mm x 3.0 x 71 for Agilent GCs Siltek Deact., 10pk
	1.5mm x 3.0 x 71 for Agilent GCs Siltek Deact., w/CarboFrit, 10pk
	1.6mm x 4.0 x 95 for Shimadzu GCs IP Deact., w/Deact. Wool, ea
	1.6mm x 4.0 x 95 for Shimadzu GCs IP Deact., w/Deact. Wool, 5pk
	1.6mm x 4.0 x 95 for Shimadzu GCs IP Deact., No Wool, 5pk
	1.6mm x 4.0 x 95 for Shimadzu GCs Siltek Deact., w/Deact. Wool, 5pk
	1.6mm x 4.0 x 95 for Shimadzu GCs Siltek Deact., 5pk
	1.6mm x 4.0 x 95 for Shimadzu GCs IP Deact., w/Deact. Wool, 25pk
	3.4mm x 5.0 x 54 for Varian GCs IP Deact., ea
	3.4mm x 5.0 x 54 for Varian GCs IP Deact, w/CarboFrit, ea
	3.4mm x 5.0 x 54 for Varian GCs Siltek Deact., ea
	3.4mm x 5.0 x 54 for Varian GCs IP Deact., 5pk
	3.4mm x 5.0 x 54 for Varian GCs IP Deact., w/Deact. Wool, 5pk
	3.4mm x 5.0 x 54 for Varian GCs IP Deact., w/Glass Wool, 5pk
	3.4mm x 5.0 x 54 for Varian GCs IP Deact., w/CarboFrit, 5pk
	3.4mm x 5.0 x 54 for Varian GCs IP Deact., w/CarboFrit, 5pk
	3.4mm x 5.0 x 54 for Varian GCs Siltek Deact., w/Deact. Wool, 5pk
	3.4mm x 5.0 x 54 for Varian GCs Siltek Deact., 5pk
	3.4mm x 5.0 x 54 for Varian GCs Siltek Deact., w/CarboFrit, 5pk
	Pack of 15
	2mm x 5.0 x 54 for Varian GCs IP Deact., ea
	2mm x 5.0 x 54 for Varian GCs IP Deact., w/Deact. Wool, ea
	2mm x 5.0 x 54 for Varian GCs IP Deact., w/CarboFrit, ea
	2mm x 5.0 x 54 for Varian GCs Base Deact., w/Base Deact Wool, ea
	2mm x 5.0 x 54 for Varian GCs Siltek Deact., w/Deact. Wool, ea
	2mm x 5.0 x 54 for Varian GCs Siltek Deact., ea
	2mm x 5.0 x 54 for Varian GCs Siltek Deact., w/CarboFrit, ea
	2mm x 5.0 x 54 for Varian GCs IP Deact., 5pk
	2mm x 5.0 x 54 for Varian GCs IP Deact., w/Deact. Wool, 5pk
	2mm x 5.0 x 54 for Varian GCs IP Deact., w/Glass Wool, 5pk
	2mm x 5.0 x 54 for Varian GCs IP Deact., w/CarboFrit, 5pk
	2mm x 5.0 x 54 for Varian GCs Base Deact., 5pk
	2mm x 5.0 x 54 for Varian GCs Base Deact., w/Base Deact. Wool, 5pk
	2mm x 5.0 x 54 for Varian GCs Siltek Deact., w/Deact. Wool, 5pk
	2mm x 5.0 x 54 for Varian GCs Siltek Deact., 5pk
	2mm x 5.0 x 54 for Varian GCs Siltek Deact., w/CarboFrit, 5pk
	3.5mm x 5.0 x 95 for Shimadzu GCs IP Deact., w/Deact. Wool, ea
	3.5mm x 5.0 x 95 for Shimadzu GCs IP Deact., No Wool, ea
	3.5mm x 5.0 x 95 for Shimadzu GCs Base Deact., w/Base Deact Wool, ea
	3.5mm x 5.0 x 95 for Shimadzu GCs Siltek Deact., w/Deact. Wool, ea
	0.75mm x 5.0 x 54 for Varian GCs IP Deact., ea
	0.75mm x 5.0 x 54 for Varian GCs Siltek Deact., ea
	0.75mm x 5.0 x 54 for Varian GCs IP Deact., 5pk
	0.75mm x 5.0 x 54 for Varian GCs Base Deact., 5pk
	0.75mm x 5.0 x 54 for Varian GCs Siltek Deact., 5pk
	0.75mm x 5.0 x 54 for Varian GCs IP Deact., 25pk

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034



**HROMalytic** +61(0)3 9762 2034

**ECHnology** Pty Ltd

Website NEW : [www.chromalytic.net.au](http://www.chromalytic.net.au) E-mail : [info@chromtech.net.au](mailto:info@chromtech.net.au) Tel: 03 9762 2034 . . . in AUSTRALIA

**Australian Distributors**  
Importers & Manufacturers  
[www.chromtech.net.au](http://www.chromtech.net.au)