

21717	Split/Splitless Liner	2mm x 4.0 x 86.2 for PE GCs IP Deact
21717-205	Split/Splitless Liner	2mm x 4.0 x 86.2 for PE GCs IP Deact
21717-210.1	Split/Splitless Liner	2mm x 4.0 x 86.2 for PE GCs Base Deact., ea
21717-211.1	Split/Splitless Liner	2mm x 4.0 x 86.2 for PE GCs Base Deact., w/Base Deact. Wool, ea
21717-213.1	Split/Splitless Liner	2mm x 4.0 x 86.2 for PE GCs Siltek Deact., w/Deact. Wool, ea
21717-214.1	Split/Splitless Liner	2mm x 4.0 x 86.2 for PE GCs Siltek Deact., ea
21717-231.1	Split/Splitless Liner	2mm x 4.0 x 86.2 for PE GCs IP Deact., w/ SV Wool, Ea
21718	Split/Splitless Liner	2mm x 4.0 x 86.2 for PE GCs IP Deact., w/Deact. Wool, 5pk
21718-205	Split/Splitless Liner	2mm x 4.0 x 86.2 for PE GCs IP Deact., No Wool, 5pk
21718-209.5	Split/Splitless Liner	2mm x 4.0 x 86.2 for PE GCs IP Deact., w/CarboFrit, 5pk
21718-213.5	Split/Splitless Liner	2mm x 4.0 x 86.2 for PE GCs Siltek Deact., w/Deact. Wool, 5pk
21718-214.5	Split/Splitless Liner	2mm x 4.0 x 86.2 for PE GCs Siltek Deact., 5pk
21719	Uniliner Liner	3.5mm x 5.0 x 95 for Shimadzu GCs IP Deact., w/Deact. Wool, 5pk
21719-205	Uniliner Liner	3.5mm x 5.0 x 95 for Shimadzu GCs IP Deact., No Wool, 5pk
21719-214.5	Uniliner Liner	3.5mm x 5.0 x 95 for Shimadzu GCs Siltek Deact., 5pk
21720	Vial Cap & Septa	8-425 Blk Closure Red/PTFE White Sil Septa.065"1000PK
21721	Vial Cap & Septa	8-425 Black Top Hat PTFE Sil Septa Closure 100Pack
21722	Vial Cap & Septa	8-425 Black Top Hat PTFE Sil Septa Closure 1000PK
21723	Vial Cap & Septa	10-425 Black Cap PTFE Sil Septa, Pack of 1000
21724	Aluminum Seals w/Septa	11mm 5 Asst Colors PTFE Red Rubber Septa 500Pack
21725	Aluminum Seals w/Septa	11mm 5 Asst Colors PTFE Silicone Septa Pack of 500
21728	Seals, Poly Crimp	11mm 4 Asst Colors PTFE Silicone Septa Pack of 400
21729	Snap Top Vial Cap	11mm Clear Polypropylene 10mil PTFE Pack of 100
21730	Snap Top Vial Cap	11mm Clear Polypropylene 10mil PTFE Pack of 1000
21731	Snap Top Vial Cap	11mm Clear Polypropylene PTFE/Butyl Rubber Septum, Pack of 100
21732	Snap Top Vial Cap	11mm Clear Polypropylene PTFE/Butyl Rubber Septum, Pack of 1000
21733	Snap Top Vial Cap	11mm Clear Polypropylene PTFE Sil Septa Pack of 100
21734	Snap Top Vial Cap	11mm Clear Polypropylene PTFE Sil Septa Pack of 1000
21741	Vial Caps	Black Polypropylene Open Hole Pack of 100
21742	Vial Caps	Black Polypropylene Open Hole Pack of 1000
21743	Vial Caps & Septa	13-425 Blk Poly Red/PTFE/ Sil Septa 0.065" 100Pack
21744	Vial Caps & Septa	13-425 Blk Poly Red/PTFE/ Sil Septa 0.065" 1000Pack
21745	Vial Caps & Septa	13-425 Black Top Hat PTFE/Sil Septa Pack of 100
21746	Vial Caps & Septa	13-425 Black Top Hat PTFE/Sil Septa Pack of 1000
21749	Vial Septa	Red PTFE/Silicone Septa 0.060" Pack of 100
21750	Vial Septa	Red PTFE/Silicone Septa 0.060" Pack of 1000
21751	Vial Septa	Red PTFE/Silicone/Red PTFE 0.040" Pack of 100
21752	Vial Septa	Red PTFE/Silicone/Red PTFE 0.040" Pack of 1000
21753	Aluminum Seal w/Septa	13mm Silver PTFE/RedRubber Pack of 100
21754	Aluminum Seal w/Septa	13mm Silver PTFE/RedRubber Pack of 1000
21755	Aluminum Seal w/Septa	13mm Silver PTFE/Silicone Pack of 100
21756	Aluminum Seal w/Septa	13mm Silver PTFE/Silicone Pack of 1000
21761	Aluminum Seal w/Septa	20mm Alum. Silver w/PTFE Gray Butyl Rub Septa 100PK
21762	Aluminum Seal w/Septa	20mm Alum. Silver w/PTFE Gray Butyl Rub Septa 1000PK
21763	Aluminum Seal w/Septa	20mm Alum. Silver w/PTFE Silicone Pack of 100
21764	Aluminum Seal w/Septa	20mm Alum. Silver w/PTFE Silicone Pack of 1000
21765	Aluminum Seal w/Septa	20mm Press Rel.Silvr w/PTFE Gray Butyl 100Pack
21766	Aluminum Seal w/Septa	20mm Press Rel.Silvr w/PTFE Gray Butyl 1000Pack
21767	Aluminum Seal w/Septa	20mm Press Rel.Silvr w/PTFE Silicone 100Pack
21768	Aluminum Seal w/Septa	20mm Press Rel.Silvr w/PTFE Silicone 1000Pack
21769	Snap Plug, Starburst	8mm, Clear Low Density Polyethylene Pack of 200
21770	Snap Plug, Starburst	8mm, Clear Low Density Polyethylene Pack of 1000
21771	Snap Plug, Conical	8mm Starburst, Clear Low Density Poly. 200Pack
21772	Snap Plug, Conical	8mm Starburst, Clear Low Density Poly. 1000Pack
21773	Snap Plug, Starburst	8mm Clr Silicone Lined Pack of 200
21774	Snap Plug, Starburst	8mm Clr Silicone Lined Pack of 1000
21775	Vial Inserts	100ul Glass LV w/PP Bottom Spring Pack of 1000
21776	Vial Inserts	250ul Glass BM w/Bottom Spring Pack of 100
21777	Vial Inserts	250ul Glass BM w/Bottom Spring Pack of 1000
21779	Vial Inserts	250ul Glass BM Pack of 1000 w/Glass Flange (step)
21780	Vial Inserts	350ul Glass Flat Bottom Pack of 100
21780-220	Vial Inserts	350ul Glass Flat Bottom Deactivation Pack of 100
21782	Vial Inserts	50ul Glass w/Polypropylene Bottom Spring Pack of 1000
21787	Vial Inserts	500ul Glass WISP Flt Bot Pack of 100
21788	Vial Inserts	500ul Glass WISP Flt Bot Pack of 1000
21795	Vial Septa	8mm x 0.065" Red PTFE/White Silicone Septa 100pk

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034

 HROMalytic +61(0)3 9762 2034 ECHnology Pty Ltd		Australian Distributors Importers & Manufacturers www.chromtech.net.au
Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA		

