

21796	Pre-Cleaned VOA Vials
21797	Pre-Cleaned VOA Vials
21797-220	Pre-Cleaned VOA Vials
21798	Pre-Cleaned VOA Vials
21799	Pre-Cleaned VOA Vials
21799-220	Deact VOA Vials
21800	Parker Fitting, Brass
21801	Parker Fitting, Brass
21802	Parker Fitting, Brass
21803	Parker Fitting, Brass
21804	Parker Fitting, Brass
21805	Parker Fitting, Brass
21806	Parker Fitting, Brass
21807	Parker Fitting, Brass
21808	Parker Fitting, Brass
21809	Parker Fitting, Brass
21810	Parker Fitting, Brass
21811	Parker Fitting, Brass
21815	Parker Fitting, Brass
21816	Parker Fitting, Brass
21817	Parker Fitting, Brass
21818	Parker Fitting, Brass
21819	Parker Fitting, Brass
21820	Parker Fitting, Brass
21823	Parker Fitting, Brass
21824	Parker Fitting, Brass
21825	Parker Fitting, Brass
21826	Parker Fitting, Brass
21827	Parker Fitting, Brass
21828	Parker Fitting, Brass
21829	Parker Fitting, Brass
21830	Parker Fitting, Brass
21831	Parker Fitting, Brass
21832	Parker Fitting, Brass
21833	Parker Fitting, Brass
21834	Parker Fitting, Brass
21835	Parker Fitting, Brass
21836	Parker Fitting, Brass
21837	Parker Fitting, Brass
21841	Parker Fitting, Brass
21842	Parker Fitting, Brass
21843	Parker Fitting, Brass
21844	Parker Fitting, Brass
21845	Parker Fitting, Brass
21846	Parker Fitting, Brass
21847	Parker Fitting, Brass
21848	Parker Fitting, Brass
21878	Brass Capillary Nut
21879	Brass Capillary Nut
21883	Plug Nuts for Agilent GCs
21884	Capillary Nut, SS
21891	Dbl Gooseneck Splitless
21891-214.1	Dbl Gooseneck Splitless
21892	Dbl Gooseneck Splitless
21892-214.5	Dbl Gooseneck Splitless
21893	Re-Threading Tool
21894	Installation Tool
21895	Injector Nut Kit
21896	Gooseneck Splitless Liner
21896-200.1	Gooseneck Splitless Liner
21896-209.1	Gooseneck Splitless Liner
21896-210.1	Gooseneck Splitless Liner
21896-211.1	Gooseneck Splitless Liner
21896-213.1	Gooseneck Splitless Liner
21896-214.1	Gooseneck Splitless Liner
21896-216.1	Gooseneck Splitless Liner

40ml Clear, Open Top w/0.125" Teflon
40ml Amber, Open Top w/0.125" Teflon
40ml Amber, Open Top w/0.125in Teflon/Silicone Septa, 72pk
20ml Clear, Open Top w/0.125" Teflon/Silicone Septa, 72pk
20ml Amber, Open Top w/0.125" Teflon/Silicone Septa, 72pk
20ml Amber, Open Top w/0.125" Teflon/Silicone Septa, 72pk
1/16" Nut 20-pk
1/8" Nut Pack of 40
1/4" Nut Pack of 40
1/16" Front Ferrule Pack of 20
1/8" Front Ferrule Pack of 40
1/4" Front Ferrule Pack of 40
1/16" Back Ferrule Pack of 20
1/8" Back Ferrule Pack of 40
1/4" Back Ferrule Pack of 40
1/16" Nut & Ferrule Set Pack of 10
1/8" Nut & Ferrule Set Pack of 20
1/4" Nut & Ferrule Set Pack of 20
1/16" Plug Pack of 5
1/8" Plug Pack of 10
1/4" Plug Pack of 10
1/16" to 1/16" Union Pack of 3
1/8" to 1/8" Union Pack of 5
1/4" to 1/4" Union Pack of 5
1/8" to 1/16" Reducing Union Pack of 5
1/4" to 1/16" Reducing Union Pack of 5
1/4" to 1/8" Reducing Union Pack of 5
1/16" Tee Pack of 2
1/8" Tee Pack of 2
1/4" Tee Pack of 2
1/8" Cross Pack of 2
1/4" Cross Pack of 2
1/8" to 1/16" Tube End Reducer Pack of 5
1/4" to 1/16" Tube End Reducer Pack of 5
1/8" to 1/4" Tube End Reducer Pack of 5
1/4" to 1/8" Tube End Reducer Pack of 5
1/8" Port Connector Pack of 5
1/4" Port Connector Pack of 10
1/8" to 1/4" Port Connector Pack of 5
1/8" to 1/8" NPT Male Connector Pack of 10
1/4" to 1/4" NPT Male Connector Pack of 10
1/16" to 1/8"NPT Male Connector Pack of 5
1/8" to 1/4" NPT Male Connector Pack of 10
1/4" to 1/8" NPT Male Connector Pack of 10
1/8" to 1/8" NPT Female Connect Pack of 5
1/4" to 1/4" NPT Female Connect Pack of 5
1/4" to 1/8" NPT Female Connect Pack of 5
For use w/Agilent 5890/6890 Use w/Std Agilent Compact Ferrules Pack of 2
For use w/Agilent 5890/6890 Use w/Std 1/16" Ferrules Pack of 2
Injector/Detector Plug Nuts 2-pk
For HP GC, Pack of 2 (Uses HP "Compact" Ferrules)
Liner, 4mm x 6.5 x 78.5 for Varian GCs, IP Deact., ea
Liner, 4mm x 6.5 x 78.5 for Varian GCs, Siltek Deact., ea
Liner, 4mm x 6.5 x 78.5 for Varian GCs, IP Deact., 5pk
Liner, 4mm x 6.5 x 78.5 for Varian GCs, Siltek Deact., 5pk
for 1/4" Varian Capillary Column Fittings
Capillary Installation Tool for Agilent 5973/5975 MS
For Shimadzu 17A, 2010 & 2014 GCs Includes: inj nut, .4mm graphite ferrule 1/16
4mm x 6.5 x 78.5 for Varian GCs IP Deact., ea
4mm x 6.5 x 78.5 for Varian GCs IP Deact., w/Deact. Wool, ea
4mm x 6.5 x 78.5 for Varian GCs IP Deact., w/CarboFrit, ea
4mm x 6.5 x 78.5 for Varian GCs Base Deact., Ea
4mm x 6.5 x 78.5 for Varian GCs Base Deact., w/Base Deact. Wool, ea
4mm x 6.5 x 78.5 for Varian GCs Siltek Deact., w/Deact. Wool, ea
4mm x 6.5 x 78.5 for Varian GCs Siltek Deact., ea
4mm x 6.5 x 78.5 for Varian GCs Siltek Deact., w/Carbofrit, ea

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034



**HROMalytic** +61(0)3 9762 2034  
**ECHnology** Pty Ltd

**Australian Distributors**  
 Importers & Manufacturers  
[www.chromtech.net.au](http://www.chromtech.net.au)

Website NEW : [www.chromalytic.net.au](http://www.chromalytic.net.au) E-mail : [info@chromtech.net.au](mailto:info@chromtech.net.au) Tel: 03 9762 2034 . . . in AUSTRALIA

