

22004 Replacement Tower
22005 Replacement Tower
22006 Replacement Tower
22007 Replacement Tower
22008 Replacement Tower
22010 Trap, Oxygen
22011 Trap, Oxygen
22012 Trap, Hydrocarbon
22013 Trap, Hydrocarbon
22014 Trap, Moisture
22015 Trap, Moisture
22016 Trap
22017 Trap, ECD Vent
22019 Trap, SGT
22020 Trap, SGT
22021 Trap, SGT
22022 Trap, SGT
22023 SGT Maintenance
22025 Baseplate, SGT
22026 Baseplate, SGT
22027 Baseplate, SGT
22028 Trap, SGT
22029 Trap, SGT
22030 Trap, SGT
22031 Trap, SGT
22032 Regulator, Brass
22038 Tedlar Bag
22039 Tedlar Bag
22040 Tedlar Bag
22041 Tedlar Bag
22042 Tedlar Bag
22043 Tedlar Bag
22048 Tedlar Bag
22049 Tedlar Bag
22052 Tedlar Bag
22053 Tedlar Bag
22054 Tedlar Bag
22061 Trap, SGT
22062 Trap, SGT
22064 O-Rings
22065 Injector Wrench
22066 Tool
22067 O-Rings, Viton
22068 Injector/FID Heater
22069 Injector/FID Heater
22071 FID Gauge Pack
22072 Cyclosplitter Liner
22072-209.1 Cyclosplitter Liner
22072-210.1 Cyclosplitter Liner
22072-214.1 Cyclosplitter Liner
22073 Cyclosplitter Liner
22073-209.5 Cyclosplitter Liner
22073-210.5 Cyclosplitter Liner
22073-214.5 Cyclosplitter Liner
22074 Baffle Liner
22074-210.1 Baffle Liner
22074-211.1 Baffle Liner
22074-214.1 Baffle Liner
22075 Baffle Liner
22075-210.5 Baffle Liner
22075-211.5 Baffle Liner
22075-214.5 Baffle Liner
22076 Air Diverters
22077 Capillary Adapter
22078 Reducing Nut
22079 Septa Nut, Shimadzu

Page 78
Replacement Tower Module Zero Air
Replacement Tower Module for Zero
Replacement Tower Module Zero Air
Replacement Tower Module Zero Air Generator Model HPZA-18000 (20682) Dom
Replacement Tower Module Zero Air Generator Model HPZA-30000 (20683) Dom
Indicating, 1/8" Fittings CAN NOT SHIP FEDEX GROUND
Indicating, 1/4" Fittings CAN NOT SHIP FEDEX GROUND
Refillable, 1/8" Fittings
Refillable, 1/4" Fittings
Indicating, 1/8" Fittings
Indicating, 1/4" Fittings (replaces 20604)
Hydrocarbon S-Trap 1/8" Fittings
for HP
Complete Carrier Gas Filter Kit. Baseplate and Triple Filter. Oxygen, Moisture and
Replacement Trap Triple Trap for Carrier Gas Oxygen, Moisture & Hydrocarbon T
FID Fuel Gas Filter Kit Baseplate + Hydrocarbon & Moisture Filter (1/8")
Replacement Trap for FID Fuel Gas. Hydrocarbon & Moisture Combination Trap
Replacement O-Ring Set for Baseplate 20pk, 10 Large O-rings, 10 Small O-rings
Single Position Baseplate for One- SGT Cartridge Filter, Brass
Two Position Baseplate For Two-SGT Cartridge Filters, Brass
Three Position Baseplate For Three-SGT Cartridge Filters
Replacement Moisture Filter, Ultra High Capacity
Replacement Oxygen Filter, Ultra High Capacity, Brass
Replacement (Charcoal) Hydrocarbons Filter, Ultra High Capacity
Filter Bundle, 1 Triple Filter and 2 Fuel Gas Filters Uses 3 Position Baseplate
for CGA 170 Gas Stds. 0-15psig outlet 0-300psig Inlet
Discontinue When Stock is Depleted w/Single SS Valve and Septum Fitting 0.5 Li
Discontinue When Stock is Depleted w/Single SS Valve and Septum Fitting 1 Lite
Discontinue When Stock is Depleted w/Single SS Valve and Septum Fitting 3 Lite
Discontinue When Stock is Depleted w/Single SS Valve and Septum Fitting 5 Lite
Discontinue When Stock is Depleted w/Single SS Valve and Septum Fitting 10 Lit
w/Single SS Valve and Septum Fitting 12 Liter Cap., 13" x 24", 10pk DISCONTINI
Discontinue When Stock is Depleted Replacement Septum for SS Valve Tedlar B
Discontinue When Stock is Depleted w/Single Polypropylene Valve & Septum Fitti
Discontinue When Stock is Depleted w/Single Polypropylene Valve & Septum Fitti
Discontinue When Stock is Depleted w/Single Polypropylene Valve & Septum Fitti
w/Single Polypropylene Valve & Septum Fitting 12 Liter Cap., 13" x 24", 10pk DIS
Charcoal Replacement Filter for LC/MS Trap, 2PK
Super Clean Cartridge System for LC/MS, 2 Position Baseplate & 2 Charcoal Filte
for Agilent Trap Fittings 25pk
for Agilent 5890/6890/6850 GCs
Temperature Measuring Stick
for Apex Liners 25pk
PRT Sensor Assembly For Agilent 5890GC
For Agilent 5890GC
For HP GCs
3.5mm x 5.0 x 95 for Shimadzu GCs IP Deact., ea
3.5mm x 5.0 x 95 for Shimadzu GCs IP Deact., w/CarboFrit, ea
3.5mm x 5.0 x 95 for Shimadzu GCs Base Deact., ea
3.5mm x 5.0 x 95 for Shimadzu GCs Siltek Deact., ea
3.5mm x 5.0 x 95 for Shimadzu GCs IP Deact., 5pk
3.5mm x 5.0 x 95 for Shimadzu GCs IP Deact., w/CarboFrit, 5pk
3.5mm x 5.0 x 95 for Shimadzu GCs Base Deact, 5pk
3.5mm x 5.0 x 95 for Shimadzu GCs Siltek Deact., 5pk
2mm x 2.75 x 120 for Thermo GCs IP Deact., ea
2mm x 2.75 x 120 for Thermo GCs Base Deact., Ea
2mm x 2.75 x 120 for Thermo GCs Base Deact., w/Base Deact. Wool, ea
2mm x 2.75 x 120 for Thermo GCs Siltek Deact., ea
2mm x 2.75 x 120 for Thermo GCs IP Deact., 5pk
2mm x 2.75 x 120 for Thermo GCs Base Deact., 5pk
2mm x 2.75 x 120 for Thermo GCs Base Deact., w/Base Deact. Wool, 5pk
2mm x 2.75 x 120 for Thermo GCs Siltek Deact., 5pk
For HP 5890/6890 GCs
FID/NPD, For HP 5890/6890 GCs
For the HP 5890/6890/6850 GCs
for use with Shimadzu 17A, 2010 & 2014 GCs

