

22184	MLE Capillary Tool Kit	for Varian GCs
22185	MLE Capillary Tool Kit	for Perkin Elmer GCs
22186	MLE Capillary Tool Kit	For Agilent GCs
22187	Flashlight	w/Swivel Head
22188	Parker Valve, Brass	1/8" Toggle
22189	Parker Valve, Brass	1/4" Toggle
22190	Parker Valve	Stainless Steel, 1/8" Toggle
22191	Parker Valve	Stainless Steel, 1/4" Toggle
22192	Parker Valve, Brass	1/8" 2-Way Ball
22193	Parker Valve, Brass	1/4" 2-Way Ball
22194	Parker Valve	Stainless Steel, 1/8" 2-Way Ball
22195	Parker Valve	Stainless Steel, 1/4" 2-Way Ball
22196	Parker Valve, Brass	1/8" Plug
22197	Parker Valve, Brass	1/4" Plug
22198	Parker Valve	Stainless Steel, 1/8" Plug
22199	Parker Valve	Stainless Steel, 1/4" Plug
22200	Parker Valve	Precision Metering, 1/8", Straight, Brass
22201	Parker Valve	Precision Metering, 1/4", Straight, Brass
22204	Parker Valve	Precision Metering, 1/8", Straight, Stainless Steel
22205	Parker Valve	Precision Metering, 1/4", Straight, Stainless Steel
22209	Parker Vernier Handle	for Metering Valves, Add-on Accessory
22210	Vespel Ferrules	1/16" x 1/16", 10pk
22211	Vespel Ferrules	1/8" x 1/8", 10pk
22212	Vespel Ferrules	1/4" x 1/4", 10pk
22213	Vespel Ferrules	1/16" x 0.3mm, 10pk
22214	Vespel Ferrules	1/16" x 0.4mm, 10pk
22215	Vespel Ferrules	1/16" x 0.5mm, 10pk
22216	Vespel Ferrules	1/16" x 0.8mm, 10pk
22217	Vespel Ferrules	1/16" x 1.0mm, 10pk
22218	Vespel Ferrules	1/16" x 1.2mm, 10pk
22219	Vespel Ferrules	1/4"x1/8", 10pk
22220	Vu2 Union Connector Kit	Fits 0.10/0.15mm ID Columns
22221	Graphite Ferrule, 0.3mmID	for M4 Fitting, for 8000 and Trace 2000 GCs, 2pk
22222	Graphite Ferrule, 0.3mmID	for M4 Fitting, for 8000 and Trace 2000 GCs, 10pk
22223	Graphpack 2M Ferrules	For use w/Gerstel PTV inlet, Fits 0.25mm ID Columns, 10-pk
22224	Graphpack 2M Ferrules	For use w/Gerstel PTV inlet, Fits 0.32mm ID Columns, 10-pk
22225	Graphpack 2M Ferrules	For use w/Gerstel PTV inlet, Fits 0.53mm ID Columns, 10-pk
22226	Merlin MicroShot Injector	0.1uL Volume Delivery
22227	Merlin MicroShot Injector	0.2uL Volume Delivery
22228	Merlin MicroShot Injector	0.5uL Volume Delivery
22229	Merlin MicroShot Injector	1.0uL Volume Delivery
22230	Merlin MicroShot Injector	2.0uL Volume Delivery
22268	Uniliner Liner	4mm x 6.3 x 78.5 for Agilent GCs IP Deact., ea
22268-214.1	Uniliner Liner	4mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., Ea.
22269	Uniliner Liner	4mm x 6.3 x 78.5 for Agilent GCs IP Deact., 5-pk
22269-210.5	Uniliner Liner	4mm x 6.3 x 78.5 for Agilent GCs Base Deact., 5pk
22269-214.5	Uniliner Liner	4mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., 5pk
22270	Cyclo-Uniliner Liner	4mm x 6.3 x 78.5 for Agilent GCs IP Deact., ea
22270-214.1	Cyclo-Uniliner Liner	4mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., Ea
22271	Cyclo-Uniliner Liner	4mm x 6.3 x 78.5 for Agilent GCs IP Deact., 5-pk
22271-214.5	Cyclo-Uniliner Liner	4mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., 5pk
22272	Open Top Uniliner Liner	4mm x 6.3 x 78.5 for Agilent GCs IP Deact. w/Deact. Wool, ea
22272-205	Open Top Uniliner Liner	4mm x 6.3 x 78.5 for Agilent GCs IP Deact., ea
22272-211.1	Open Top Uniliner Liner	4mm x 6.3 x 78.5 for Agilent GCs Base Deact. w/ Base Wool, Ea
22272-213.1	Open Top Uniliner Liner	4mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., Deact. Wool, ea
22272-214.1	Open Top Uniliner Liner	4mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., Ea
22273	Open Top Uniliner Liner	4mm x 6.3 x 78.5 for Agilent GCs IP Deact. w/Deact. Wool, 5-pk
22273-202.5	Open Top Uniliner Liner	4mm x 6.3 x 78.5 for Agilent GCs IP Deact. w/ Glass Wool, 5pk
22273-205	Open Top Uniliner Liner	4mm x 6.3 x 78.5 for Agilent GCs IP Deact., No Wool, 5 pk
22273-211.5	Open Top Uniliner Liner	4mm x 6.3 x 78.5 for Agilent GCs Base Deact., w/ Base Wool, 5pk
22273-213.5	Drilled Top Uniliner Lnr	4mm x 6.3 x 78.5 for Agilent GCs Siltek Deact, w/ Deact. Wool, 5pk
22273-231.5	Open Top-Uniliner Liner	4mm x 6.3 x 78.5 for Agilent GCs IP Deact. w/ SV Wool, 5pk
22274	Double Gooseneck Liner	3.5mm x 5.0 x 95 for Shimadzu GCs IP Deact., ea
22275	Double Gooseneck Liner	3.5mm x 5.0 x 95 for Shimadzu GCs IP Deact., 5pk
22275-210.5	Double Gooseneck Liner	3.5mm x 5.0 x 95 for Shimadzu GC, Base Deact, 5pk
22275-214.5	Double Gooseneck Liner	3.5mm x 5.0 x 95 for Shimadzu GCs Siltek Deact., 5pk

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034

 HROMalytic +61(0)3 9762 2034 ECHnology Pty Ltd		Australian Distributors Importers & Manufacturers www.chromtech.net.au
Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA		

[Ctrl F]
> Cat.#s

> Current System AUD Prices

