

22408 Recessed Gooseneck Liner  
 22409 Recessed Gooseneck Liner  
 22409-211.5 Recessed Gooseneck Liner  
 22409-213.5 Recessed Gooseneck Liner  
 22409-231.5 Recessed Gooseneck Liner  
 22410 Recessed Gooseneck Liner  
 22410-209.25 Recessed Gooseneck Liner  
 22411 Drilled Uniliner Liner  
 22411-200.1 Drilled Uniliner Liner  
 22411-213.1 Drilled Uniliner Liner  
 22411-214.1 Drilled Uniliner Liner  
 22412 Drilled Uniliner Liner  
 22412-200.5 Drilled Uniliner Liner  
 22412-214.5 Drilled Uniliner Liner  
 22413 Drilled Uniliner Liner  
 22413-214.1 Drilled Uniliner Liner  
 22414 Drilled Uniliner Liner  
 22415 Open Liner  
 22415-209.1 Open Liner  
 22415-216.1 Open Liner  
 22415-231.1 Open Liner  
 22416 Open Liner  
 22416-209.5 Open Liner  
 22416-214.5 Open Liner  
 22416-229.5 Open Liner  
 22417 Open Liner  
 22417-214.1 Open Liner  
 22418 Open Liner  
 22418-214.5 Open Liner  
 22419 Fritted Gooseneck Liner  
 22419-214.1 Fritted Gooseneck Liner  
 22419-231.1 Fritted Gooseneck Liner  
 22420 Fritted Gooseneck Liner  
 22420-214.5 Fritted Gooseneck Liner  
 22420-231.5 Fritted Gooseneck Liner  
 22421 Low Pressure Drop  
 22422 Low Pressure Drop  
 22422-213.5 Low Pressure Drop  
 22423 EZ No-Vent Connector Kit  
 22424 Micropacked Adapter Kit  
 22425 Micropacked Adapter Kit  
 22426 Micropacked Adapter Kit  
 22427 Micropacked Adapter Kit  
 22428 Micropacked Adapter  
 22429 Replacement Inlet Seal  
 22430 Replacement Inlet Guide  
 22431 EZ No-Vent Connector Kit  
 22432 EZ No-Vent Ferrules  
 22433 Interlocked Vial/Insert  
 22434 Interlocked Vial/Insert  
 22435 Interlocked Vial/Insert  
 22436 Interlocked Vial/Insert  
 22437 Interlocked Vial/Insert  
 22438 Interlocked Vial/Insert  
 22439 Interlocked Vial/Insert  
 22440 Interlocked Vial/Insert  
 22452 Line Regulator, Brass  
 22454 EZ No-Vent Connector Kit  
 22455 Wrench Set  
 22456 Trap, SGT Click-On  
 22457 Trap, SGT Click-On  
 22458 Trap, SGT Click-On  
 22459 Trap, SGT Click-On  
 22460 Trap, SGT Click-On  
 22461 Trap, SGT Click-On  
 22462 Trap, SGT Click-On

4mm x 8.5 x 78.5 for Agilent GCs IP Deact., w/Deact. Wool, 5pk  
 4mm x 6.5 x 78.5 for Agilent GCs IP Deact., w/Deact. Wool, 5pk  
 4mm x 6.5 x 78.5 for Agilent GCs Base Deact., w/Deact. Wool, 5pk  
 4mm x 6.5 x 78.5 for Agilent GCs Siltek Deact., w/Deact. Wool, 5pk  
 4mm x 6.5 x 78.5 for Agilent GCs IP Deact., w/ SV Wool, 5pk  
 4mm x 6.5 x 78.5 for Agilent GCs IP Deact., w/Deact. Wool, 25pk  
 4mm x 6.5 x 78.5 for Agilent GCs IP Deact., w/CarboFrit, 25pk  
 Hole on Top, 5mm x 8.0 x 105 for Thermo GCs, IP Deact., ea  
 Hole on Top, 5mm x 8.0 x 105 For Thermo GCs, IP Deact., w/Deact. Wool, ea  
 Hole on Top, 5mm x 8.0 x 105 for Thermo GCs, Siltek, Deact Wool, Ea  
 Hole on Top, 5mm x 8.0 x 105 for Thermo GCs, Siltek Deact., ea  
 Hole on Top, 5mm x 8.0 x 105 for Thermo GCs, IP Deact., 5pk  
 Hole on Top, 5mm x 8.0 x 105 for Thermo GCs IP Deact., w/Deact. Wool, 5pk  
 Hole on Top, 5mm x 8.0 x 105 for Thermo GCs, Siltek Deact., 5pk  
 Hole on Bottom, 5mm x 8.0 x 105 for Thermo GCs, IP Deact., ea  
 Hole on Bottom, 5mm x 8.0 x 105 for Thermo GCs, Siltek Deact., ea  
 Hole on Bottom, 5mm x 8.0 x 105 for Thermo GCs, IP Deact., 5pk  
 3mm x 5.0 x 80 for ATAS GCs IP Deact., ea  
 3mm x 5.0 x 80 for ATAS GCs IP Deact., w/CarboFrit, ea  
 3mm x 5.0 x 80 for ATAS GCs Siltek Deact., w/ Carbofrit, Ea  
 3mm x 5.0 x 80 for ATAS GCs IP Deact., SV Wool, ea  
 3mm x 5.0 x 80 for ATAS GCs IP Deact., 5pk  
 3mm x 5.0 x 80 for ATAS GCs IP Deact. w/ CarboFrit, 5pk  
 3mm x 5.0 x 80 for ATAS GCs Siltek Deact., 5pk  
 3mm x 5.0 x 80 for ATAS GCs Base Deact., w/CarboFrit, 5pk  
 1mm x 5.0 x 80 for ATAS GCs IP Deact., ea  
 1mm x 5.0 x 80 for ATAS GCs Siltek Deact., ea  
 1mm x 5.0 x 80 for ATAS GCs IP Deact., 5pk  
 1mm x 5.0 x 80 for ATAS GCs Siltek Deact., 5pk  
 3mm x 5.0 x 80 for ATAS GCs IP Deact., ea  
 3mm x 5.0 x 80 for ATAS GCs Siltek Deact., ea  
 3mm x 5.0 x 80 for ATAS GCs IP Deact. w/ SV Wool, Ea  
 3mm x 5.0 x 80 for ATAS GCs IP Deact., 5pk  
 3mm x 5.0 x 80 for ATAS GCs Siltek Deact., 5pk  
 3mm x 5.0 x 80 for ATAS GCs IP Deact, SV Wool, 5pk  
 Precision Liner, 2mm x 6.3 x 78.5 for Varian GCs, IP Deact., w/Deact. Wool, ea  
 Precision Liner, 2mm x 6.3 x 78.5 for Varian GCs, IP Deact., w/Deact. Wool, 5pk  
 Precision Liner, 2mm x 6.3 x 78.5 for Varian GCs, Siltek Deact., w/Deact. Wool, 5,  
 for Varian Saturn 2000 Series MSs with 3400, 3600, 3800 GCs  
 Discontinue When Stock is Depleted Split/Splitless Injection. Complete Kit w/Injec  
 Column Adapter Kit for On Column Injection. Complete Kit w/Injection Port and Fil  
 Injection Port Adapter Kit for Split/Splitless Injections. Split/Splitless Injection Port  
 Injection Port Adapter Kit for On Column Injections. Split/Splitless Injection Port Ac  
 Column Adapter Fitting for FID \*\* For Use w/Packed Column FIDs Only \*\*  
 for Micropacked Column Adapter. 2pk  
 Replacement Siltek On Column Inlet Guide  
 for Shimadzu GCMS-QP2010 and GCMS-QP2010 Plus  
 for Connecting Transfer Line to EZ No-Vent Connector, 0.4mm ID, 2-pk  
 300uL Clear, 9mm Thread 100-pk  
 300uL Clear, 9mm Thread 500-pk  
 300uL Amber, 9mm Thread 100-pk  
 300uL Amber, 9mm Thread 500-pk  
 300uL Clear, 11mm Crimp or Snap Ring 100-pk  
 300uL Clear, 11mm Crimp or Snap Ring 500-pk  
 300uL Amber, 11mm Crimp or Snap Ring 100-pk  
 300uL Amber, 11mm Crimp or Snap Ring 500-pk  
 Single Stage, Ultra High Purity Outlet Pressure: 0-100psig  
 for Thermo Focus DSQ GC/MS  
 3/8" x 7/16" Open End Use w/EZ No-Vent for Thermo DSQ 2-pk  
 Complete Carrier Gas Filter Kit, 1/8" SS, Includes 2 Connectors and 1 Triple Trap  
 Complete Carrier Gas Filter Kit, 1/8" Brass, Includes 2 Connectors and 1 Triple Tr  
 Complete Carrier Gas Filter Kit, 1/4" SS, Includes 2 Connectors and 1 Triple Trap  
 Complete Carrier Gas Filter Kit, 1/4" Brass, Includes 2 Connectors and 1 Triple Tr  
 Complete Fuel Gas Filter Kit, 1/8" SS, Includes 4 Connectors and 2 Moisture/Hydr  
 Complete Fuel Gas Filter Kit, 1/8" Brass, Includes 4 Connectors and 2 Moisture/H  
 Complete Fuel Gas Filter Kit, 1/4" SS, Includes 4 Connectors and 2 Moisture/Hydr

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034



**HROMalytic** +61(0)3 9762 2034  
**ECHnology** Pty Ltd

**Australian Distributors**  
 Importers & Manufacturers  
[www.chromtech.net.au](http://www.chromtech.net.au)

Website NEW : [www.chromalytic.net.au](http://www.chromalytic.net.au) E-mail : [info@chromtech.net.au](mailto:info@chromtech.net.au) Tel: 03 9762 2034 . . . in AUSTRALIA

