

| | | |
|-------|-------------------------|---|
| 22463 | Trap, SGT Click-On | Complete Fuel Gas Filter Kit, 1/4" Bra |
| 22464 | Trap, SGT Click-On | Replacement Triple Trap for Carrier C |
| 22465 | Trap, SGT Click-On | Replacement Trap for FID Fuel Gas, Includes 1 |
| 22466 | Trap, SGT Click-On | Replacement Hydrocarbon Trap Ultra High Capacity |
| 22467 | Trap, SGT Click-On | Replacement Moisture Trap Ultra High Capacity |
| 22468 | Trap, SGT Click-On | Replacement Oxygen Trap Ultra High Capacity |
| 22469 | Trap, SGT Click-On | Complete Helium Specific Gas Filter Kit, 1/8" SS, Includes 2 Connectors and 1 Tri |
| 22470 | Trap, SGT Click-On | Complete Helium Specific Gas Filter Kit, 1/8" Brass, Includes 2 Connectors and 1 |
| 22471 | Trap, SGT Click-On | Complete Helium Specific Gas Filter Kit, 1/4" SS, Includes 2 Connectors and 1 Tri |
| 22472 | Trap, SGT Click-On | Complete Helium Specific Gas Filter Kit, 1/4" Brass, Includes 2 Connectors and 1 |
| 22473 | Trap, SGT Click-On | Replacement Helium Specific Triple Trap Oxygen/Moisture/Hydrocarbon |
| 22474 | Trap, SGT Click-On | Indicating Cartridge |
| 22475 | Trap, SGT Click-On | 1/8" Brass Connectors Pack of 2 |
| 22476 | Trap, SGT Click-On | 1/8" Stainless Steel Connectors Pack of 2 |
| 22477 | Trap, SGT Click-On | 1/4" Brass Connectors Pack of 2 |
| 22478 | Trap, SGT Click-On | 1/4" Stainless Steel Connectors Pack of 2 |
| 22479 | Trap, SGT Click-On | Double Connector |
| 22480 | Trap, SGT Click-On | Wall Mounting Clamps Pack of 4 |
| 22481 | Trap, SGT Click-On | Replacement O-rings for Click-On Connectors, Pack of 20, 10 small & 10 large O- |
| 22482 | Pump Block Piston Seal | for Agilent 1050/1100/1200, Teflon w/Graphite, 2pk |
| 22483 | Pump Block Piston Seal | for Agilent 1050/1100/1200, Teflon w/Graphite, 10pk |
| 22484 | Mobile Phase Pre-Heater | |
| 22485 | ResTape Teflon Tape | 1/2" x 260" Green PTFE Thread Tape for Oxygen Service, High Purity |
| 22486 | ResTape Teflon Tape | 1/2" x 260" Yellow PTFE Thread Tape for Gas Service, Gas Tight 3 Wrap |
| 22487 | ResTape Teflon Tape | 1/2" x 260" Gray PTFE Thread Tape for Stainless Steel, Anti Galling |
| 22488 | Silcosteel-Hydroguard | Tubing, 1/4"OD, 0.035"Wall Electropolished 316L Seamless Tubing, Min.Order Qt |
| 22488 | Silcosteel-Hydroguard | Tubing, 1/4"OD, 0.035"Wall Electropolished 316L Seamless Tubing, Min.Order Qt |
| 22488 | Silcosteel-Hydroguard | Tubing, 1/4"OD, 0.035"Wall Electropolished 316L Seamless Tubing, Min.Order Qt |
| 22489 | Silcosteel-Hydroguard | Tubing, 1/8"OD, 0.020" Wall Electropolished 316L Seamless Tubing, Min.Order Q |
| 22489 | Silcosteel-Hydroguard | Tubing, 1/8"OD, 0.020" Wall Electropolished 316L Seamless Tubing, Min.Order Q |
| 22489 | Silcosteel-Hydroguard | Tubing, 1/8"OD, 0.020" Wall Electropolished 316L Seamless Tubing, Min.Order Q |
| 22489 | Silcosteel-Hydroguard | Tubing, 1/8"OD, 0.020" Wall Electropolished 316L Seamless Tubing, Min.Order Q |
| 22490 | Silcosteel-Hydroguard | Tubing 0.180"ID x 1/4"OD 0.035" Wall 316L Seamless Min.Order Qty: 5 Feet |
| 22490 | Silcosteel-Hydroguard | Tubing 0.180"ID x 1/4"OD 0.035" Wall 316L Seamless Min.Order Qty: 5 Feet |
| 22490 | Silcosteel-Hydroguard | Tubing 0.180"ID x 1/4"OD 0.035" Wall 316L Seamless Min.Order Qty: 5 Feet |
| 22490 | Silcosteel-Hydroguard | Tubing 0.180"ID x 1/4"OD 0.035" Wall 316L Seamless Min.Order Qty: 5 Feet |
| 22491 | Silcosteel-Hydroguard | Tubing 0.055"ID x 1/8"OD 0.035" Wall 316L Seamless Min.Order Qty: 5 Feet |
| 22491 | Silcosteel-Hydroguard | Tubing 0.055"ID x 1/8"OD 0.035" Wall 316L Seamless Min.Order Qty: 5 Feet |
| 22491 | Silcosteel-Hydroguard | Tubing 0.055"ID x 1/8"OD 0.035" Wall 316L Seamless Min.Order Qty: 5 Feet |
| 22491 | Silcosteel-Hydroguard | Tubing 0.055"ID x 1/8"OD 0.035" Wall 316L Seamless Min.Order Qty: 5 Feet |
| 22492 | Silcosteel-Hydroguard | Tubing 0.210"ID x 1/4"OD Min.Order Qty: 5 Feet |
| 22492 | Silcosteel-Hydroguard | Tubing 0.210"ID x 1/4"OD Min.Order Qty: 5 Feet |
| 22492 | Silcosteel-Hydroguard | Tubing 0.210"ID x 1/4"OD Min.Order Qty: 5 Feet |
| 22492 | Silcosteel-Hydroguard | Tubing 0.210"ID x 1/4"OD Min.Order Qty: 5 Feet |
| 22493 | Silcosteel-Hydroguard | Tubing 0.085"ID x 1/8"OD Min.Order Qty: 5 Feet |
| 22493 | Silcosteel-Hydroguard | Tubing 0.085"ID x 1/8"OD Min.Order Qty: 5 Feet |
| 22493 | Silcosteel-Hydroguard | Tubing 0.085"ID x 1/8"OD Min.Order Qty: 5 Feet |
| 22493 | Silcosteel-Hydroguard | Tubing 0.085"ID x 1/8"OD Min.Order Qty: 5 Feet |
| 22494 | Silcosteel-Hydroguard | Tubing, 0.040"ID x 1/16"OD Min.Order Qty: 5 Feet |
| 22494 | Silcosteel-Hydroguard | Tubing, 0.040"ID x 1/16"OD Min.Order Qty: 5 Feet |
| 22494 | Silcosteel-Hydroguard | Tubing, 0.040"ID x 1/16"OD Min.Order Qty: 5 Feet |
| 22494 | Silcosteel-Hydroguard | Tubing, 0.040"ID x 1/16"OD Min.Order Qty: 5 Feet |
| 22495 | Silcosteel-Hydroguard | Tubing, 0.030"ID x 1/16"OD Min.Order Qty: 5 Feet |
| 22495 | Silcosteel-Hydroguard | Tubing, 0.030"ID x 1/16"OD Min.Order Qty: 5 Feet |
| 22495 | Silcosteel-Hydroguard | Tubing, 0.030"ID x 1/16"OD Min.Order Qty: 5 Feet |
| 22495 | Silcosteel-Hydroguard | Tubing, 0.030"ID x 1/16"OD Min.Order Qty: 5 Feet |
| 22496 | Silcosteel-Hydroguard | Tubing, 0.020"ID x 1/16"OD Min.Order Qty: 5 Feet |
| 22496 | Silcosteel-Hydroguard | Tubing, 0.020"ID x 1/16"OD Min.Order Qty: 5 Feet |
| 22496 | Silcosteel-Hydroguard | Tubing, 0.020"ID x 1/16"OD Min.Order Qty: 5 Feet |
| 22496 | Silcosteel-Hydroguard | Tubing, 0.020"ID x 1/16"OD Min.Order Qty: 5 Feet |
| 22497 | Silcosteel-Hydroguard | Tubing, 0.010"ID x 1/16"OD Min.Order Qty: 5 feet |
| 22497 | Silcosteel-Hydroguard | Tubing, 0.010"ID x 1/16"OD Min.Order Qty: 5 feet |
| 22497 | Silcosteel-Hydroguard | Tubing, 0.010"ID x 1/16"OD Min.Order Qty: 5 feet |
| 22497 | Silcosteel-Hydroguard | Tubing, 0.010"ID x 1/16"OD Min.Order Qty: 5 feet |
| 22500 | Tubing, Sulfinert | 0.011" ID, 0.022" OD MXT 5ft Minimum Order Max.Continuous Length 200' |

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034



HROMalytic +61(0)3 9762 2034
ECHnology Pty Ltd

Australian Distributors
Importers & Manufacturers
www.chromtech.net.au

Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA

(Ctrl F)
> Cat.#s

> Current System AUD Prices

