

22603	Purifier Module, Hydrogen	1/8" Fittings	Page 87
22604	Purifier Module, Nitrogen	1/4" Fittings	
22605	Purifier Module, Nitrogen	1/8" Fittings	
22606	Purifier Module, Air	1/4" Fittings	
22607	Purifier Module, Air	1/8" Fittings	
22608	FID Cap. Column Adaptor	for PE AutoSys XL, For Use w/PE Style Cap. Nuts	
22609	FID Cap. Column Adaptor	for PE AutoSys XL, For Use w/ 1/16" Compression Style Nuts	
22610	Silcosteel-CR Fittings	1/16" to 1/8" NPT Male Connector Swagelok# SS-100-1-2	
22611	Silcosteel-CR Fittings	1/8" to 1/4" NPT Male Connector Swagelok# SS-200-1-4	
22612	Silcosteel-CR Fittings	1/4" to 1/8" NPT Male Connector Swagelok# SS-400-1-2	
22613	Silcosteel-CR Fittings	1/8" to 1/8" NPT Female Connector Swagelok# SS-200-7-2	
22614	Silcosteel-CR Fittings	1/4" to 1/4" NPT Female Connector Swagelok# SS-400-7-4	
22615	Silcosteel-CR Fittings	1/4" to 1/8" NPT Female Connector Swagelok# SS-400-7-2	
22616	Silcosteel-CR Fittings	1/8" to 1/4" NPT Female Connector Swagelok# SS-200-7-4	
22617	Silcosteel-CR Fittings	1/8" Bulkhead Union Swagelok# SS-200-61	
22618	Silcosteel-CR Fittings	1/4" Bulkhead Union Swagelok# SS-400-61	
22620	Silcosteel-CR Fittings	1/8" Plug Swagelok# SS-200-P	
22622	Swaging Tool	Swagelok Compression Fitting Tool, 1/4" Compression, For Preset Swagelok Co	
22623	Tee Wrench, Swagelok	1/4" and 6mm Fittings, Compression Fitting Holder	
22624	Inspection Gauge	Swagelok Compression Fitting Inspection Gauge, 1/4" 3/8" 1/2" Compression Fitti	
22627	Inspection Light	Flexible LED Stylus Reach Pen Light	
22656	Restek ProFLOW 6000	Electronic Flowmeter, Battery Powered, 1yr Warranty from Date of Purchase	
22656-R	Recalibration Service	ProFLOW 6000 Electronic Flowmeter, PO & SRV #s Required	
22657	Soft-Side Storage Case	for Leak Detector/Flowmeter	
22658	Leak Detector Accessory	Small Probe Adaptor	
22663	Diffusion Pump Fan Assy.	Discontinue When Stock is Depleted for Agilent 5972 MS	
22664	Weldment, Split/Splitless	for Agilent 6890 GCs (Use with TEKMAR Purge & Traps)	
22665	Weldment, Split/Splitless	for Agilent 6890 GCs (Use with OI Purge & Traps)	
22666	Weldment, Split/Splitless	for Agilent 5890 GCs (Use with TEKMAR Purge & Traps)	
22667	Weldment, Split/Splitless	for Agilent 5890 GCs (Use with OI Purge & Traps)	
22668	Weldment	for Agilent 6890 GCs with optional canister filter (Use with TEKMAR Purge and Tr	
22669	Weldment, Split/Splitless	for Agilent 6890 GCs with optional canister filter (for use with OI Purge and Traps)	
22670	Weldment	Siltek Optional Split/Splitless Weldment For Agilent 6890/6850 GCs, For use with	
22671	Shell Weldment	for Agilent 6890/6850 Siltek	
22672	Split/Splitless Weldment	For Agilent 6890/6850 with EPC, Siltek	
22673	Injector	Replacement Shell Weldment for HP 6890/6850	
22674	Injector	Replacement Split/Splitless Weldment for HP6890/6850 with EPC	
22683	Graphite Ferrule	for Varian 1078/1079 5mm Liner Seal, 10pk	
22684	Ferrule, Graphite	CIS4 and PTV Liner Seal 5pk	
22685	Aluminum Oxide Powder	For Cleaning Mass Spec Parts, 1kg	
22686	Weldment	Agilent 6890/6850 Optional Split/Splitless Weldment for use with Large Canister T	
22687	Pump Oil	Rough Pump Oil for MSD Pumps, Oil Vacuum Pump #19, 1 Liter 12/cs	
22688	Capillary Nut	for Shimadzu 17A, 2010 & 2014 GCs 2pk	
22689	Tool	Replacement Sanding Disks for the Injection Port Repair Tool. 5 fine and 5 Medium	
22690	Regulator	Inlet CGA 160, Outlet 1/4" Female NPT. For use with 14 Liter Scott/Air Liquide Tra	
22691	Regulator	Inlet CGA 165, Outlet 1/4" Female NPT, For use with 48 Liter Scott/Air Liquide Tra	
22692	Autosampler Hardware	Agilent 7673 A/B Motor Belt	
22694	Replacement Cable	Discontinue When Stock is Depleted Agilent 6890 to PC 9F/9F (RS232)	
22695	Autosampler Hardware	Agilent 7673 A/B Autosampler Syringe Pulley Belt	
22697	Versa Vial	Glass, 12x32mm, 2.0mL Amber, 100pk	
22698	Versa Vial	Glass, 12x32mm, 2.0mL Amber, 1000pk	
22699	Versa Vial	Glass, 12x32mm, 2.0mL Amber w/White Graduated Marking Spot, 100pk	
22700	Versa Vial	Glass, 12x32mm, 2.0mL Amber w/White Graduated Marking Spot, 1000pk	
22701	Versa Vial	Glass, 12x32mm, 2.0mL Clear, 100pk	
22702	Versa Vial	Glass, 12x32mm, 2.0mL Clear, 1000pk	
22703	Versa Vial	Glass, 12x32mm, 2.0mL Clear w/White Graduated Marking Spot, 100pk	
22704	Versa Vial	Glass, 12x32mm, 2.0mL Clear w/White Graduated Marking Spot, 1000pk	
22705	Versa Vial, Polypropylene	12x32mm, 1.5mL, 100pk	
22706	Versa Vial, Polypropylene	12x32mm, 1.5mL, 1000pk	
22707	Versa Vial	250uL Glass Insert w/Glass Flange, 100pk	
22709	Versa Vial	250uL Polypropylene Insert w/Flange, 100pk	
22710	Versa Vial	250uL Polypropylene Insert w/Flange, 1000pk	
22711	Versa Vial	250uL Glass Flat Bottom Insert, 100pk	
22712	Versa Vial	250uL Glass Flat Bottom Insert, 1000pk	
22713	Versa Vial	12mm, Green Polyethylene Plug, 100pk	
22714	Versa Vial	12mm, Green Polyethylene Plug, 1000pk	

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034

 HROMalytic +61(0)3 9762 2034 ECHnology Pty Ltd		Australian Distributors Importers & Manufacturers www.chromtech.net.au
Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA		

(Ctrl F)
> Cat.#s

> Current System AUD Prices

