

22715 Versa Vial
22716 Versa Vial
22717 Versa Vial
22718 Versa Vial
22719 Versa Vial
22720 Versa Vial
22721 EZ Twist Top Inj. Port
22722 EZ Twist Top Inj. Port
22723 EZ Twist Top Weldment
22724 EZ Twist Top Weldment
22725 EZ Twist Top Inj. Port
22726 EZ Twist Top Inj. Port
22727 EZ Twist Top Weldment
22728 EZ Twist Top Tool
22729 EZ Twist Top O-Rings
22730 EZ Twist Top Weldment
22731 EZ Twist Top Weldment
22732 EZ Twist Top Weldment
22733 EZ Twist Top Weldment
22734 EZ Twist Top Weldment
22735 EZ Twist Top Inj. Port
22736 EZ Twist Top Inj. Port
22737 Syringe, SGE
22738 Syringe, SGE
22739 Syringe, SGE
22740 Syringe, SGE
22741 Syringe, SGE
22742 Syringe, SGE
22743 Syringe, Hamilton
22744 Syringe, Hamilton
22745 Syringe, Hamilton
22746 Syringe, Hamilton
22747 Syringe, Hamilton
22748 Syringe, Hamilton
22749 Syringe, SGE
22750 Syringe, SGE
22751 Syringe, SGE
22752 Syringe, SGE
22753 Syringe, SGE
22754 Syringe, SGE
22755 Syringe, Hamilton
22756 Syringe, Hamilton
22757 Syringe, Hamilton
22758 Syringe, Hamilton
22759 Syringe, Hamilton
22760 Syringe, Hamilton
22761 Syringe, Hamilton
22762 Syringe, Hamilton
22763 Syringe, Hamilton
22764 Syringe, Hamilton
22765 Syringe, Hamilton
22766 Norm-Ject Plastic Syringe
22767 Norm-Ject Plastic Syringe
22768 Norm-Ject Plastic Syringe
22769 Norm-Ject Plastic Syringe
22770 Norm-Ject Plastic Syringe
22771 Norm-Ject Plastic Syringe
22772 Norm-Ject Plastic Syringe
22773 Norm-Ject Plastic Syringe
22774 Norm-Ject Plastic Syringe
22775 Norm-Ject Plastic Syringe
22776 Norm-Ject Plastic Syringe
22777 Norm-Ject Plastic Syringe
22778 Norm-Ject Plastic Syringe
22779 Merlin Microseal
22780 Merlin Microseal

Page 88
12mm, Gray Chlorobutyl/Siliconized I
12mm, Grey Chlorobutyl/Siliconized F
12mm, White PTFE/Sil Plug 100pk
12mm, White PTFE/Sil Plug 1000pk
12mm, White PTFE/Sil Plug w/Slit, 100pk
12mm, White PTFE/Sil Plug w/Slit, 1000pk
Complete Injection Port for Agilent 6890 GCs DO NOT SHIP TO JAPAN OR GER
Complete Injection Port for Agilent 6890 GCs Siltek Treated DO NOT SHIP TO JA
Replacement Shell Weldment for Agilent 6890 DO NOT SHIP TO JAPAN OR GE
Replacement Weldment for 5890 and 6890 GCs DO NOT SHIP TO JAPAN OR G
Complete Injection Port for Agilent 5890 GCs, DO NOT SHIP TO JAPAN OR GER
Complete Injection Port for Agilent 5890 GCs Siltek Treated DO NOT SHIP TO JA
Replacement Shell Weldment for Agilent 5890 DO NOT SHIP TO JAPAN OR GE
Weldment Tool for Agilent 5890 and 6890 GCs
Small Replacement O-Rings for Weldment, 10pk
Replacement Shell Weldment for Agilent 6890 - Siltek Treated DO NOT SHIP TO
Replacement Shell Weldment for Agilent 5890 - Siltek Treated DO NOT SHIP TO
Siltek Replacement Weldment for Agilent 5890 & 6890 GCs DO NOT SHIP TO JA
Optional Split/Splitless Shell Weldment for Agilent 6890 GCs For Use w/Large Ca
Siltek Treated Optional Split/Splitless Shell Weldment for Agilent 6890 GCs For U
Complete Injection Port w/Optional Split Vent for Agilent 6890 GCs DO NOT SHIF
Siltek Treated Injection Port w/Optional Split Vent for Agilent 6890 GCs DO NOT
Leap/CTC LC Autosampler 10F-CTC-LC, 10uL
Leap/CTC LC Autosampler 25F-C/T-LC, 25uL
Leap/CTC LC Autosampler 25R-C/T-GT-LC, Gas Tight, 25uL
Leap/CTC LC Autosampler 50F-C/T-GT-LC, Gas Tight, 50uL
Leap/CTC LC Autosampler 100R-C/T-GT-LC, Gas Tight, 100uL
Leap/CTC LC Autosampler 500F-CTC-GT-LC(0.41), Gas Tight, 500uL
Leap/CTC LC Autosampler 701N, 10uL
Leap/CTC LC Autosampler 1702N, 25uL
Leap/CTC LC Autosampler 1701N Slim Line, 100uL
Leap/CTC LC Autosampler 1701N, 100uL
Leap/CTC LC Autosampler 1725N, 250uL
Leap/CTC LC Autosampler 1750N, 500uL
10F-C/T-GT-5/0.63C, Gas Tight 10uL/23/50mm/cone
25-C/T-5/0.47C 25uL/26/50mm/cone
25-C/T-GT-5/0.63C, Gas Tight 25uL/23/50mm/cone
25-R-C/T-GT-5/0.47H, Gas Tight, 25uL/26/50mm/s-hole
100F-C/T-GT-5/0.63C, Gas Tight, 100uL/23/50mm/cone
100R-C/T-GT-5/0.47C, Gas Tight, 100uL/26/50mm/cone
7701.2N/1.2uL/26/51mm/AS
75N/5uL/26/51mm/AS
701N/10uL/23s/51mm/AS
701N/10uL/23s-26s/51mm/AS
701N/10uL/23s/51mm/2
701N Slim Line/10uL/26s/51mm/2
701N/10uL/26s/51mm/AS
701N/10uL/26s/51mm/2 6pk
1702N/25uL/26s/51mm/AS Gas Tight
1702N Slim Line/25uL/26s/51mm/AS Gas Tight, 6.7mm Barrel OD
1701N Slim Line/100uL/26s/51mm/AS Gas Tight, 6.7mm Barrel OD
1mL Luer Slip Tuberculin, 100pk
3mL Luer Slip Centric Tip, 100pk
5mL Luer Slip Centric Tip, 100pk
10mL Luer Slip Eccentric Tip, 100pk
20mL Luer Slip Eccentric Tip, 100pk
30mL Luer Slip Eccentric Tip, 50pk
50mL Luer Slip Eccentric Tip, 30pk
3mL Luer Lock Tip 100pk
5mL Luer Lock Tip 100pk
10mL Luer Lock Tip 100pk
20mL Luer Lock Tip 100pk
30mL Luer Lock Tip 50pk
50mL Luer Lock Tip 30pk
Adapter Kit for Varian 1078 and 1079 SPME Systems (nut w/start switch adapter)
Adapter Kit for Varian 1177 SPME System (nut w/start switch, adapter, o-ring, spa

[Ctrl F]
> Cat.#s

> Current System AUD Prices



Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034

**HROMalytic** +61(0)3 9762 2034
ECHnology Pty Ltd
Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA

Australian Distributors
Importers & Manufacturers
www.chromtech.net.au