

22887	Silcosteel-CR, Fitting	1/8" to 1/8" Male NPT Union
22889	Silcosteel-CR, Fitting	1/16" to 1/8" Male NPT Union
22890	Silcosteel-CR, Fitting	1/8" to 1/4" Male NPT Union
22891	Silcosteel-CR, Fitting	1/4" to 1/8" Male NPT Union
22892	Silcosteel-CR, Fitting	1/8" to 1/8" Female NPT Union
22893	Silcosteel-CR, Fitting	1/4" to 1/4" Female NPT Union
22894	Silcosteel-CR, Fitting	1/4" to 1/8" Female NPT Union
22896	Silcosteel-CR Tubing	0.055" ID x 1/8" OD, Seamless 316L Grade, 0.035" Wall min. order qty: 5
22896	Silcosteel-CR Tubing	0.055" ID x 1/8" OD, Seamless 316L Grade, 0.035" Wall min. order qty: 5
22896	Silcosteel-CR Tubing	0.055" ID x 1/8" OD, Seamless 316L Grade, 0.035" Wall min. order qty: 5
22896	Silcosteel-CR Tubing	0.055" ID x 1/8" OD, Seamless 316L Grade, 0.035" Wall min. order qty: 5
22897	Silcosteel-CR Tubing	0.180" ID x 1/4" OD, Seamless 316L Grade, 0.035" Wall min. order qty: 5
22897	Silcosteel-CR Tubing	0.180" ID x 1/4" OD, Seamless 316L Grade, 0.035" Wall min. order qty: 5
22897	Silcosteel-CR Tubing	0.180" ID x 1/4" OD, Seamless 316L Grade, 0.035" Wall min. order qty: 5
22897	Silcosteel-CR Tubing	0.180" ID x 1/4" OD, Seamless 316L Grade, 0.035" Wall min. order qty: 5
22898	Silcosteel-CR Tubing	6' Straight Length, 1/8"OD 0.035" Wall 316L Seamless Treated Internally and Externally
22899	Silcosteel-CR Tubing	6' Straight Length, 1/4"OD 0.035" Wall 316L Seamless Treated Internally and Externally
22900	Silcosteel-CR Tubing	6' Straight Length, 3/8"OD 0.049" Wall 316L Seamless Treated Internally and Externally
22901	Siltek/Sulfinert Tubing	6' Straight Length, 1/8"OD 0.035" Wall 316L Seamless Treated Internally and Externally
22902	Siltek/Sulfinert Tubing	6' Straight Length, 1/4"OD 0.035" Wall 316L Seamless Treated Internally and Externally
22903	Siltek/Sulfinert Tubing	6' Straight Length, 3/8"OD 0.049" Wall 316L Seamless Treated Internally and Externally
22904	Silcosteel-CR Fitting	3/8" Union Silcosteel-CR Treated. Swagelok # SS-600-6
22905	Silcosteel-CR Fitting	3/8" Tee Silcosteel-CR Treated. Swagelok # SS-600-3
22906	Silcosteel-CR Fitting	3/8" to 1/4" Reducing Union. Silcosteel-CR Treated. Swagelok # SS-600-6-4
22907	Silcosteel-CR Fitting	3/8" Tube to 3/8" MNPT Male Connector Silcosteel-CR Treated. Swagelok # SS-600-6
22909	Siltek/Sulfinert Fitting	3/8" Union Siltek/Sulfinert Treated. Swagelok # SS-600-6
22910	Siltek/Sulfinert Fitting	3/8" Tee Siltek/Sulfinert Treated. Swagelok # SS-600-3
22911	Siltek/Sulfinert Fitting	3/8" to 1/4" Reducing Union Siltek/Sulfinert Treated Swagelok # SS-600-6-4
22912	Siltek/Sulfinert Fitting	3/8" Tube to 3/8" MNPT Male Connector Siltek/Sulfinert Treated. Swagelok # SS-600-6
22914	Tubing, Sulfinert/Siltek	3/8" OD x 0.277" ID x 0.049" Seamless 316L Grade SS Siltek/Sulfinert Treated internally
22914	Tubing, Sulfinert/Siltek	3/8" OD x 0.277" ID x 0.049" Seamless 316L Grade SS Siltek/Sulfinert Treated internally
22914	Tubing, Sulfinert/Siltek	3/8" OD x 0.277" ID x 0.049" Seamless 316L Grade SS Siltek/Sulfinert Treated internally
22914	Tubing, Sulfinert/Siltek	3/8" OD x 0.277" ID x 0.049" Seamless 316L Grade SS Siltek/Sulfinert Treated internally
22915	Tubing, Silcosteel-CR	3/8" OD x 0.277" ID x 0.049" Seamless 316L Grade SS Silcosteel-CR Treated
22915	Tubing, Silcosteel-CR	3/8" OD x 0.277" ID x 0.049" Seamless 316L Grade SS Silcosteel-CR Treated
22915	Tubing, Silcosteel-CR	3/8" OD x 0.277" ID x 0.049" Seamless 316L Grade SS Silcosteel-CR Treated
22915	Tubing, Silcosteel-CR	3/8" OD x 0.277" ID x 0.049" Seamless 316L Grade SS Silcosteel-CR Treated
22916	Canister Cleaning System	TO-Clean Oven, Capacity 12 x 6L Canisters, Includes Vacuum Pump 120v, 60Hz
22917	Canister Cleaning System	TO-Clean Oven, Capacity 12 x 6L Canisters, Includes Vacuum Pump 220/230V, 50Hz
22918	Canister Cleaning System	Dewar, Glass, 4300mL SS Tube Traps Domestic Orders Drop Ship from Manufacturer
22919	Canister Cleaning System	Oven Cart, 48 x 30in 12 Gauge Steel, Push Handle and Casters Ships FedEx Ground
22920	Canister Cleaning System	TO-Clean Oven 1L Option Includes Tubing, Fittings, and Inserts for 24-1L Canisters
22921	Sample Cylinder	75cc, 1800psig, 304L, SS 1/4" Female NPT Ends
22921-PI	Sample Cylinder	TPED, 75cc, 1450psig, 304L, SS, 1/4" Female NPT Ends
22922	Sample Cylinder	150cc, 1800psig, 304L, SS 1/4" Female NPT Ends
22922-PI	Sample Cylinder	TPED, 150cc, 1450psig, 304L, SS, 1/4" Female NPT Ends
22923	Sample Cylinder	300cc, 1800psig, 304L, SS 1/4" Female NPT Ends
22923-PI	Sample Cylinder	TPED, 300cc, 1450psig, 304L, SS, 1/4" Female NPT Ends
22924	Sample Cylinder	500cc, 1800psig, 304L, SS 1/4" Female NPT Ends
22924-PI	Sample Cylinder	TPED, 500cc, 1450psig, 304L, SS, 1/4" Female NPT Ends
22925	Sample Cylinder	1000cc, 1800psig, 304L, SS 1/4" Female NPT Ends
22925-PI	Sample Cylinder	TPED, 1000cc, 1450psig, 304L, SS, 1/4" Female NPT Ends
22926	Sample Cylinder	2250cc, 1800psig, 304L, SS 1/4" Female NPT Ends
22926-PI	Sample Cylinder	TPED, 2250cc, 1450psig, 304L, SS, 1/4" Female NPT Ends
22927	Sample Cylinder	150cc, 5000psig, 316L, SS 1/4" Female NPT Ends
22927-PI	Sample Cylinder	TPED, 150cc, 4350psig, 316L, SS, 1/4" Female NPT Ends
22928	Sample Cylinder	300cc, 5000psig, 316L, SS 1/4" Female NPT Ends
22928-PI	Sample Cylinder	TPED, 300cc, 4350psig, 316L, SS, 1/4" Female NPT Ends
22929	Sample Cylinder	500cc, 5000psig, 316L, SS 1/4" Female NPT Ends
22929-PI	Sample Cylinder	TPED, 500cc, 4350psig, 316L, SS, 1/4" Female NPT Ends
22930	Soil Gas Sampling Kit	20 minute, Tee fitting w/0.0065" orifice
22931	Soil Gas Sampling Kit	30 minute, Tee fitting w/0.0055" orifice
22932	Soil Gas Sampling Kit	1 hour, Tee fitting w/0.0040" orifice
22933	Soil Gas Sampling Kit	4 hour, Tee fitting w/0.0020" orifice
22934	Soil Gas Sampling Kit	10 hour, Tee fitting w/0.0014" orifice
22935	Soil Gas Sampling Kit	20 minute, Tee fitting w/0.0065" orifice Siltek treated

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034



HROMalytic +61(0)3 9762 2034

ECHnology Pty Ltd

Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA

Australian Distributors
Importers & Manufacturers
www.chromtech.net.au

(Ctrl F)
> Cat.#s

> Current System AUD Prices

