

22936	Soil Gas Sampling Kit
22937	Soil Gas Sampling Kit
22938	Soil Gas Sampling Kit
22939	Soil Gas Sampling Kit
22940	Soil Gas Sampler
22941	Soil Gas Sampler
22942	Soil Gas Sampler
22943	Soil Gas Sampler
22944	Soil Gas Sampler
22945	Soil Gas Sampler
22946	Soil Gas Sampler
22947	Soil Gas Sampler
22948	Soil Gas Sampler
22949	Soil Gas Sampler
22950	Gas Sampling Bag
22951	Gas Sampling Bag
22952	Gas Sampling Bag
22953	Gas Sampling Bag
22954	PUFs
22955	PUFs
22956	PUFs
22957	PUFs
22958	Gas Sampling Bag
22959	Gas Sampling Bag
22960	Gas Sampling Bag
22961	Gas Sampling Bag
22962	Gas Sampling Bag
22963	Gas Sampling Bag
22964	PUFs
22965	PUFs
22966	Gas Sampling Bag
22967	Gas Sampling Bag
22968	Gas Sampling Bag
22972	Merlin Microseal
22973	Gooseneck Splitless Liner
22973-200.1	Gooseneck Splitless Liner
22973-231.1	Gooseneck Splitless Liner
22974	Gooseneck Splitless Liner
22974-200.5	Gooseneck Splitless Liner
22974-231.5	Gooseneck Splitless Liner
22975	Splitless Liner
22975-200.1	Splitless Liner
22975-231.1	Splitless Liner
22976	Splitless Liner
22976-200.5	Splitless Liner
22976-231.5	Splitless Liner
22979	Drilled Cyclo Uniliner
22979-214.1	Drilled Cyclo Uniliner
22980	Drilled Cyclo Uniliner
22980-214.5	Drilled Cyclo Uniliner
22983	Single Gooseneck
22983-211.1	Single Gooseneck
22983-213.1	Single Gooseneck
22983-214.1	Single Gooseneck
22984	Single Gooseneck
22984-211.5	Single Gooseneck
22984-213.5	Single Gooseneck
22984-231.5	Single Gooseneck
22985	Single Gooseneck
22985-211.25	Single Gooseneck
22985-213.25	Single Gooseneck
22986	Drilled Uniliner Liner
22986-213.1	Drilled Uniliner Liner
22986-214.1	Drilled Uniliner Liner
22986-216.1	Drilled Uniliner Liner
22987	Drilled Uniliner Liner

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034

 HROMalytic +61(0)3 9762 2034 ECHnology Pty Ltd		Australian Distributors Importers & Manufacturers www.chromtech.net.au
Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . IN AUSTRALIA		

Page 91

30 minute, Tee fitting w/0.0055" orifice
1 hour, Tee fitting w/0.0040" orifice
4 hour, Tee fitting w/0.0020" orifice
10 hour, Tee fitting w/0.0014" orifice
20 minute, Tee Fitting w/0.0065" orifice
30 minute, Tee Fitting w/0.0055" orifice
1 hour, Tee Fitting w/0.0040" orifice
4 hour, Tee Fitting w/0.0020" orifice
10 hour, Tee Fitting w/0.0014" orifice
20 minute, Tee Fitting w/0.0065" orifice
30 minute, Tee Fitting w/0.0055" orifice
1 hour, Tee Fitting w/0.0040" orifice
4 hour, Tee Fitting w/0.0020" orifice
10 hour, Tee Fitting w/0.0014" orifice
Multi-Layer Foil, 1L, 7" x 7" w/polypropylene combo valve & septum, 1 eyelet, 5-pk
Multi-Layer Foil, 3L, 10" x 10" w/polypropylene combo valve & septum, 1 eyelet, 5-pk
Multi-Layer Foil, 5L, 12" x 12" w/polypropylene combo valve & septum, 1 eyelet, 5-pk
Multi-Layer Foil, 10L, 12" x 22" w/polypropylene combo valve & septum, 1 eyelet, 5-pk
Large PUF plug, unwashed, 6cm OD x 7.6cm L, 10-pk
Large PUF plug, unwashed, 6cm OD x 5.1cm L, 10-pk
Large PUF plug, unwashed, 6cm OD x 2.5cm L, 10-pk
Small PUF plug, unwashed, 22mm OD x 7.6cm L, 10-pk
ALTEF, 0.5L, 6"x6" w/polypropylene combo valve & septum, 1 eyelet, 10-pk
ALTEF, 1L, 7"x7" w/polypropylene combo valve & septum, 1 eyelet, 10-pk
ALTEF, 3L, 10"x10" w/polypropylene combo valve & septum, 1 eyelet, 10-pk
ALTEF, 5L, 12"x12" w/polypropylene combo valve & septum, 1 eyelet, 10-pk
ALTEF, 10L, 12"x22" w/polypropylene combo valve & septum, 1 eyelet, 10-pk
ALTEF, 25L, 18"x24" w/polypropylene combo valve & septum, 1 eyelet, 5-pk
Large PUF Glass Holder Fits 6cm OD PUF Plug
Small PUF Glass Holder Fits 22mm OD PUF Plug
Multi-Layer Foil, 12L, 13" x 24" w/ polypropylene combo valve & septum, 1 eyelet, 5-pk
Multi-Layer Foil, 25L, 18" x 24" w/polypropylene combo valve & septum, 1 eyelet, 5-pk
Multi-Layer Foil, 40L, 24" x 24.5" w/polypropylene combo valve & septum, 1 eyelet, 5-pk
for Shimadzu GC-2010 and GC-2025, Includes: Nut, Adapter, and 2 Septum
5.0mm x 6.5 x 78.5 for Agilent GCs IP Deact., ea
5.0mm x 6.5 x 78.5 for Agilent GCs IP Deact., w/Deact Wool, ea
5.0mm x 6.5 x 78.5 for Agilent GCs IP Deact., w/ SV Wool, Ea
5.0mm x 6.5 x 78.5 for Agilent GCs IP Deact., 5-pk
5.0mm x 6.5 x 78.5 for Agilent GCs IP Deact., w/ Deact. Wool, 5pk
5.0mm x 6.5 x 78.5 for Agilent GCs IP Deact., w/ SV Wool, 5pk
5.0mm x 6.5 x 78.5 for Agilent GCs IP Deact., ea
5.0mm x 6.5 x 78.5 for Agilent GCs IP Deact., w/Deact. Wool, ea
5.0mm x 6.5 x 78.5 for Agilent GCs IP Deact., SV Wool, Ea
5.0mm x 6.5 x 78.5 for Agilent GCs IP Deact., 5-pk
5.0mm x 6.5 x 78.5 for Agilent GCs IP Deact.,w/Deact. Wool, 5-pk
5.0mm x 6.5 x 78.5 for Agilent GCs IP Deact., w/ SV Wool, 5pk
Hole near Top, 4.0mm x 6.3 x 78.5 For Agilent GCs, IP Deact., ea
Hole near Top, 4.0mm x 6.3 x 78.5 For Agilent GCs, Siltek Deact., ea
Hole near Top, 4.0mm x 6.3 x 78.5 For Agilent GCs, IP Deact., 5-pk
Hole Near Top, 4.0mm x 6.3 x 78.5 for Agilent GCs, Siltek Deact., 5-pk
Precision Liner, 4.0mm x 6.3 x 78.5 for Agilent GCs IP Deact., w/Deact. Wool, ea
Precision Liner, 4.0mm x 6.3 x 78.5 for Agilent GCs Base Deact., w/Base Wool, ea
Precision Liner, 4.0mm x 6.3 x 78.5, for Agilent GCs Siltek Deact., w/ Deact. Wool
Precision Liner, 4.0mm x 6.3 x 78.5 for Agilent GC's Siltek Deact., ea
Precision Liner, 4.0mm x 6.3 x 78.5 for Agilent GCs IP Deact., w/Deact. Wool, 5pk
Precision Liner, 4.0mm x 6.3 x 78.5 For Agilent GCs, Base Deact., Base Wool, 5p
Precision Liner, 4.0mm x 6.3 x 78.5 for Agilent GCs Siltek Deact., w/Deact Wool, 5pk
Precision Liner, 4.0mm x 6.3 x 78.5 For Agilent GCs, IP Deact., SV Wool, 5pk
Precision Liner, 4.0mm x 6.3 x 78.5 for Agilent GCs IP Deact., w/Deact. Wool, 25pk
Precision Liner, 4.0mm x 6.3 x 78.5, For Agilent GCs Base Deact., Base Wool, 25pk
Precision Liner, 4.0mm x 6.3 x 78.5 for Agilent GCs, Siltek Deact. w/ Deact. Wool, 5pk
Hole on Top, 2.0mm x 4.0 x 86.2 for PE PSS Inlets, IP Deact., ea
Hole on Top, 2.0mm x 4.0 x 86.2 for PE PSS Inlets, Siltek Deact. w/ Deact. Wool, 5pk
Hole on Top, 2.0mm x 4.0 x 86.2 for PE PSS Inlets, Siltek Deact., ea
Hole on Top, 2.0mm x 4.0 x 86.2 for PE PSS Inlets, Siltek Deact., w/ Carbofrit, Ea
Hole on Top, 2.0mm x 4.0 x 86.2 for PE PSS Inlets, IP Deact., 5pk

(Ctrl F)
> Cat.#s

> Current System AUD Prices

