

22987-202.5	Drilled Uniliner Liner
22987-213.5	Drilled Uniliner Liner
22987-214.5	Drilled Uniliner Liner
22987-216.5	Drilled Uniliner Liner
22988	Drilled Uniliner Liner
22988-214.1	Drilled Uniliner Liner
22989	Drilled Uniliner Liner
22990	Zero Dilution Inner Liner
22991	Zero Dilution Inner Liner
22991-214.5	Zero Dilution Inner Liner
22992	Zero Dilution Outer Liner
22992-214.1	Zero Dilution Outer Liner
22993	Zero Dilution Outer Liner
22994	Oven Flapper Assembly
22995	Oven Flapper Assembly
22996	Gasket and Hardware Kit
22997	Metric Wrench Set
22998	Hex Key Set
22999	Hex Key Set
23001	Tool Set
23002	Tool
23004	Tool Set
23009	Tool
23010	FID Collector Assembly
23011	Tool
23012	Tool
23015	Tool
23016	Re-threading Tool
23017	Re-threading Tool
23018	Re-threading Tool
23019	Re-threading Tool
23020	PID Lamp
23026	Shortix Cutter
23027	Shortix Cutter
23029	Tool
23030	Tool
23031	Split Vent Trap Assembly
23032	Replacement Trap
23033	Plier Set
23034	Torx Screwdriver Kit
23035	PRT Sensor
23036	Collector Mount
23037	Collector Housing
23038	FID Jet
23039	Oven Temperature Sensor
23040	Oven Temperature Sensor
23041	Base Weldment
23042	Retaining Nut
23043	FID Collector Mount
23044	FID Collector Housing
23045	FID Collector Housing
23046	Sure Fit Injection Port
23047	Sure Fit Weldment
23048	Sure Fit Shell Weldment
23049	Sure Fit Injection Port
23050	Sure Fit Shell Weldment
23051	Sure Fit Weldment
23052	Base Weldment
23053	Base Weldment
23057	Silver Seal
23058	Silver Seal
23061	Auto-ignite FID
23062	Nozzle Insulator
23063	FID Body
23064	Replacement Washer
23065	Generator, Hydrogen

Page 92
Hole on Top, 2.0mm x 4.0 x 86.2 for F
Hole on Top, 2.0mm x 4.0 x 86.2 for F
Hole on Top, 2.0mm x 4.0 x 86.2 for F
Hole on Top, 2.0mm x 4.0 x 86.2 for PE PSS Inlets, Siltek Deact. w/ Carbofrit, 5pk
Hole on Bottom, 2.0mm x 4.0 x 86.2 for PE PSS Inlets, IP Deact., ea
Hole on Bottom, 2.0mm x 4.0 x 86.2 for PE PSS Inlets, Siltek Deact., ea
Hole on Bottom, 2.0mm x 4.0 x 86.2 for PE PSS Inlets, IP Deact., 5pk
1mm x 2 x 73 for PE GCs IP Deact., ea
1mm x 2 x 73 for PE GCs IP Deact., 5pk
1mm x 2 x 73 for PE GCs Siltek Deact., 5pk
2.5mm x 6.2 x 90 for PE GCs IP Deact., ea
2.5mm x 6.2 x 90 for PE GCs Siltek Deact., Ea
2.5mm x 6.2 x 90 for PE GCs IP Deact., 5pk
For Agilent 5890 GCs
For Agilent 6890 GCs
Replacement Kit for Oven Flapper Assembly, Agilent 5890/6890
3pk, 6x7mm, 8x10mm, 16x17mm Double Open End Wrenches
Std Inch, 12 Piece Ball-Point w/Plastic Indexed Caddy
Metric, 9 Piece Ball-Point w/Plastic Indexed Caddy
Wrench, Adjustable Set
Screwdriver, 5 in 1 Magnetic
54 Piece Tool Set
IMP Triple Head Tubing Bender
Kit for HP 5890 FID
Rigid Tubing Cutter for 1/8" or 1/4" Metal Tubing
Rigid Tubing Cutter Replacement Wheels Pack of 2
Scoring Wafer with Handle, 2pk
for 1/16" Compression Fittings
for 1/8" Compression Fittings
for 1/4" Compression Fittings and Agilent Injectors
7/16", for Varian Injection Ports
Model 108-BTEX
Capillary GC Column Cutter for 0.25mm to 0.53mm OD Capillary Tubing
Maintenance Kit
SSI Tubing Cutter Machine 110-120/220-240 Volts
SSI Replacement Cutting Wheels for use with Catalog #23029, 3pk
Optional Split Vent Trap Assembly for Agilent 6890/6850 GCs
for use with the Optional Split Vent Trap Assembly (#23031) (2 Traps/4 O-rings)
Side Cutter, Wire Cutter, and Pliers 3 Piece Set
Pack of 3
for Agilent 5890 GCs. For Use w/Split/Splitless Injection Ports & FIDs
for Agilent 5890 FID
for Agilent 5890 FID
for PE Autosys XL and Clarus 500
for Agilent 6890 GC
for Agilent 5890 GC
for Agilent 5890 FID.
Heater Block Retaining Nut for Agilent 6850/6890 GCs
for use with Agilent 6890 GCs
for Agilent 6890 GCs (Collector Housing Only)
and Mount for Agilent 6890 GCs
Siltek Split/Splitless Kit for Agilent 6890 GCs, Uses Resteks Enhanced Base Fittin
Siltek Split/Splitless Weldment for Agilent 6890 GCs
Siltek, for Agilent 6890 GCs, Uses Resteks Enhanced Base Fitting
Siltek Split/Splitless Kit for Agilent 6890 GCs, Uses Std Agilent Inlet Seals
Siltek, for Agilent 6890 GCs, Uses Std Agilent Inlet Seals
Siltek Optional Split/Splitless Weldment for Agilent 6890 GCs
Pack Column FID, for use with Agilent 6890 GCs
Capillary Column FID, for use with Agilent 6890 GCs
for Thermo Split/Splitless Injector, 10pk
for Thermo Split/Splitless Injector, 20pk
Replacement Part Kit for PE AutoSys XL and Clarus 500 GCs
for Auto-Ignite FID, PE AutoSys XL and Clarus 500 GCs
for Auto-Ignite Flame Ionization Detector. For PE AutoSystem XL and Clarus 500C
Silicone Washer for FID Collector Housing, 12pk, Agilent 5890/6890 GCs
PEM Model, H2PEM-100, 100cc/min Generating Capacity, 24mo. Warranty from I

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034



HROMalytic +61(0)3 9762 2034

ECHnology Pty Ltd

Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA

Australian Distributors
Importers & Manufacturers
www.chromtech.net.au

