

23066 Generator, Hydrogen
 23067 Generator, Hydrogen
 23068 Generator, Hydrogen
 23069 Desiccant Cartridge
 23070 6 Month Maintenance Kit
 23071 24 Month Maintenance Kit
 23072 ETP Electron Multiplier
 23073 ETP Electron Multiplier
 23074 ETP Electron Multiplier
 23075 ETP Electron Multiplier
 23077 ETP Electron Multiplier
 23078 FID Jet
 23079 FID Jet
 23080 FID Jet
 23081 ETP Electron Multiplier
 23082 Headspace Vials
 23083 Headspace Vials
 23084 Headspace Vials
 23085 Headspace Vials
 23086 Headspace Vials
 23086-222 Headspace Vials
 23087 Headspace Vials
 23087-223 Headspace Vials
 23088 Headspace Vials
 23088-222 Headspace Vials
 23089 Headspace Vials
 23090 Headspace Vial Caps
 23091 Headspace Vial Caps
 23092 Headspace Vial Caps
 23093 Headspace Vial Caps
 23094 Headspace Vial Caps
 23095 Headspace Vial Caps
 23100 Swagelok Fitting, Brass
 23101 Swagelok Fitting, Brass
 23102 Swagelok Fitting, Brass
 23103 Swagelok Fitting, Brass
 23104 Swagelok Fitting, Brass
 23105 Swagelok Fitting, Brass
 23106 Swagelok Fitting, Brass
 23107 Swagelok Fitting, Brass
 23108 Swagelok Fitting, Brass
 23109 Swagelok Fitting, Brass
 23110 Swagelok Fitting, Brass
 23111 Swagelok Fitting, Brass
 23112 Swagelok Fitting, Brass
 23113 Swagelok Fitting, Brass
 23114 Swagelok Fitting, Brass
 23115 Swagelok Fitting, Brass
 23116 Swagelok Fitting, Brass
 23117 Swagelok Fitting, Brass
 23118 Swagelok Fitting, Brass
 23119 Swagelok Fitting, Brass
 23120 Swagelok Fitting, Brass
 23121 Swagelok Fitting, Brass
 23122 Swagelok Fitting, Brass
 23123 Swagelok Fitting, Brass
 23124 Swagelok Fitting, Brass
 23125 Swagelok Fitting, Brass
 23126 Swagelok Fitting, Brass
 23127 Swagelok Fitting, Brass
 23128 Swagelok Fitting, Brass
 23129 Swagelok Fitting, Brass
 23130 Swagelok Fitting, Brass
 23131 Swagelok Fitting, Brass
 23132 Swagelok Fitting, Brass
 23133 Swagelok Fitting, Brass

Page 93
 PEM Model, H2PEM-165, 165 cc/min
 PEM Model, H2PEM-260, 260 cc/min
 PEM Model, H2PEM-510, 510 cc/min
 Replacement, for H2 PEM Generators
 for H2 PEM Generators, Kit Includes: 1 Deionizer Cartridge, 1 Water Filter, 3 Envi
 for H2 PEM Generators, Includes: 1 Deionizer Cartridge, 1 Water Filter, 3 Environ
 For Agilent 5970 GC-MS
 For Agilent 5971, 5972, GCD GC-MS
 For Agilent 5973 and 5975 GC-MS, Includes Mount for Installation
 For Agilent 5973 and 5975 GC-MS and LC-MSD Replacement Multiplier
 Discontinue When Stock is Depleted For API300, 3000, and 4000 Applied Biosyst
 High Temp, Capillary Dedicated for Agilent 5890/6890/6850 GCs, EA, (0.018" ID 1
 High Temp, Capillary Dedicated for Agilent 5890/6890/6850 GCs, 3pk, (0.018" ID
 for Thermo Scientific Trace and Focus GCs
 for Thermo Finnigan Trace DSQ, DSQ II and Polaris G GC/MS
 20mL (22x75) Screw Thread, Clear Glass, 100-pk Rounded Bottom
 20mL (22x75) Screw Thread, Clear Glass, 1000-pk Rounded Bottom
 10mL (22x45) Screw Thread, Clear Glass, 100-pk Rounded Bottom
 10mL (22x45) Screw Thread, Clear Glass, 1000-pk Rounded Bottom
 20mL (22x75) Screw Thread, Amber Glass, 100-pk Rounded Bottom
 20mL (22x75) Screw Thread, Amber Glass, 100-pk, Siltek Deact.
 20mL (22x75) Screw Thread, Amber Glass, 1000-pk Rounded Bottom
 20mL (22x75) Screw Thread, Amber Glass, 1000pk Siltek Deact.
 10mL (22x45) Screw Thread, Amber Glass, 100-pk Rounded Bottom
 10mL (22x45) Screw Thread, Amber Glass, 100pk, Siltek Deact.
 10mL (22x45) Screw Thread, Amber Glass, 1000-pk Rounded Bottom
 18mm Magnetic Screw Thread Cap with PTFE/Silicone 100-pk
 18mm Magnetic Screw Thread Cap with PTFE/Silicone 1000-pk
 18mm Magnetic Screw Thread Cap with PTFE/Silicone for SPME, 100-pk
 18mm Magnetic Screw Thread Cap with PTFE/Silicone for SPME, 1000-pk
 18mm Magnetic Screw Thread Cap with PTFE/Red Chlorobutyl, 100-pk
 18mm Magnetic Screw Thread Cap with PTFE/Red Chlorobutyl, 1000-pk
 1/16" Nut, 20-pk
 1/8" Nut, 40-pk
 1/4" Nut, 40-pk
 1/16" Front Ferrule, 20-pk
 1/8" Front Ferrule, 40-pk
 1/4" Front Ferrule, 40-pk
 1/16" Back Ferrule, 20-pk
 1/8" Back Ferrule, 40-pk
 1/4" Back Ferrule, 40-pk
 1/16" Nut and Ferrule Set, 10-pk
 1/8" Nut and Ferrule Set, 20-pk
 1/4" Nut and Ferrule Set, 20-pk
 1/16" Plug, 5-pk
 1/8" Plug, 10-pk
 1/4" Plug, 10-pk
 1/16" Union, 3-pk
 1/8" Union, 5-pk
 1/4" Union, 5-pk
 1/8" to 1/16" Reducing Union, 5-pk
 1/4" to 1/16" Reducing Union, 5-pk
 1/4" to 1/8" Reducing Union, 5-pk
 1/16" Tee, 2-pk
 1/8" Tee, 2-pk
 1/4" Tee, 2-pk
 1/8" Cross, 2-pk
 1/4" Cross, 2-pk
 1/8" to 1/16" Tube End Reducer, 5-pk
 1/4" to 1/16" Tube End Reducer, 5-pk
 1/8" to 1/4" Tube End Reducer, 5-pk
 1/4" to 1/8" Tube End Reducer, 5-pk
 1/8" Port Connector, 5-pk
 1/4" Port Connector, 10-pk
 1/8" to 1/4" Port Connector, 5-pk
 1/8" to 1/8" NPT Male Connector, 10-pk

