

23200	Swagelok Valve
23201	Swagelok Valve
23202	Swagelok Valve
23203	Swagelok Valve
23204	Swagelok Valve
23205	Swagelok Valve
23206	Swagelok Vernier Knob
23207	Swagelok Fitting
23208	Swagelok Repl. O-ring
23209	Swagelok Fitting, Siltek
23210	Swagelok Fitting
23211	Swagelok Fitting, Siltek
23212	Swagelok Fitting
23213	Swagelok Fitting
23214	Swagelok Fitting
23215	Swagelok Fitting
23216	Swagelok Fitting, Siltek
23300.1	SKY Liner
23300.25	SKY Liner
23300.5	SKY Liner
23301.1	SKY Liner, Splitless
23301.25	SKY Liner, Splitless
23301.5	SKY Liner, Splitless
23302.1	SKY Liner, Splitless
23302.25	SKY Liner, Splitless
23302.5	SKY Liner, Splitless
23303.1	SKY Liner, Splitless
23303.25	SKY Liner, Splitless
23303.5	SKY Liner, Splitless
23305.1	SKY Liner, Split
23305.25	SKY Liner, Split
23305.5	SKY Liner, Split
23306.1	SKY Liner
23306.5	SKY Liner
23307.1	SKY Liner
23307.5	SKY Liner
23308.1	SKY Liner, Splitless
23308.25	SKY Liner, Splitless
23308.5	SKY Liner, Splitless
23309.1	SKY Liner
23309.5	SKY Liner
23310.1	SKY Liner
23310.25	SKY Liner
23310.5	SKY Liner
23311.1	SKY Liner
23311.25	SKY Liner
23311.5	SKY Liner
23312.1	SKY Liner
23312.25	SKY Liner
23312.5	SKY Liner
23313.1	SKY Liner, Splitless
23313.25	SKY Liner, Splitless
23313.5	SKY Liner, Splitless
23314.1	SKY Liner, Splitless
23314.25	SKY Liner, Splitless
23314.5	SKY Liner, Splitless
23315.1	SKY Liner, Splitless
23315.25	SKY Liner, Splitless
23315.5	SKY Liner, Splitless
23316.1	SKY Liner, Splitless
23316.25	SKY Liner, Splitless
23316.5	SKY Liner, Splitless
23317.1	SKY Liner
23317.25	SKY Liner
23317.5	SKY Liner
23318.1	SKY Liner, Split

1/8" Stainless Steel Ball
1/4" Stainless Steel Ball
1/8" Stainless Steel Plug
1/4" Stainless Steel Plug
1/8" Stainless Steel Straight
1/4" Stainless Steel Straight
for Metering Valves
Stainless Steel 1/4" VCO to 1/4" Tube Adapter, 2-pk
70 Durometer Fluorocarbon FKM, VCO 1/4", Size 010 10-pk
1/4" VCO to 1/4" Tube Adapter
Stainless Steel 1/4" VCO to 1/4" Tube Fitting, 2-pk
1/4" VCO to 1/4" Tube Fitting
Stainless Steel 1/4" VCO Nut 2-pk
Stainless Steel 1/4" VCO Nut Blind, 2-pk
Stainless Steel 1/4" VCO Body Blind, 2-pk
Stainless Steel 1/4" VCO to 1/8" Tube Fitting, 2-pk
1/4" VCO to 1/8" Tube Fitting
Split/Splitless Straight w/Wool 4mm x 6.3 x 78.5 for Agilent GCs ea
Split/Splitless Straight w/Wool 4mm x 6.3 x 78.5 for Agilent GCs 25-pk
Split/Splitless Straight w/Wool 4mm x 6.3 x 78.5 for Agilent GCs 5-pk
Straight 4mm x 6.3 x 78.5 for Agilent GCs ea
Straight 4mm x 6.3 x 78.5 for Agilent GCs 25-pk
Straight 4mm x 6.3 x 78.5 for Agilent GCs 5-pk
Single Taper Gooseneck 4mm x 6.5 x 78.5 for Agilent GCs ea
Single Taper Gooseneck 4mm x 6.5 x 78.5 for Agilent GCs 25-pk
Single Taper Gooseneck 4mm x 6.5 x 78.5 for Agilent GCs 5-pk
Single Taper Gooseneck w/Wool 4mm x 6.5 x 78.5 for Agilent GCs ea
Single Taper Gooseneck w/Wool 4mm x 6.5 x 78.5 for Agilent GCs 25-pk
Single Taper Gooseneck w/Wool 4mm x 6.5 x 78.5 for Agilent GCs 5-pk
Precision Liner w/Wool 4mm x 6.3 x 78.5 for Agilent GCs ea
Precision Liner w/Wool 4mm x 6.3 x 78.5 for Agilent GCs 25-pk
Precision Liner w/Wool 4mm x 6.3 x 78.5 for Agilent GCs 5-pk
Drilled Uniliner, hole near bottom 4mm x 6.3 x 78.5 for Agilent GCs ea
Drilled Uniliner, hole near bottom 4mm x 6.3 x 78.5 for Agilent GCs 5-pk
Drilled Uniliner, hole near bottom 4mm x 6.3 x 78.5 for Agilent GCs w/Wool, ea
Drilled Uniliner, hole near bottom 4mm x 6.3 x 78.5 for Agilent GCs w/Wool, 5-pk
Double Taper Gooseneck 4mm x 6.5 x 78.5 for Agilent GCs ea
Double Taper Gooseneck 4mm x 6.5 x 78.5 for Agilent GCs 25-pk
Double Taper Gooseneck 4mm x 6.5 x 78.5 for Agilent GCs 5-pk
Low Pressure Drop Precision Liner w/Wool 4mm x 6.3 x 78.5 for Agilent GCs ea
Low Pressure Drop Precision Liner w/Wool 4mm x 6.3 x 78.5 for Agilent GCs 5-pk
Cyclo Double Taper Gooseneck 4mm x 6.5 x 78.5 for Agilent GCs ea
Cyclo Double Taper Gooseneck 4mm x 6.5 x 78.5 for Agilent GCs 25-pk
Cyclo Double Taper Gooseneck 4mm x 6.5 x 78.5 for Agilent GCs 5-pk
Drilled Uniliner, hole near top 4mm x 6.3 x 78.5 for Agilent GCs ea
Drilled Uniliner, hole near top 4mm x 6.3 x 78.5 for Agilent GCs 25-pk
Drilled Uniliner, hole near top 4mm x 6.3 x 78.5 for Agilent GCs 5-pk
Cyclosplitter 4mm x 6.3 x 78.5 for Agilent GCs ea
Cyclosplitter 4mm x 6.3 x 78.5 for Agilent GCs 25-pk
Cyclosplitter 4mm x 6.3 x 78.5 for Agilent GCs 5-pk
2mm x 6.5 x 78.5 for Agilent GCs ea
2mm x 6.5 x 78.5 for Agilent GCs 25-pk
2mm x 6.5 x 78.5 for Agilent GCs 5-pk
2mm x 6.5 x 78.5 for Agilent GCs w/Wool, ea
2mm x 6.5 x 78.5 for Agilent GCs w/Wool, 25-pk
2mm x 6.5 x 78.5 for Agilent GCs w/Wool, 5-pk
Single Taper Gooseneck 2mm x 6.5 x 78.5 for Agilent GCs ea
Single Taper Gooseneck 2mm x 6.5 x 78.5 for Agilent GCs 25-pk
Single Taper Gooseneck 2mm x 6.5 x 78.5 for Agilent GCs 5-pk
Single Taper Gooseneck w/Wool 2mm x 6.5 x 78.5 for Agilent GCs ea
Single Taper Gooseneck w/Wool 2mm x 6.5 x 78.5 for Agilent GCs 25-pk
Single Taper Gooseneck w/Wool 2mm x 6.5 x 78.5 for Agilent GCs 5-pk
Split/Splitless w/Wool 2mm x 4.0 x 86.2 for PE GCs ea
Split/Splitless w/Wool 2mm x 4.0 x 86.2 For PE GCs 25-pk
Split/Splitless w/Wool 2mm x 4.0 x 86.2 for PE GCs 5-pk
3.5mm x 5.0 x 95 for Shimadzu GCs ea

[Ctrl F]  
> Cat.#s

> Current System AUD Prices



Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034

**HROMalytic** +61(0)3 9762 2034

**ECHnology** Pty Ltd

Website NEW : [www.chromalytic.net.au](http://www.chromalytic.net.au) E-mail : [info@chromtech.net.au](mailto:info@chromtech.net.au) Tel: 03 9762 2034 . . . in AUSTRALIA

**Australian Distributors**  
Importers & Manufacturers  
[www.chromtech.net.au](http://www.chromtech.net.au)