

23365	100mL Volumetric Flask
23366	200mL Volumetric Flask
23367	250mL Volumetric Flask
23368	500mL Volumetric Flask
23369	1000mL Volumetric Flask
23370	Micro Volumetric Flask
23372	Micro Volumetric Flask
23373	Micro Volumetric Flask
23374	Micro Volumetric Flask
23375	Micro Volumetric Flask
23376	Micro Volumetric Flask
23377	25mL Auto-Zero Buret
23378	50mL Auto-Zero Buret
23379	Squeeze-O-Matic Buret
23380	Squeeze-O-Matic Buret
23381	30mL Separatory Funnel
23382	60mL Separatory Funnel
23383	125mL Separatory Funnel
23384	250mL Separatory Funnel
23385	500mL Separatory Funnel
23386	1000mL Separatory Funnel
23387	2000mL Separatory Funnel
23388	30mL Gas Impinger
23389	30mL Gas Impinger
23390	1mL Repeating Pipet
23391	5mL Repeating Pipet
23392	10mL Repeating Pipet
23394	20mL Repeating Pipet
23395	25mL Repeating Pipet
23396	11mm Crimper
23397	11mm Decapper
23398	20mm Crimper
23399	20mm Decapper
23400	Double Cylinder Holder
23401	Triple Cylinder Holder
23402	Four Cylinder Holder
23403	O-rings, High Temp
23404	O-rings, High Temp
23405	O-rings, High Temp
23406	Flip Seal Kit
23407	Gold-Plated Flip Seal
23408	Siltek Flip Seal
23409	Gold-Plated Flip Seal
23410	Siltek Flip Seal
23411	Gold-Plated Flip Seal
23412	Siltek Flip Seal
23413	Gold-Plated Flip Seal
23414	Siltek Flip Seal
23415	Gold Plated Inlet Seals
23416	Siltek Inlet Seals
23417	SS Inlet Seals
23418	Gold Plated Inlet Seals
23419	Siltek Inlet Seals
23420	SS Inlet Seals
23950	Filter Vials
23951	Filter Vials
23952	Filter Vials
23953	Filter Vials
23954	Filter Vials
23955	Filter Vials
23956	Filter Vials
23957	Filter Vials
23958	Filter Vials
23959	Filter Vials
23960	Filter Vials
23961	Filter Vials

Class A, w/Stopper Domestic Orders
Class A, w/Stopper Domestic Orders
Class A, w/Stopper Domestic Orders
Class A, w/Stopper Domestic Orders Drop Ship from Tech Glass
Class A, w/Stopper Domestic Orders Drop Ship from Tech Glass
1mL, Class A, w/Stopper Domestic Orders Drop Ship from Tech Glass
2mL, Class A, w/Stopper Domestic Orders Drop Ship from Tech Glass
5mL, Class A, w/Stopper Domestic Orders Drop Ship from Tech Glass
10mL, Class A, w/Stopper Domestic Orders Drop Ship from Tech Glass
25mL, Class A, w/Stopper Domestic Orders Drop Ship from Tech Glass
50mL, Class A, w/Stopper Domestic Orders Drop Ship from Tech Glass
w/Reservoir, Class A, Teflon Stopcock Domestic Orders Drop Ship from Tech Gla
w/Reservoir, Class A, Teflon Stopcock Domestic Orders Drop Ship from Tech Gla
10mL, w/Poly Bottle, Teflon Plug, White Domestic Orders Drop Ship from Tech Gl
25mL, w/Poly Bottle, Teflon Plug, White Domestic Orders Drop Ship from Tech Gl
Squibb Type, Teflon Stopcock Domestic Orders Drop Ship from Tech Glass
Squibb Type, Teflon Stopcock Domestic Orders Drop Ship from Tech Glass
Squibb Type, Teflon Stopcock Domestic Orders Drop Ship from Tech Glass
Squibb Type, Teflon Stopcock Domestic Orders Drop Ship from Tech Glass
Squibb Type, Teflon Stopcock Domestic Orders Drop Ship from Tech Glass
Squibb Type, Teflon Stopcock Domestic Orders Drop Ship from Tech Glass
Complete w/Fritted Tube Domestic Orders Drop Ship from Tech Glass
Complete w/Dispersion Tube Domestic Orders Drop Ship from Tech Glass
Complete Domestic Orders Drop Ship from Tech Glass
Complete Domestic Orders Drop Ship from Tech Glass
Complete Domestic Orders Drop Ship from Tech Glass
Complete Domestic Orders Drop Ship from Tech Glass
Hand Operated
Hand Operated
Hand Operated
Hand Operated
Wall-Mounted
Wall-Mounted
Wall-Mounted
Fits Split (6.3mm OD) or Splitless (6.5mm OD) Liners 10-pk
Fits Split (6.3mm OD) or Splitless (6.5mm OD) Liners 25-pk
for use w/EZ Twist Top Injection Port Weldment 10-pk
Includes Adaptor and 0.8mm ID Gold Plated DVR Inlet Seal
0.8mm ID DVR Inlet Seal, 2-pk
0.8mm ID DVR Inlet Seal, 2-pk
0.8mm ID DVR Inlet Seal, 10-pk
0.8mm ID DVR Inlet Seal, 10-pk
1.2mm ID DVR Inlet Seal, 2-pk
1.2mm ID DVR Inlet Seal, 2-pk
1.2mm ID DVR Inlet Seal, 10-pk
1.2mm ID DVR Inlet Seal, 10-pk
0.8mmID, for HP GCs, 50-pk
0.8mmID, for HP GCs, 50-pk
0.8mmID, for HP GCs, 50-pk
Dual Vespel Ring, 0.8mmID, for HP GCs, 50-pk
Dual Vespel Ring, 0.8mmID, for HP GCs, 50-pk
Dual Vespel Ring, 0.8mmID, for HP GCs, 50-pk
0.2um Nylon w/pre-slit cap, 200-pk, Thomson SINGLE StEP, Black Cap
0.2um Nylon w/pre-slit cap, 500-pk, Thomson SINGLE StEP, Black Cap
0.45um Nylon w/pre-slit cap, 200-pk, Thomson SINGLE StEP, Pink Cap
0.45um Nylon w/pre-slit cap, 500-pk, Thomson SINGLE StEP, Pink Cap
0.2um PTFE w/pre-slit cap, 200-pk, Thomson SINGLE StEP, Green Cap
0.2um PTFE w/pre-slit cap, 500-pk, Thomson SINGLE StEP, Green Cap
0.45um PTFE w/pre-slit cap, 200-pk, Thomson SINGLE StEP, Blue Cap .
0.45um PTFE w/pre-slit cap, 500-pk, Thomson SINGLE StEP, Blue Cap
0.2um PVDF w/pre-slit cap, 200-pk, Thomson SINGLE StEP, Red Cap
0.2um PVDF w/pre-slit cap, 500-pk, Thomson SINGLE StEP, Red Cap
0.45um PVDF w/pre-slit cap, 200-pk, Thomson SINGLE StEP, Yellow Cap
0.45um PVDF w/pre-slit cap, 500-pk, Thomson SINGLE StEP, Yellow Cap

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034



**HROMalytic** +61(0)3 9762 2034

**ECHnology** Pty Ltd

Website NEW : [www.chromalytic.net.au](http://www.chromalytic.net.au) E-mail : [info@chromtech.net.au](mailto:info@chromtech.net.au) Tel: 03 9762 2034 . . . in AUSTRALIA

**Australian Distributors**  
Importers & Manufacturers  
[www.chromtech.net.au](http://www.chromtech.net.au)

