

25290	Plunger Seal	Polyethylene, LC-10AS, 10AT, 10ATv
25291	Sapphire Plunger	LC-10AS
25292	Plunger Rinse Seal	LC-10AS
25293	Plunger Seal	LC-600, LC-9A, LC-10AD
25294	Sapphire Plunger	LC-600, LC-9A, LC-10AD
25295	Inlet Check Valve	LC-600, LC-9A, LC-10AD
25296	Fast LC Development Kit	Four 30 x 2.1mm Fast LC Cartridges. Includes Catalog #s 91063320, 91743320, 9
25297	Fast LC Development Kit	Four 30 x 4.0mm Fast LC Cartridges. Includes Catalog #s 91063340, 91743340, 9
25298	Fast LC Cartridge Holder	Direct Connect, PEEK Tip
25299	Fast LC Cartridge Holder	Standard Fittings
25300	Opti-Cap	Including Cap and PEEK Plug
25301	Opti-Cap Kit	Opti-Cap, Teflon Tubing, Mobile Phase Filter and Sparging Filter
25302	Opti-Cap Kit w/1L Bottle	Opti-Cap Kit with 1L Graduated Safety Coated Bottle
25303	Opti-Cap Kit w/2L Bottle	Opti-Cap Kit with 2L Graduated Safety Coated Bottle
25304	1L Safety Coated Bottle	Graduated, GL45 Threads
25305	2L Safety Coated Bottle	Graduated, GL45 Threads
25306	Teflon Tubing 1/8" 0.063"	1/8" OD x 0.063" ID x 3m L
25307	Teflon Tubing 1/8" 0.094"	1/8" OD x 0.094" ID x 3m L
25308	PEEK Tubing Elbow 90 Deg	For 1/16" Tubing, Pack of 5
25309	PEEK Tubing Elbow 180 Deg	For 1/16" Tubing, Pack of 5
25310	Tubing Clip	For 1/16" and 1/8" Tubing Pack of 5
25311	Inlet Filter	Helium Sparger, 2um Threaded
25312	Inlet Filter	Helium Sparger, 10um Threaded
25313	Inlet Filter	Helium Sparger, 20um Threaded
25314	LastDrop Inlet Filter 2um	Mobile Phase Filter
25315	LastDrop Inlet Filter	10um Mobile Phase Filter
25319	PEEK Plug 1/4"-28 Thread	For Opti-Cap, Pack of 3
25320	PEEK Tubing, Pink Dash	Pink Dash Stripe, 3pk, 0.0025"ID x 1/16" OD x 1m L
25321	ValvTool Wrench	For 1/4" Nuts Previously called Rheotool.
25322	Survival Kit for HPLC	PEEK
25323	PEEK Union 1/16"	Pack of 2
25324	PEEK Fingertight Fittings	Universal 10-32 Pack of 10
25325	Tool	PEEK Fitting Extractor HPLC
25326	QuickSplit Splitter	Binary Fixed Flow, Split Ratio 100:1, Post Column
25327	QuickSplit Splitter	Binary Fixed Flow, Split Ratio 50:1, Post Column
25328	QuickSplit Splitter	Binary Fixed Flow, Split Ratio 20:1, Post Column
25329	QuickSplit Splitter	Binary Fixed Flow, Split Ratio 10:1, Post Column
25330	QuickSplit Splitter	Binary Fixed Flow, Split Ratio 5:1, Post Column
25331	Fixed Flow Splitter	Resistor Set Split Ratio 100:1, Post Column
25332	Fixed Flow Splitter	Resistor Set Split Ratio 50:1, Post Column
25333	Fixed Flow Splitter	Resistor Set Split Ratio 20:1, Post Column
25334	Fixed Flow Splitter	Resistor Set Split Ratio 10:1, Post Column
25335	Fixed Flow Splitter	Resistor Set Split Ratio 5:1, Post Column
25336	QuickSplit Splitter	Adjustable Flow, Split Ratio 5:1 to 100:1, Post Column
25337	QuickSplit Splitter	Adjustable Flow, Split Ratio 1:1 to 20:1, Post Column
25338	Splitter Resistor	Adjustable Flow, Split Ratio 5:1 to 100:1, Post Column
25339	Splitter Resistor	Adjustable Flow, Split Ratio 1:1 to 20:1, Post Column
25340	FlatLine Pulse Damper	
25341	HyperShear Static Mixer	In-Line Mixer, 50uL Stainless Steel
25342	HyperShear Static Mixer	In-Line Mixer, 150uL Stainless Steel
25343	HyperShear Static Mixer	In-Line Mixer, 250uL Stainless Steel
25344	Check Valve Cartridge	Assembly, Agilent 1090, Similar to
25345	Sapphire Piston	Agilent 1090
25347	Piston Seals (Black)	Agilent 1090, 4pk
25348	Needle Seat, Agilent 1090	
25349	Rotor Seal	Rheodyne Style, Agilent 1090
25352	HPLC Valid. Kit	Allure C18 150 x 4.6mm Kit of 3 Columns
25354	HPLC Valid. Kit	Allure Basix 150 x 4.6mm Kit of 3 Columns
25355	HPLC Valid. Kit	Ultra IBD 150 x 4.6mm Kit of 3 Columns
25356	LC/MS Valid. Kit	Allure C18 50 x 2.1mm Kit of 3 Columns
25358	LC/MS Valid. Kit	Allure Basix 50 x 2.1mm Kit of 3 Columns
25359	LC/MS Valid. Kit	Ultra IBD 50 x 2.1mm Kit of 3 Columns
25360	Inlet Check Valve Assy.	
25361	Inlet Check Valve Housing	
25362	Inlet Check Valve	Rebuild Kit 2pk
25363	Outlet Check Valve Assy.	Actuator Style Similar to Waters # WAT025028

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034

		Australian Distributors Importers & Manufacturers www.chromtech.net.au
Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA		

[Ctrl F]
> Cat.#s

> Current System AUD Prices

