

26322	Rupture Disc Tee	1/4" Male NPT x 1/4" Female NPT 28
26323	Rupture Disc Tee	1/4" Male NPT x 1/4" Female NPT 28
26324	Rupture Disc Replacement	Fits Rupture Disc Tee 2850psig DOT
26326	Metering Control Valve	1/4" Male NPT x 1/4" Male NPT 3500psig DOT press rating, Stainless Steel
26327	Metering Control Valve	1/4" Male NPT x 1/4" Male NPT 3500psig DOT press rating, Sulfinert
26328	Gas Sampling Bag	ALTEF, 12L, 13"x24" w/Polypropylene combo valve & septum, 1 eyelet, 10-pk
26329	Gas Sampling Bag	ALTEF, 40L, 24"x 24.25" w/Polypropylene combo valve & septum, 1 eyelet, 5-pk
26330	Gas Sampling Bag	ALTEF, 80L, 28.25" x 30.5" w/polypropylene combo valve & septum, 1 eyelet, 3-pl
26331	Gas Sampling Bag	ALTEF, 100L, 28" x 36" w/polypropylene combo valve & septum, 1 eyelet, 3-pk
26393	Active Inlet Cartridge	Designed for Agilent Models 1050, 1100, 1200
26394	PEEK Performance Kit	Includes: Hub-Cap Adapter w/Cap, Clean-cut Tubing Cutter, Tubing Clips, Finger
26395	Hub-Cap Filter Kit	for HPLC, Used to prefilter the Mobil Phase
26396	Membrane Filters	Polypropylene, 47mm, 0.45um, 100pk
26397	Membrane Filters	Polypropylene, 47mm, 0.22um, 100pk
26398	Membrane Filters	Nylon, 47mm, 0.45um, 100pk
26399	Membrane Filters	Nylon, 47mm, 0.22um, 100pk
26400	HPLC Through Valve	2-Way, 1/16" Fittings, 1/4-28, SS, Includes Nuts and Ferrules
26401	HPLC Angle Valve	2-Way, 1/16" Fittings, SS, Includes Nuts and Ferrules
26402	HPLC Bottom Vent Valve	3-Way, 1/16" Fittings, 1/4-28, SS, Includes Nuts and Ferrules
26403	HPLC Side Vent Valve	1/16" Fittings, 1/4-28, SS, Includes Nuts and Ferrules
26404	HPLC Dual Stem Valve	3-Way, 1/16" Fittings, 1/4-28, SS, Includes Nuts and Ferrules
26405	HPLC Check Valve	Soft Seat, 1/16" Fittings, SS, Includes Nuts and Ferrules
26406	HPLC Prime/Purge Valve	1/4-28 Flanged Seat, SS, w/Tubing and Fittings
26407	Valve Repair Kit	For Prime/Purge Valve
26408	Pack in a Box	HPLC Column Packing Station Includes Pump, Reservoir, Column Hardware, Pac
26409	HyperShear Static Mixer	In-Line Mixer Assembly 1uL Stainless Steel
26410	HyperShear Static Mixer	In-Line Mixer Assembly 1uL Peek
26411	HyperShear Static Mixer	In-Line Mixer Assembly 25uL Stainless Steel
26412	HyperShear Static Mixer	In-Line Mixer Assembly 25uL PEEK
26413	HyperShear Static Mixer	In-Line Mixer Assembly 50uL PEEK
26414	HyperShear Static Mixer	In-Line Mixer Assembly 150uL PEEK
26415	HyperShear Static Mixer	In-Line Mixer Assembly 250uL PEEK
26416	QuickSplit Flow Splitter	Adjustable Flow Splitter Split Ratio 50:1 to 1000:1 Post Column
26417	In-Line Check Valve	With 1/8" Ball Cartridge 48uL internal volume, 15,000psi max pressure
26418	In-Line CV Cartridge	Replacement 1/8" Ball Cartridge 48uL internal volume, 15,000psi max pressure
26419	In-Line Check Valve, UHP	With 1/8" Ball Cartridge, Ultra High Pressure, 48uL internal volume, 30,000psi ma
26420	In-Line CV Cartridge, UHP	Replacement 1/8" Ball Cartridge, Ultra High Pressure 48uL internal volume, 30,00
26421	In-Line Check Valve	With 3/16" Ball Cartridge, 60uL internal volume, 15,000psi max pressure
26422	In-Line CV Cartridge	Replacement 3/16" Ball Cartridge 60uL internal volume, 15,000psi max pressure
26423	Solvent Inlet Filter, SS	For Agilent 1040, 1050, 1090, 1100, 1200, 8452A, 8453, G1265A, G1311, G1312,
26424	Stator Face Assembly	For Agilent 1100 and 1200
26425	Standard Pump Seals	For Perkin Elmer Kit S200
26426	Check Valve, Inlet	For Shimadzu LC-20AD/B
26427	Check Valve, Outlet	For Shimadzu LC-20AD/B
26428	Head Plunger Seal	For Waters Acquity and nanoAcquity, 2-pk
26429	Wash Seal	For Waters Acquity and nanoAcquity, 2-pk
26430	Pump PM Kit	For Waters Pump PM Kit
26510	Secure-Fit Fitting	Stainless Steel Single Ended 50cm x 0.005" ID
26511	Secure-Fit Fitting	Stainless Steel Single Ended 50cm x 0.007" ID
26512	Secure-Fit Fitting	Stainless Steel Single Ended 50cm x 0.010" ID
26513	Secure-Fit Fitting	Stainless Steel Double Ended 50cm x 0.005" ID
26514	Secure-Fit Fitting	Stainless Steel Double Ended 50cm x 0.007" ID
26515	Secure-Fit Fitting	Stainless Steel Double Ended 50cm x 0.010" ID
26516	Sidewinder Column Heater	Temp. Control Module w/Long Column Holder (25cm)
26517	Sidewinder Column Heater	Temp. Control Module w/Short Column Holder (10cm)
26518	Sidewinder Column Module	Heater/Cooler Temp. Control Module, 30cm Holder
26519	Preventative Maint. Kit	for Waters 515 Pump. Kit Includes: 1 Solvent Filter 10um, 2 performance plus che
26520	Injector Lubricant	PTFE, 10 grams
26521	Inlet Check Valve	for Shimadzu LC-10AT, LC-10ATvp.
26525	Capillary SS Tubing	130mm x 0.17mm ID, Green, 1/16" SS Male Nut, F/B Ferrule Set
26526	Capillary SS Tubing	800mm x 0.17mm ID, Green 1/16" SS Male Nut, F/B Ferrule Set 1/16" Rheodyne
26527	Capillary SS Tubing	180mm x 0.17mm ID, Green 1/16" SS Male Nut, F/B Ferrule Set
26528	Capillary SS Tubing	700mm x 0.25mm ID, Blue 1/16" SS Male Nut, F/B Ferrule Set
26529	Capillary SS Tubing	700mm x 0.25mm ID, Blue 1/16" SS Male Nut, F/B Ferrule Set 1/16" Rheodyne M
26530	Seat Capillary	SS Tubing 0.17mm ID, Green 1/16" SS Male Nut, F/B Ferrule Set 1/16" Rheodyne
26531	Capillary SS Tubing	105mm x 0.17mm ID, Green

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034

		+61(0)3 9762 2034 <b>ECH</b> nology Pty Ltd	<b>Australian Distributors</b> Importers & Manufacturers <a href="http://www.chromtech.net.au">www.chromtech.net.au</a>
Website NEW : <a href="http://www.chromalytic.net.au">www.chromalytic.net.au</a> E-mail : <a href="mailto:info@chromtech.net.au">info@chromtech.net.au</a> Tel: 03 9762 2034 . . . in AUSTRALIA			



(Ctrl F)  
> Cat.#s

> Current System AUD Prices

press rating, Stainless Steel