

26532	Mixing Capillary	1/16" SS Male Nut, F/B Ferrule Set 1/	Page 124
26533	Tubing	Valve to Metering Head, Blue 1/16" S	(Ctrl F) > Cat.#s
26534	Capillary SS Tubing	150mm x 0.17mm ID, Green	> Current System AUD Prices
26535	Capillary SS Tubing	280mm x 0.17mm ID, Green	
26536	Capillary SS Tubing	400mm x 0.17mm ID, Green	
26537	Fitting, Stainless Steel	1/16" Male Nut, 1/16" Front and Back Ferrule Set, 10pk	
26538	Hub-Cap Adapter	Adapter to use the Opti-Cap on a 4 Liter Bottle	
26539	Hub-Cap Adapter	Adapter to use the Opti-Cap on a 4 Liter Bottle, 3pk	
26540	Hub-Cap Adapter	New 4 Liter Bottle Adapter and Opti-Cap	
26541	Hub-Cap Assembly	Assembly of the Bottle Cap and Plug	
26542	Hub-Cap Multi Pack	3pk	
26543	Mobile Phase Indicator	Waste Overflow Indicator for HPLC Systems, AA Battery Operated	
26544	Replacement AA Battery	for the Mobile Phase Waste Indicator	
26545	Replacement AA Batteries	for the Mobile Phase Waste Indicator, 3pk	
26546	BioSafe Column System	PEEK, 4.6x30mm, 2um	
26547	Face Seals	Replacement Kit, 4pk	
26548	1/16" Ferrule, 316 SST	10pk, Component of Kit 25097	
26549	UHP Pulse Dampener		
26550	Waste Overflow Indicator	for HPLC Systems w/GL45 Bottles, Alerts user to empty the waste collection bottle	
26551	Opti-cap adapter	w/Hub cap	
27100	Septa, BTO	5mm, CenterGuide, 50pk	
27101	Septa, BTO	5mm, CenterGuide, 100pk	
27102	Septa, BTO	6mm, 50pk	
27103	Septa, BTO	6mm, 100pk	
27104	Septa, BTO	9mm, CenterGuide, 50pk	
27105	Septa, BTO	9mm, CenterGuide, 100pk	
27106	Septa, BTO	9.5mm, 50pk	
27107	Septa, BTO	9.5mm, 100pk	
27108	Septa, BTO	10mm, 50pk	
27109	Septa, BTO	10mm, 100pk	
27110	Septa, BTO	11mm, CenterGuide, 50pk	
27111	Septa, BTO	11mm, CenterGuide, 100pk	
27112	Septa, BTO	11.5mm, CenterGuide, 50pk	
27113	Septa, BTO	11.5mm, CenterGuide, 100pk	
27114	Septa, BTO	12.7mm (1/2"), CenterGuide, 50pk	
27115	Septa, BTO	12.7mm (1/2"), CenterGuide, 100pk	
27116	Septa, BTO	17mm, CenterGuide, 50pk	
27117	Septa, BTO	17mm, CenterGuide, 100pk	
27118	Septa, BTO	Shimadzu Plug, 50pk	
27119	Septa, BTO	Shimadzu Plug, 100pk	
27120	Septa, Thermolite	5mm (3/16"), 25pk	
27121	Septa, Thermolite	5mm (3/16"), 50pk	
27122	Septa, Thermolite	5mm (3/16"), 100pk	
27123	Septa, Thermolite	6mm (1/4"), 25pk	
27124	Septa, Thermolite	6mm (1/4"), 50pk	
27125	Septa, Thermolite	6mm (1/4"), 100pk	
27126	Septa, Thermolite	7mm, 25pk	
27127	Septa, Thermolite	7mm, 50pk	
27128	Septa, Thermolite	7mm, 100pk	
27129	Septa, Thermolite	8mm, 25pk	
27130	Septa, Thermolite	8mm, 50pk	
27131	Septa, Thermolite	8mm, 100pk	
27132	Septa, Thermolite	9mm, 25pk	
27133	Septa, Thermolite	9mm, 50pk	
27134	Septa, Thermolite	9mm, 100pk	
27135	Septa, Thermolite	9.5mm (3/8"), 25pk	
27136	Septa, Thermolite	9.5mm (3/8"), 50pk	
27137	Septa, Thermolite	9.5mm (3/8"), 100pk	
27138	Septa, Thermolite	10mm, 25pk	
27139	Septa, Thermolite	10mm, 50pk	
27140	Septa, Thermolite	10mm, 100pk	
27141	Septa, Thermolite	11mm (7/16"), 25pk	
27142	Septa, Thermolite	11mm (7/16"), 50pk	
27143	Septa, Thermolite	11mm (7/16"), 100pk	
27144	Septa, Thermolite	11.5mm, 25pk	
27145	Septa, Thermolite	11.5mm, 50pk	

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034

 <b>HROMalytic</b> +61(0)3 9762 2034 <b>ECHnology</b> Pty Ltd		<b>Australian Distributors</b> Importers & Manufacturers <a href="http://www.chromtech.net.au">www.chromtech.net.au</a>
Website NEW : <a href="http://www.chromalytic.net.au">www.chromalytic.net.au</a> E-mail : <a href="mailto:info@chromtech.net.au">info@chromtech.net.au</a> Tel: 03 9762 2034 . . . in AUSTRALIA		