

41302	Rtx-PCB Cap. Column	20m, 0.18mm ID, 0.18um
41303	Rtx-PCB Cap. Column	40m, 0.18mm ID, 0.18um
41303-6850	Rtx-PCB Cap. Column	40m, 0.18mm ID, 0.18um For HP 6850
41304	Rtx-PCB Cap. Column	60m, 0.18mm ID, 0.18um
41601	Rtx-Wax Cap. Column	10m, 0.10mm ID, 0.10um
41601-023	Rtx-Wax Cap. Column	10m, 0.10mm ID, 0.10um w/full Grob Mix test
41601-071	Rtx-Wax Cap. Column	10 x 1m, 0.10mm ID, 0.10um No Cages
41601-076	Rtx-Wax Cap. Column	2 x 5m, 0.10mm ID, 0.10um
41601-149	Rtx-Wax Cap. Column	5m/3m/2m, 0.10mm ID, 0.10um
41602	Rtx-Wax Cap. Column	20m, 0.10mm ID, 0.10um
41603	Rtx-Wax Cap. Column	10m, 0.10mm ID, 0.20um
41604	Rtx-Wax Cap. Column	20m, 0.10mm ID, 0.20um
41604-089	Rtx-Wax Cap. Column	2 x 10m, 0.10mm ID, 0.20um
42001	Rtx-1701 Cap. Column	10m, 0.18mm ID, 0.20um
42001-6850	Rtx-1701 Cap. Column	10m, 0.18mm ID, 0.20um For HP 6850 GC's
42002	Rtx-1701 Cap. Column	20m, 0.18mm ID, 0.20um
42003	Rtx-1701 Cap. Column	40m, 0.18mm ID, 0.20um
42010	Rtx-1701 Cap. Column	10m, 0.18mm ID, 0.40um
42010-600	Rtx-1701 Cap. Column	10m, 0.18mm ID, 0.40um Package of 6
42011	Rtx-1701 Cap. Column	20m, 0.18mm ID, 0.40um
42012	Rtx-1701 Cap. Column	40m, 0.18mm ID, 0.40um
42101	Rtx-CLP I Cap. Column	10m, 0.18mm ID, 0.18um
42102	Rtx-CLP I Cap. Column	20m, 0.18mm ID, 0.18um
42201	Rtx-1701 Cap. Column	10m, 0.1mm, 0.1um
42201-067	Rtx-1701 Cap. Column	5 x 2m, 0.1mm, 0.1um
42202	Rtx-1701 Cap. Column	20m, 0.1mm, 0.1um
42301	Rtx-CLP II Cap. Column	10m, 0.18mm ID, 0.14um
42302	Rtx-CLP II Cap. Column	20m, 0.18mm ID, 0.14um
42601	Stabilwax Cap. Column	10m, 0.10mm ID, 0.10um
42702	Rtx-5Sil MS Cap. Column	20m, 0.18mm ID, 0.18um
42702-600	Rtx-5Sil MS Cap. Column	20m, 0.18mm ID, 0.18um Pack of 6
42703	Rtx-5Sil MS Cap. Column	10m, 0.18mm ID, 0.18um
42704	Rtx-5Sil MS Cap. Column	20m, 0.18mm ID, 0.36um
42705	Rtx-5Sil MS Cap. Column	12m, 0.20mm ID, 0.33um
42706	Rtx-5Sil MS Cap. Column	25m, 0.20mm ID, 0.20um
42706-600	Rtx-5Sil MS Cap. Column	25m, 0.20mm ID, 0.20um Pack of 6
42707	Rtx-5Sil MS Cap. Column	50m, 0.20mm ID, 0.20um
42708	Rtx-5Sil MS Cap. Column	12m, 0.20mm ID, 0.35um
42709	Rtx-5Sil MS Cap. Column	50m, 0.20mm ID, 0.35um
42902	Rtx-440 Cap. Column	20m, 0.18mm ID, 0.18um
42903	Rtx-440 Cap. Column	40m, 0.18mm ID, 0.18um
43101	Rtx-CLP Cap. Column	10m, 0.10mm ID, 0.10um
43301	Rtx-CLPII Cap. Column	10m, 0.10mm ID, 0.10um
43302	Rtx-CLPII Cap. Column	20m, 0.10mm ID, 0.10um
43601	Rxi-5Sil MS Cap. Column	10m, 0.10mm ID, 0.10um
43601-067	Rxi-5Sil MS Cap. Column	2 x 5m, 0.10mm ID, 0.10um
43602	Rxi-5Sil MS Cap. Column	20m, 0.18mm ID, 0.18um
43602-600	Rxi-5Sil MS Cap. Column	20m, 0.18mm ID, 0.18um Pack of 6
43602-6850	Rxi-5Sil MS Cap. Column	20m, 0.18mm ID, 0.18um 5in cage for HP 6850
43604	Rxi-5Sil MS Cap. Column	20m, 0.18mm ID, 0.36um
43604-600	Rxi-5Sil MS Cap. Column	20m, 0.18mm ID, 0.36um Pack of 6
43604-6850	Rxi-5Sil MS Cap. Column	20m, 0.18mm ID, 0.36um
43605	Rxi-5Sil MS Cap. Column	40m, 0.18mm ID, 0.18um
43607	Rxi-5Sil MS Cap. Column	60m, 0.18mm ID, 0.10um
43701	Rxi-XLB Cap. Column	10m, 0.10mm ID, 0.10um
43702	Rxi-XLB Cap. Column	20m, 0.18mm ID, 0.18um
43800	Rxi-1ms Cap. Column	10m, 0.15mm ID, 0.15um
43801	Rxi-1ms Cap. Column	20m, 0.15mm ID, 0.15um
43802	Rxi-1ms Cap. Column	20m, 0.15mm ID, 2.0um
43815	Rxi-5Sil MS Cap. Column	10m, 0.15mm ID, 0.15um
43816	Rxi-5Sil MS Cap. Column	20m, 0.15mm ID, 0.15um
43817	Rxi-5Sil MS Cap. Column	20m, 0.15mm ID, 2.0um
43820	Rxi-17Sil MS Cap. Column	10m, 0.15mm ID, 0.15um
43821	Rxi-17Sil MS Cap. Column	20m, 0.15mm ID, 0.15um
43830	Stabilwax Cap. Column	10m, 0.15mm ID, 0.15um
43831	Stabilwax Cap. Column	20m, 0.15mm ID, 0.15um

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034

 HROMalytic +61(0)3 9762 2034 ECHnology Pty Ltd		Australian Distributors Importers & Manufacturers www.chromtech.net.au
Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA		

[Ctrl F]
> Cat.#s

> Current System AUD Prices

