

70105-600	MXT-1 Cap. Column
70106	MXT-1 Cap. Column
70106-600	MXT-1 Cap. Column
70106-6850M	MXT-1 Cap. Column
70107	MXT-1 Cap. Column
70107-6850M	MXT-1 Cap. Column
70108	MXT-1 Cap. Column
70108-137	MXT-1 Cap. Column
70108-276	MXT-1 Cap. Column
70108-600	MXT-1 Cap. Column
70109	MXT-1 Cap. Column
70109-273	MXT-1 Cap. Column
70109-6850M	MXT-1 Cap. Column
70111	MXT-1 Cap. Column
70112	MXT-1HT SimDist Column
70112-600	MXT-1HT SimDist Column
70114	MXT-1 Cap. Column
70114-283	MXT-1 Cap. Column
70115	MXT-1HT SimDist Column
70115-273	MXT-1HT Sim Dist Column
70116	MXT-1 Cap. Column
70116-101	MXT-1 Cap. Column
70117	MXT-1 Cap. Column
70117-283	MXT-1 Cap. Column
70118	MXT-1HT SimDist Column
70119	MXT-1HT SimDist Column
70120	MXT-1 Cap. Column
70120-273	MXT-1 Cap. Column
70121	MXT-1 Cap. Column
70121-273	MXT-1 Cap. Column
70122	MXT-1 Cap. Column
70122-104	MXT-1 Cap. Column
70122-10427	MXT-1 Cap. Column
70122-107	MXT-1 Cap. Column
70122-10727	MXT-1 Cap. Column
70122-10728	MXT-1 Cap. Column
70122-123	MXT-1 Cap. Column
70122-12327	MXT-1 Cap. Column
70122-271	MXT-1 Cap. Column
70122-273	MXT-1 Cap. Column
70122-274	MXT-1 Cap. Column
70122-600	MXT-1 Cap. Column
70123	MXT-1 Cap. Column
70123-273	MXT-1 Cap. Column
70123-6850M	MXT-1 Cap. Column
70124	MXT-1 Cap. Column
70124-111	MXT-1 Cap. Column
70124-273	MXT-1 Cap. Column
70125	MXT-1 Cap. Column
70125-111	MXT-1 Cap. Column
70125-11127	MXT-1 Cap. Column
70125-112	MXT-1 Cap. Column
70125-271	MXT-1 Cap. Column
70125-273	MXT-1 Cap. Column
70125-600	MXT-1 Cap. Column
70126	MXT-1 Cap. Column
70126-273	MXT-1 Cap. Column
70126-283	MXT-1 Cap. Column
70127	MXT-1 Cap. Column
70127-271	MXT-1 Cap. Column
70127-272	MXT-1 Cap. Column
70127-273	MXT-1 Cap. Column
70127-350	MXT-1 Cap. Column
70128	MXT-1 Cap. Column
70128-351	MXT-1 Cap. Column
70129	MXT-1 Cap. Column

15m, 0.25mm ID, 0.10um 6pk
15m, 0.28mm ID, 0.10um
15m, 0.28mm ID, 0.10um Pack of 6
15m, 0.28mm ID, 0.10um 5in coil banded w/copper wire no cage
15m, 0.53mm ID, 0.15um
15m, 0.53mm ID, 0.15um 5in coil banded w/copper wire no cage
15m, 0.53mm ID, 0.20um
8m, 0.53mm ID, 0.20um
15m, 0.53mm ID, 0.20um 6 inch Diameter Cage
15m, 0.53mm ID, 0.20um Package of 6
30m, 0.28mm ID, 0.10um
30m, 0.28mm ID, 0.10um 3.5"OD w/o Cage,
30m, 0.28mm ID, 0.10um on 6850 Cage
30m, 0.53mm ID, 0.20um
5m, 0.53mm ID, 0.10um on 11-Pin Cage
5m, 0.53mm ID, 0.10um On 11-Pin Cage, Pack of 6
105m, 0.25mm ID, 0.10um
105m, 0.25mm ID, 0.10um 3.5" Inside Diameter w/o Cage
5m, 0.53mm ID, 0.20um on 11-Pin Cage
5m, 0.53mm ID, 0.20um Coil into 3.5"OD w/out cage
30m, 0.25mm ID, 0.10um
3-10m, 0.25mm ID, 0.10um
60m, 0.25mm ID, 0.10um
60m, 0.25mm ID, 0.10um 3.5" Inside Diameter w/o Cage
10m, 0.53mm ID, 0.21um on 11-Pin Cage
10m, 0.53mm ID, 1.2um on 11-Pin Cage
15m, 0.25mm ID, 0.25um
15m, 0.25mm ID, 0.25um 3.5"OD w/o Cage,
15m, 0.28mm ID, 0.25um
15m, 0.28mm ID, 0.25um 3.5"OD w/o Cage,
15m, 0.53mm ID, 0.25um
3-5m, 0.53mm ID, 0.25um
3-5m, 0.53mm ID, 0.25um 6in coil w/out cage
10m, 0.53mm ID, 0.25um
10m, 0.53mm ID, 0.25um 6 inch coil
10m, 0.53mm ID, 0.25um 3.5"ID Coil w/o Cage
5m & 10m, 0.53mm ID, 0.25um
5m & 10m, 0.53mm ID, 0.25um 6" Conf w/out cage
15m, 0.53mm ID, 0.25um 6" Config. w/o Cage
15m, 0.53mm ID, 0.25um 3.5"OD w/o Cage,
15m, 0.53mm ID, 0.25um 2.5" Coil
15m, 0.53mm ID, 0.25um Pack of 6
30m, 0.25mm ID, 0.25um
30m, 0.25mm ID, 0.25um 3.5"OD without cage Fits SRI GCs
30m, 0.25mm ID, 0.25um 5" Coil for Agilent 6850, Banded w/ copper wire
30m, 0.28mm ID, 0.25um
2 - 15m, 0.28mm ID, 0.25um
30m, 0.28mm ID, 0.25um 3.5"OD w/o Cage,
30m, 0.53mm ID, 0.25um
2x15m, 0.53mm ID, 0.25um
2x15m, 0.53mm ID, 0.25um 3.5"OD w/o Cage,
20m, 0.53mm ID, 0.25um
30m, 0.53mm ID, 0.25um 6" Config. w/o Cage
30m, 0.53mm ID, 0.25um 3.5"OD w/o Cage,
30m, 0.53mm ID, 0.25um Pack of 6
60m, 0.25mm ID, 0.25um
60m, 0.25mmID, 0.25um 3.5"OD w/o Cage,
60m, 0.25mm ID, 0.25um 3.5" Inner Diameter w/o Cage
60m, 0.28mm ID, 0.25um
60m, 0.28mm ID, 0.25um 6" Config. w/Cage
60m, 0.28mmID, 0.25um 4 1/2"ID w/out cage (4.5"ID/5.0"OD)
60m, 0.28mmID, 0.25um 3.5"OD w/o Cage,
60m, 0.28mm ID, 0.25um w/LDV Con. to 0.28mmID MXT GC
60m, 0.53mm ID, 0.25um
60m, 0.53mm ID, 0.25um w/5mMXTGuard&MXTLDVConnector
105m, 0.25mm ID, 0.25um

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034



**HROMalytic** +61(0)3 9762 2034  
ECHnology Pty Ltd

**Australian Distributors**  
Importers & Manufacturers  
www.chromtech.net.au

Website NEW : [www.chromalytic.net.au](http://www.chromalytic.net.au) E-mail : [info@chromtech.net.au](mailto:info@chromtech.net.au) Tel: 03 9762 2034 . . . in AUSTRALIA

(Ctrl F)  
> Cat.#s

> Current System AUD Prices

