

70192-273	MXT-1 Cap. Column
70192-2730	MXT-1 Cap. Column
70192-274	MXT-1 Cap. Column
70192-283	MXT-1 Cap. Column
70193	MXT-1 Cap. Column
70193-115	MXT-1 Cap. Column
70193-271	MXT-1 Cap. Column
70193-272	MXT-1 Cap. Column
70193-2720	MXT-1 Cap. Column
70193-273	MXT-1 Cap. Column
70193-2730	MXT-1 Cap. Column
70193-274	MXT-1 Cap. Column
70193-283	MXT-1 Cap. Column
70199	MXT-2887 Cap. Column
70199-051	MXT-2887 Cap. Column
70199-076	MXT-2887 Cap. Column
70199-07668	MXT-2887 Cap. Column
70199-271	MXT-2887 Cap. Column
70199-273	MXT-2887 Cap. Column
70199-274	MXT-2887 Cap. Column
70199-283	MXT-2887 Cap. Column
70199-6850M	MXT-2887 Cap. Column
70205	MXT-5 Cap. Column
70208	MXT-5 Cap. Column
70211	MXT-5 Cap. Column
70220	MXT-5 Cap. Column
70220-273	MXT-5 Cap. Column
70221	MXT-5 Cap. Column
70221-350	MXT-5 Cap. Column
70222	MXT-5 Cap. Column
70222-107	MXT-5 Cap. Column
70222-271	MXT-5 Cap. Column
70222-273	MXT-5 Cap. Column
70222-274	MXT-5 Cap. Column
70222-600	MXT-5 Cap. Column
70223	MXT-5 Cap. Column
70223-273	MXT-5 Cap. Column
70223-283	MXT-5 Cap. Column
70223-400	MXT-5 Cap. Column
70223-6850M	MXT-5 Cap. Column
70224	MXT-5 Cap. Column
70224-273	MXT-5 Cap. Column
70225	MXT-5 Cap. Column
70225-272	MXT-5 Cap. Column
70225-273	MXT-5 Cap. Column
70225-351	MXT-5 Cap. Column
70226	MXT-5 Cap. Column
70226-271	MXT-5 Cap. Column
70226-273	MXT-5 Cap. Column
70227	MXT-5 Cap. Column
70227-273	MXT-5 Cap. Column
70228	MXT-5 Cap. Column
70228-6850	MXT-5 Cap. Column
70228-6850M	MXT-5 Cap. Column
70235	MXT-5 Cap. Column
70236	MXT-5 Cap. Column
70236-10728	MXT-5 Cap. Column
70236-11928	MXT-5 Cap. Column
70236-273	MXT-5 Cap. Column
70236-283	MXT-5 Cap. Column
70237	MXT-5 Cap. Column
70237-107	MXT-5 Cap. Column
70237-12328	MXT-5 Cap. Column
70237-273	MXT-5 Cap. Column
70238	MXT-5 Cap. Column
70238-106	MXT-5 Cap. Column

30m, 0.53mm ID, 7.00um 3.5"OD w/o
30m, 0.53mm ID, 7.00um 3.5"OD band
30m, 0.53mm ID, 7.00um Coil into 2/1
30m, 0.53mm ID, 7.00um 3.5" ID Coil
60m, 0.53mm ID, 7.00um
20 & 40m, 0.53mm ID, 7.00um
60m, 0.53mm ID, 7.00um 6" Coil
60m, 0.53mm ID, 7.00um 4.5" Coil
60m, 0.53mm ID, 7.00um 4 1/2in ID banded w/copper wire
60m, 0.53mm ID, 7.00um 3.5"OD w/o Cage,
60m, 0.53mm ID, 7.00um 3.5"OD banded w/copper wire
60m, 0.53mm ID, 7.00um 2.5"OD Coil w/o Cage
60m, 0.53mm ID, 7.00um 3.5"ID Coil w/o Cage
10m, 0.53mm ID, 2.65um
10m, 0.53mm ID, 2.65um No Cage (No guarantee for breakage)
2-5m, 0.53mm ID, 2.65um
2-5m, 0.53mm ID, 2.65um 5in coil banded w/copper wire
10m, 0.53mm ID, 2.65um 6in conf w/out cage
10m, 0.53mm ID, 2.65um 3.5"OD w/o Cage,
10m, 0.53mm ID, 2.65um 2.5" Coil
10m, 0.53mm ID, 2.65um 3.5" ID Coil
10m, 0.53mm ID, 2.65um 5in coil, banded w/copper wire
15m, 0.25mm ID, 0.10um
30m, 0.25mm ID, 0.10um
60m, 0.25mm ID, 0.10um
15m, 0.25mm ID, 0.25um
15m, 0.25mm ID, 0.25um 3.5"OD w/o Cage,
15m, 0.28mm ID, 0.25um
15m, 0.28mm ID, 0.25um Connect 0.28mm ID MXT GC with LDV
15m, 0.53mm ID, 0.25um
10m, 0.53mm ID, 0.25um
15m, 0.53mm ID, 0.25um 6in conf w/out cage
15m, 0.53mm ID, 0.25um 3.5"OD w/o Cage,
15m, 0.53mm ID, 0.25um Coil MXT columns into 2 1/2" OD w/out cage
15m, 0.53mm ID, 0.25um 6pk
30m, 0.25mm ID, 0.25um
30m, 0.25mm ID, 0.25um 3.5"OD w/o Cage,
30m, 0.25mm ID, 0.25um 3.5"ID/4.0"OD Coil
30m, 0.25mm ID, 0.25um 4.0"ID, 4.5"OD Coil w/o Cage
30m, 0.25mm ID, 0.25um 5" Coil
30m, 0.28mm ID, 0.25um
30m, 0.28mm ID, 0.25um 3.5"OD w/o Cage,
30m, 0.53mm ID, 0.25um
30m, 0.53mm ID, 0.25um 4.5"Coil
30m, 0.53mm ID, 0.25um 3.5"OD w/o Cage,
30m, 0.53mm ID, 0.25um w/5m, 0.53mm Guard&MXTLDV Con.
60m, 0.25mm ID, 0.25um
60m, 0.25mm ID, 0.25um 6" Config w/o Cage
60m, 0.25mm ID, 0.25um 3.5"OD w/o Cage,
60m, 0.28mm ID, 0.25um
60m, 0.28mm ID, 0.25um 3.5"OD w/o Cage,
60m, 0.53mm ID, 0.25um
60m, 0.53mm ID, 0.25um w/5" 6850 Cage
60m, 0.53mm ID, 0.25um 5in coil banded w/copper wire
15m, 0.25mm ID, 0.50um
15m, 0.28mm ID, 0.50um
10m, 0.28mm ID, 0.50um 3.5"ID Coil w/o Cage
2 x 7.5m, 0.28mm ID, 0.50um 3.5"ID Coil w/o Cage
15m, 0.28mm ID, 0.50um 3.5"OD w/o Cage,
15m, 0.28mm ID, 0.50um 3.5"ID Coil w/o Cage
15m, 0.53mm ID, 0.50um
10m, 0.53mm ID, 0.50um
1-10m & 1-5m 0.53mm ID, 0.50um 3.5"ID w/out cage
15m, 0.53mm ID, 0.50um 3.5"OD w/o Cage,
30m, 0.25mm ID, 0.50um
25m, 0.25mm ID, 0.50um

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034



**HROMalytic** +61(0)3 9762 2034  
ECHnology Pty Ltd

**Australian Distributors**  
Importers & Manufacturers  
www.chromtech.net.au

Website NEW : [www.chromalytic.net.au](http://www.chromalytic.net.au) E-mail : [info@chromtech.net.au](mailto:info@chromtech.net.au) Tel: 03 9762 2034 . . . in AUSTRALIA



(Ctrl F)  
> Cat.#s

> Current System AUD Prices