

70569	MXT-50 Cap. Column	30m, 0.53mm ID, 0.83um
70569-10128	MXT-50 Cap. Column	3 x 10m, 0.53mm ID, 0.83um 3.5"ID C
70569-10228	MXT-50 Cap. Column	10 & 20m, 0.53mm ID, 0.83um 3.5" C
70569-11228	MXT-50 Cap. Column	20m, 0.53mm ID, 0.83um 3.5"ID w/out cage (3.5"ID,4.0"OD)
70569-273	MXT-50 Cap. Column	30m, 0.53mm ID, 0.83um 3.5"OD w/o Cage,
70569-283	MXT-50 Cap. Column	30m, 0.53mm ID, 0.83um 3.5"ID Coil w/o Cage
70570	MXT-50 Cap. Column	30m, 0.53mm ID, 1.50um
70570-273	MXT-50 Cap. Column	30m, 0.53mm ID, 1.50um 3.5"OD w/o Cage,
70570-283	MXT-50 Cap. Column	30m, 0.53mm ID, 1.50um 3.5"ID w/out cage
70573	MXT-50 Cap. Column	60m, 0.53mm ID, 1.50um
70605	MXT-WAX Cap. Column	15m, 0.25mm ID, 0.10um
70608	MXT-WAX Cap. Column	30m, 0.25mm ID, 0.10um
70608-273	MXT-WAX Cap. Column	30m, 0.25mm ID, 0.10um 3.5in OD w/out cage
70611	MXT-WAX Cap. Column	60m, 0.25mm ID, 0.10um
70620	MXT-WAX Cap. Column	15m, 0.25mm ID, 0.25um
70621	MXT-WAX Cap. Column	15m, 0.28mm ID, 0.25um
70622	MXT-WAX Cap. Column	15m, 0.53mm ID, 0.25um
70622-273	MXT-WAX Cap. Column	15m, 0.53mm ID, 0.25um 3.5in OD w/out cage
70623	MXT-WAX Cap. Column	30m, 0.25mm ID, 0.25um
70623-273	MXT-WAX Cap. Column	30m, 0.25mm ID, 0.25um 3.5"OD w/o Cage,
70623-283	MXT-WAX Cap. Column	30m, 0.25mm ID, 0.25um 3.5"ID Coil w/o Cage
70624	MXT-WAX Cap. Column	30m, 0.28mm ID, 0.25um
70624-273	MXT-WAX Cap. Column	30m, 0.28mm ID, 0.25um 3.5"OD w/o Cage,
70625	MXT-WAX Cap. Column	30m, 0.53mm ID, 0.25um
70625-273	MXT-WAX Cap. Column	30m, 0.53mm ID, 0.25um 3.5"OD w/o Cage,
70625-27360	MXT-WAX Cap. Column	30m, 0.53mm ID, 0.25um 3.5"OD w/o Cage, 0.5m loose at each end 6pk
70625-283	MXT-WAX Cap. Column	30m, 0.53mm ID, 0.25um 3.5"ID Coil, No Cage
70626	MXT-WAX Cap. Column	60m, 0.25mm ID, 0.25um
70626-271	MXT-WAX Cap. Column	60m, 0.25mm ID, 0.25um 6 inch Diameter Cage
70626-273	MXT-WAX Cap. Column	60m, 0.25mm ID, 0.25um 3.5"OD without cage, SRI GCs
70627	MXT-WAX Cap. Column	60m, 0.28mm ID, 0.25um
70627-271	MXT-WAX Cap. Column	60m, 0.28mm ID, 0.25um 6" Config w/Cage
70627-273	MXT-WAX Cap. Column	60m x 0.28mm x 0.25um 3.5"OD w/o Cage,
70628	MXT-WAX Cap. Column	60m, 0.53mm ID, 0.25um
70635	MXT-WAX Cap. Column	15m, 0.25mm ID, 0.50um
70636	MXT-WAX Cap. Column	15m, 0.28mm ID, 0.50um
70636-12328	MXT-WAX Cap. Column	1-10m & 1-5m, 0.28mm ID, 0.50um 3.5"ID w/out cage (3.5"ID/4.0"OD)
70636-283	MXT-WAX Cap. Column	15m, 0.28mm ID, 0.50um 3.5"ID Coil w/o Cage
70637	MXT-WAX Cap. Column	15m, 0.53mm ID, 0.50um
70637-095	MXT-WAX Cap. Column	2-2.5m and 2-5m, 0.53mm ID, 0.50um
70637-104	MXT-WAX Cap. Column	3 x 5m, 0.53mm ID, 0.50um
70637-10428	MXT-WAX Cap. Column	15m, 0.53mm ID, 0.50um Break Column into three 5m pieces 3 1/5 inch Diameter
70637-107	MXT-WAX Cap. Column	10m, 0.53mm ID, 0.50um
70637-10728	MXT-WAX Cap. Column	10m, 0.53mm ID, 0.50um 3.5"ID w/out cage
70637-12327	MXT-WAX Cap. Column	10m & 5m, 0.53mm ID, 0.50um 6" Coil
70637-12328	Mxt-WAX Cap. Column	10m and 5m, 0.53mm ID, 0.50um 3.5" ID without cage
70637-271	MXT-WAX Cap. Column	15m, 0.53mm ID, 0.50um 6" Coil
70637-273	MXT-WAX Cap. Column	15m, 0.53mm ID, 0.50um 3.5"OD w/o Cage,
70637-283	MXT-WAX Cap. Column	15m, 0.53mm ID, 0.50um 3.5"ID w/out cage (3.5"ID/4.0"OD)
70637-285	MXT-WAX Cap. Column	15m, 0.53mm ID, 0.50um Connect to G.Col w/LDV Conn.
70638	MXT-WAX Cap. Column	30m, 0.25mm ID, 0.50um
70638-273	MXT-WAX Cap. Column	30m, 0.25mm ID, 0.50um 3.5"OD w/o Cage,
70639	MXT-WAX Cap. Column	30m, 0.28mm ID, 0.50um
70639-10227	MXT-WAX Cap. Column	10m & 20m, 0.28mm ID, 0.50um 3.5"OD w/o Cage,
70639-273	MXT-WAX Cap. Column	30m, 0.28mm ID, 0.50um 3.5"OD w/o Cage,
70640	MXT-WAX Cap. Column	30m, 0.53mm ID, 0.50um
70640-074	MXT-WAX Cap. Column	5m/10m/15m, 0.53mm ID, 0.50um
70640-098	MXT-WAX Cap. Column	5m, 10m, 15m, 0.53mm ID, 0.50um Unconnected on Single Cage
70640-101	MXT-WAX Cap. Column	3 x 10m, 0.53mm ID, 0.50um
70640-102	MXT-WAX Cap. Column	10m & 20m, 0.53mm ID, 0.50um
70640-10228	MXT-WAX Cap. Column	10m & 20m, 0.53mm ID, 0.50um 3.5" ID Coil
70640-11227	MXT-WAX Cap. Column	20m, 0.53mm ID, 0.50um 6"Coil
70640-117	MXT-WAX Cap. Column	30m, 0.53mm ID, 0.50um Break into 2 x 5m and 1 x 20m Columns
70640-11728	MXT-WAX Cap. Column	(2)5m, (1)20m 0.53mm ID, 0.50um 3.5" ID Coil
70640-271	MXT-WAX Cap. Column	30m, 0.53mm ID, 0.50um 6"Coil
70640-273	MXT-WAX Cap. Column	30m, 0.53mm ID, 0.50um 3.5"OD w/o Cage,

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034

 HROMalytic +61(0)3 9762 2034 ECHnology Pty Ltd		Australian Distributors Importers & Manufacturers www.chromtech.net.au
Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA		

[Ctrl F]
> Cat.#s

> Current System AUD Prices

