

70640-2730	MXT-WAX Cap. Column
70640-283	MXT-WAX Cap. Column
70640-2830	MXT-WAX Cap. Column
70640-6850M	MXT-WAX Cap. Column
70641	MXT-WAX Cap. Column
70642	MXT-WAX Cap. Column
70642-10928	MXT-WAX Cap. Column
70642-271	MXT-WAX Cap. Column
70642-273	MXT-WAX Cap. Column
70643	MXT-WAX Cap. Column
70643-271	MXT-WAX Cap. Column
70643-273	MXT-WAX Cap. Column
70651	MXT-WAX Cap. Column
70651-10728	MXT-WAX Cap. Column
70651-123	MXT-WAX Cap. Column
70651-271	MXT-WAX Cap. Column
70651-273	MXT-WAX Cap. Column
70651-283	MXT-WAX Cap. Column
70652	MXT-WAX Cap. Column
70652-095	MXT-WAX Cap. Column
70652-09528	MXT-WAX Cap. Column
70652-104	MXT-WAX Cap. Column
70652-10427	MXT-WAX Cap. Column
70652-10428	MXT-WAX Cap. Column
70652-10428	MXT-WAX Cap. Column
70652-107	MXT-WAX Cap. Column
70652-10727	MXT-WAX Cap. Column
70652-10727	MXT-WAX Cap. Column
70652-10728	MXT-WAX Cap. Column
70652-10728	MXT-WAX Cap. Column
70652-10760	MXT-WAX Cap. Column
70652-123	MXT-WAX Cap. Column
70652-12327	MXT-WAX Cap. Column
70652-12328	MXT-WAX Cap. Column
70652-271	MXT-WAX Cap. Column
70652-272	MXT-WAX Cap. Column
70652-27260	MXT-WAX Cap. Column
70652-273	MXT-WAX Cap. Column
70652-283	MXT-WAX Cap. Column
70652-28335	MXT-WAX Cap. Column
70652-600	MXT-WAX Cap. Column
70654	MXT-WAX Cap. Column
70654-10128	MXT-WAX Cap. Column
70654-141	MXT-WAX Cap. Column
70654-271	MXT-WAX Cap. Column
70654-273	MXT-WAX Cap. Column
70654-283	MXT-WAX Cap. Column
70655	MXT-WAX Cap. Column
70655-083	MXT-WAX Cap. Column
70655-101	MXT-WAX Cap. Column
70655-10128	MXT-WAX Cap. Column
70655-102	MXT-WAX Cap. Column
70655-10228	MXT-WAX Cap. Column
70655-106	MXT-WAX Cap. Column
70655-10627	MXT-WAX Cap. Column
70655-10628	MXT-WAX Cap. Column
70655-111	MXT-WAX Cap. Column
70655-112	MXT-WAX Cap. Column
70655-11227	MXT-WAX Cap. Column
70655-122	MXT-WAX Cap. Column
70655-271	MXT-WAX Cap. Column
70655-272	MXT-WAX Cap. Column
70655-273	MXT-WAX Cap. Column
70655-283	MXT-WAX Cap. Column
70655-2830	MXT-WAX Cap. Column
70655-2831	MXT-WAX Cap. Column

30m, 0.53mm ID, 0.50um 3.5in OD cc
30m, 0.53mm ID, 0.50um 3.5" ID Coil
30m, 0.53mm ID, 0.50um 3.5"ID Coil, Banded w/ Copper Wire
30m, 0.53mm ID, 0.50um 5"ID Coil Banded w/Copper Wire
60m, 0.25mm ID, 0.50um
60m, 0.28mm ID, 0.50um
10m & 50m, 0.28mm ID, 0.50um 3.5"ID Coil w/o Cage
60m, 0.28mm ID, 0.50um 6" Config w/Cage
60m, 0.28mm ID, 0.50um 3.5"OD w/o Cage,
60m, 0.53mm ID, 0.50um
60m, 0.53mm ID, 0.50um 6"Coil
60m, 0.53mmID, 0.50um 3.5"OD w/o Cage,
15m, 0.28mm ID, 1.00um
10m, 0.28mm ID, 1.00um 3.5"ID w/o cage
10m and 5m, 0.28mm ID, 1.00um
15m, 0.28mm ID, 1.00um 6" Coil
15m, 0.28mm ID, 1.0um 3.5"OD w/o Cage,
15m, 0.28mm ID, 1.00um 3.5 "ID w/o cage
15m, 0.53mm ID, 1.00um
15m, 0.53mmID, 1.00um Break into 2,2 1/2m columns and 2 5m columns
2 x 2.5m, 2 x 5m 0.53mm ID, 1.00um 3.5"ID Coil w/o Cage
3 x 5m, 0.53mm ID, 1.00um
3 x 5m, 0.53mmID, 1.00um 6" Configuration for MXT column w/o cage
3 x 5m, 0.53mm ID, 1.00um 3.5" ID Coil
3 x 5m, 0.53mm ID, 1.00um 3.5"ID without cage w/ 18" coils
10m, 0.53mm ID, 1.00um
10m, 0.53mm ID, 1.00um 6"Coil
10m, 0.53mm ID, 1.00um 3.5"Coil
10m, 0.53mm ID, 1.00um 3.5"OD w/o Cage, 0.5m loose at each end
10m, 0.53mmID, 1.00um 3.5"ID Coil,banded w/ copper wire (3.5"ID/4.0"OD)
10m, 0.53mm ID, 1.00um Pack of 6
5m & 10m, 0.53mm ID, 1.00um
15m, 0.53mm ID, 1.00um w/(1)10m & (1)5m w 6" Config
5m & 10m, 0.53mmID, 1.0um, 3.5" Inside Diameter
15m, 0.53mm ID, 1.00um 6"Coil
15m, 0.53mm ID, 1.00um 4.5"Coil
15m, 0.53mm ID, 1.00um 4.5" Coil Pack of 6
15m, 0.53mm ID, 1.00um 3.5"OD w/o Cage,
15m, 0.53mm ID, 1.00um 3.5" ID Coil
15m, 0.53mm ID, 1.00um 3.5"IDCoil w/5m,MXTGC/LDV Conn
15m, 0.53mm ID, 1.00um Pack of 6
30m, 0.28mm ID, 1.00um
3 x 10m, 0.28mm ID, 1.00um 3.5" ID w/o Cage
2 5m and 2 10m, 0.28mm ID, 1.00um
30m, 0.28mm ID, 1.0um 6"Coil
30m, 0.28mm ID, 1.00um 3.5"OD w/o Cage,
30m, 0.28mm ID, 1.00um 3.5" ID Coil
30m, 0.53mm ID, 1.00um
2m, 3m, 25m, 0.53mm ID, 1.00um
3-10m, 0.53mm ID, 1.00um
3 x 10m, .53mmID, 1.0um 3.5" Config
10m & 20m, 0.53mm ID, 1.00um
10m & 20m, 0.53mm ID, 1.00um 3.5" ID Coil
25m, 0.53mm ID, 1.00um
25m, 0.53mm ID, 1.00um 3.5"OD w/o Cage,
25m, 0.53mm ID, 1.00um 3.5" ID Coil
2 x 15m, 0.53mm ID, 1.00um
20m, 0.53mm ID, 1.00um
20m, 0.53mm ID, 1.0um 4.5"ID Coil w/o Cage
15x10x5, 0.53mm ID, 1.00um
30m, 0.53mm ID, 1.00um 6" Coil
30m, 0.53mm ID, 1.00um 4.5" Coil
30m, 0.53mm ID, 1.00um 3.5"OD w/o Cage,
30m, 0.53mm ID, 1.00um 3.5" ID Coil
30m, 0.53mm ID, 1.00um 3.5" Coil Banded w/Copper Wire
30m, 0.53mm ID, 1.00um 3.5"ID without cage w/ 18" leads

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034



HROMalytic +61(0)3 9762 2034

ECHnology Pty Ltd

Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA

Australian Distributors
Importers & Manufacturers
www.chromtech.net.au

