

70655-600 MXT-WAX Cap. Column
 70655-6850M MXT-WAX Cap. Column
 70657 MXT-WAX Cap. Column
 70657-10528 MXT-WAX Cap. Column
 70657-121 MXT-WAX Cap. Column
 70657-271 MXT-WAX Cap. Column
 70657-273 MXT-WAX Cap. Column
 70657-283 MXT-WAX Cap. Column
 70658 MXT-WAX Cap. Column
 70658-068 MXT-WAX Cap. Column
 70658-105 MXT-WAX Cap. Column
 70658-10527 MXT-WAX Cap. Column
 70658-10527 MXT-WAX Cap. Column
 70658-10528 MXT-WAX Cap. Column
 70658-109 MXT-WAX Cap. Column
 70658-10928 MXT-WAX Cap. Column
 70658-11528 MXT-WAX Cap. Column
 70658-120 MXT-WAX Cap. Column
 70658-13227 MXT-WAX Cap. Column
 70658-138 MXT-WAX Cap. Column
 70658-140 MXT-WAX Cap. Column
 70658-271 MXT-WAX Cap. Column
 70658-272 MXT-WAX Cap. Column
 70658-273 MXT-WAX Cap. Column
 70658-276 MXT-WAX Cap. Column
 70658-277 MXT-WAX Cap. Column
 70658-283 MXT-WAX Cap. Column
 70658-351 MXT-WAX Cap. Column
 70658-600 MXT-WAX Cap. Column
 70666 MXT-WAX Cap. Column
 70666-104 MXT-WAX Cap. Column
 70666-12328 MXT-WAX Cap. Column
 70666-271 MXT-WAX Cap. Column
 70666-273 MXT-WAX Cap. Column
 70666-283 MXT-WAX Cap. Column
 70667 MXT-WAX Cap. Column
 70667-104 MXT-WAX Cap. Column
 70667-107 MXT-WAX Cap. Column
 70667-10728 MXT-WAX Cap. Column
 70667-123 MXT-WAX Cap. Column
 70667-12327 MXT-WAX Cap. Column
 70667-12327 MXT-WAX Cap. Column
 70667-143 MXT-WAX Cap. Column
 70667-272 MXT-WAX Cap. Column
 70667-273 MXT-WAX Cap. Column
 70667-274 MXT-WAX Cap. Column
 70667-2740 MXT-WAX Cap. Column
 70667-283 MXT-WAX Cap. Column
 70667-600 MXT-WAX Cap. Column
 70669 MXT-WAX Cap. Column
 70669-072 MXT-WAX Cap. Column
 70669-101 MXT-WAX Cap. Column
 70669-271 MXT-WAX Cap. Column
 70669-273 MXT-WAX Cap. Column
 70669-274 MXT-WAX Cap. Column
 70669-283 MXT-WAX Cap. Column
 70670 MXT-WAX Cap. Column
 70670-101 MXT-WAX Cap. Column
 70670-102 MXT-WAX Cap. Column
 70670-10227 MXT-WAX Cap. Column
 70670-10228 MXT-WAX Cap. Column
 70670-10627 MXT-WAX Cap. Column
 70670-111 MXT-WAX Cap. Column
 70670-112 MXT-WAX Cap. Column
 70670-122 MXT-WAX Cap. Column
 70670-271 MXT-WAX Cap. Column

Page 165
 30m, 0.53mm ID, 1.00um Pack of 6
 30m, 0.53mm ID, 1.00um 5" Coil, Bar
 60m, 0.28mm ID, 1.00um
 50m, 0.28mm ID, 1.00um 3.5" ID Coil
 40m & 2x10m, 0.28mm ID, 1.00um
 60m, 0.28mm ID, 1.00um 6" Conf w/out cage
 60m, 0.28mm ID, 1.00um 3.5"OD w/o Cage,
 60m, 0.28mm ID, 1.00um 3.5" ID Coil
 60m, 0.53mm ID, 1.00um
 22m & 38m, 0.53mm ID, 1.00um
 50m, 0.53mm ID, 1.00um
 50m, 0.53mm ID, 1.00um 6" Coil
 50m, 0.53mm ID, 1.00um 4.5in OD without Cage
 50m, 0.53mm ID, 1.00um 3.5" ID Coil
 50m & 10m, 0.53mm ID, 1.00um
 50m & 10m, 0.53mm ID, 1.00um 3.5" ID Coil
 40m & 20m, 0.53mm ID, 1.00um 3.5" ID Coil
 30m & 20m & 10m, 0.53mm ID, 1.00um
 2x25m, 1x10m, 0.53mm ID, 1.00um 6" Coil
 15m, 45m, 0.53mm ID, 1.00um
 45m, 0.53mm ID, 1.00um
 60m, 0.53mm ID, 1.00um 6" Coil
 60m, 0.53mm ID, 1.00um 4.5" Coil
 60m, 0.53mm ID, 1.00um 3.5"OD w/o Cage,
 60m, 0.53mm ID, 1.00um 6" Coil
 60m, 0.53mm ID, 1.00um 7" Coil
 60m, 0.53mm ID, 1.00um 3.5" ID Coil
 60m, 0.53mm ID, 1.00um w/5m, 0.53mm ID MXT GC LDV Connector
 60m, 0.53mm ID, 1.00um Pack of 6
 15m, 0.53mm ID, 1.50um
 3x5m, 0.53mm ID, 1.50um
 5m & 10m, 0.53mm ID, 1.50um 3.5" Coil
 15m, 0.53mm ID, 1.50um 6" Configuration w/o Cage
 15m, 0.53mm ID, 1.50um 3.5"OD w/o Cage,
 15m, 0.53mm ID, 1.50um 3.5" ID Coil
 15m, 0.53mm ID, 2.00um
 3 x 5m, 0.53mm ID, 2.00um
 10m, 0.53mm ID, 2.00um
 10m, 0.53mm ID, 2.00um 3.5" ID Coil
 10m & 5m, 0.53mm ID, 2.00um
 10m & 5m, 0.53mm ID, 2.00um 3.5"OD banded w/copper wire
 1-10m & 1-5m, 0.53mm ID, 2.00um 2.5"OD coil banded with copper wire
 12.5m, 0.53mm ID, 2.00um
 15m, 0.53mm ID, 2.00um 4.5" ID w/out Cage
 15m, 0.53mm ID, 2.00um 3.5"OD w/o Cage
 15m, 0.53mm ID, 2.00um coil into 2 1/2"OD w/out cage
 15m, 0.53mm ID, 2.00um 2.5: OD Coil Banded w/ copper wire
 15m, 0.53mm ID, 2.00um 3.5" ID Coil
 15m, 0.53mm ID, 2.00um 6pk
 30m, 0.53mm ID, 1.50um
 30m, 0.53mm ID, 1.50um Wind on Styrofoam reel
 3 X 10m, 0.53mm ID, 1.50um
 30m, 0.53mm ID, 1.50um 6" Config. w/o Cage
 30m, 0.53mm ID, 1.50um 3.5"OD w/o Cage
 30m, 0.53mm ID, 1.50um 2.5" Coil
 30m, 0.53mm ID, 1.50um 3.5" Inside Diameter Coil w/o Cage
 30m, 0.53mm ID, 2.00um
 3 x 10m, 0.53mm ID, 2.0um
 10m & 20m, 0.53mm ID, 2.00um
 10m & 20m, 0.53mm ID, 2.00um 3.5"OD w/o Cage
 10m & 20m, 0.53mm ID, 2.00um 3.5" Inside Diameter w/o Cage
 25m, 0.53mm ID, 2.0um 3.5"OD w/o Cage
 2 x 15m, 0.53mm ID, 2.00um
 20m, 0.53mm ID, 2.00um
 5m, 10m, 15m, 0.53mm ID, 2.00um
 30m, 0.53mm ID, 2.00um 6"Coil

[Ctrl F]
 > Cat.#s

> Current System AUD Prices



Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034

		+61(0)3 9762 2034 ECH nology Pty Ltd	Australian Distributors Importers & Manufacturers www.chromtech.net.au
Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA			