

72054	MXT-1701 Cap. Column
72054-271	MXT-1701 Cap. Column
72055	MXT-1701 Cap. Column
72055-273	MXT-1701 Cap. Column
72055-283	MXT-1701 Cap. Column
72055-6850M	MXT-1701 Cap. Column
72056	MXT-1701 Cap. Column
72057	MXT-1701 Cap. Column
72058	MXT-1701 Cap. Column
72058-105	MXT-1701 Cap. Column
72058-10527	MXT-1701 Cap. Column
72058-109	MXT-1701 Cap. Column
72058-273	MXT-1701 Cap. Column
72058-283	MXT-1701 Cap. Column
72066	MXT-1701 Cap. Column
72067	MXT-1701 Cap. Column
72069	MXT-1701 Cap. Column
72069-272	MXT-1701 Cap. Column
72070	MXT-1701 Cap. Column
72070-273	MXT-1701 Cap. Column
72070-283	MXT-1701 Cap. Column
72072	MXT-1701 Cap. Column
72073	MXT-1701 Cap. Column
72073-283	MXT-1701 Cap. Column
72082	MXT-1701 Cap. Column
72082-107	MXT-1701 Cap. Column
72082-271	MXT-1701 Cap. Column
72085	MXT-1701 Cap. Column
72085-101	MXT-1701 Cap. Column
72085-112	MXT-1701 Cap. Column
72085-271	MXT-1701 Cap. Column
72085-272	MXT-1701 Cap. Column
72085-283	MXT-1701 Cap. Column
72088	MXT-1701 Cap. Column
72088-109	MXT-1701 Cap. Column
72088-118	MXT-1701 Cap. Column
72088-271	MXT-1701 Cap. Column
72088-283	MXT-1701 Cap. Column
72088-351	MXT-1701 Cap. Column
73198	MXT-1 Cap. Column
75035	MXT-200 Cap. Column
75038	MXT-200 Cap. Column
75038-273	MXT-200 Cap. Column
75050	MXT-200 Cap. Column
75052	MXT-200 Cap. Column
75052-07027	MXT-200 Cap. Column
75052-10727	MXT-200 Cap. Column
75052-273	MXT-200 Cap. Column
75052-2730	MXT-200 Cap. Column
75052-283	MXT-200 Cap. Column
75052-2830	MXT-200 Cap. Column
75052-6850M	MXT-200 Cap. Column
75053	MXT-200 Cap. Column
75053-272	MXT-200 Cap. Column
75053-2740	MXT-200 Cap. Column
75053-2760	MXT-200 Cap. Column
75055	MXT-200 Cap. Column
75055-112	MXT-200 Cap. Column
75055-11227	MXT-200 Cap. Column
75055-273	MXT-200 Cap. Column
75055-283	MXT-200 Cap. Column
75058	MXT-200 Cap. Column
75058-283	MXT-200 Cap. Column
75067	MXT-200 Cap. Column
75067-051	MXT-200 Cap. Column
75067-273	MXT-200 Cap. Column

30m, 0.28mm ID, 1.00um
30m, .028mm ID, 1.00um 6 inch Diarr
30m, 0.53mm ID, 1.00um
30m, 0.53mm ID, 1.00um 3.5"OD w/o Cage
30m, 0.53mm ID, 1.00um 3.5" ID Coil
30m, 0.53mm ID, 1.00um 5in coil banded w/copper wire
60m, 0.25mm ID, 1.00um
60m, 0.28mm ID, 1.00um
60m, 0.53mm ID, 1.00um
50m, 0.53mm ID, 1.00um
50m, 0.53mm ID, 1.00um 6"Coil
10m & 50m, 0.53mmID, 1.00um
60m, 0.53mmID, 1.00um 3.5"OD w/o Cage
60m, 0.53mm ID, 1.00um 3.5" ID Coil
15m, 0.28mm ID, 1.50um
15m, 0.53mm ID, 1.50um
30m, 0.28mm ID, 1.50um
30m, 0.28mm ID, 1.50um Coiled 4.5" ID without cage
30m, 0.53mm ID, 1.50um
30m, 0.53mm ID, 1.50um 3.5"OD w/o Cage
30m, 0.53mm ID, 1.50um 3.5" ID Coil
60m, 0.28mm ID, 1.50um
60m, 0.53mm ID, 1.50um
60m, 0.53mm ID, 1.50um 3.5" ID Coil
15m, 0.53mm ID, 3.00um
10m, 0.53mm ID, 3.00um
15m, 0.53mm ID, 3.00um 6"Coil
30m, 0.53mm ID, 3.00um
Three 10m, 0.53mm ID, 3.00um
20m, 0.53mm ID, 3.00um
30m, 0.53mm ID, 3.00um 6"Coil
30m, 0.53mm ID, 3.00um No Cage
30m, 0.53mm ID, 3.00um 3.5" ID Coil
60m, 0.53mm ID, 3.00um
10m and 50m, 0.53mm ID, 3.00um
2 x 30m, 0.53mm ID, 3.00um
60m, 0.53mm ID, 3.00um 6"Coil
60m, 0.53mmID, 3.0um 3.5" Inside Diameter w/Cage
60m, 0.53mm ID, 3.00um Connect 5m, 0.53mm ID GC Use LDV Connector
30m, 0.32mm ID, 4.00um
15m, 0.25mm ID, 0.50um
30m, 0.25mm ID, 0.50um
30m, 0.25mm ID, 0.50um 3.5"OD w/o Cage
15m, 0.25mm ID, 1.00um
15m, 0.53mm ID, 1.00um
10m and 2 x 2.5m, 0.53mm ID, 1.00um 4 1/2"ID coil banded w/copper wire
10m, 0.53mm ID, 1.00um 4 1/2"ID banded w/copper wire (4.5"ID,5.0"OD)
15m, 0.53mm ID, 1.00um 3.5"OD w/o Cage
15m, 0.53mmID 1.00um 3.5"OD banded w/copper wire
15m, 0.53mm ID, 1.00um 3.5"ID w/out cage (3.5"ID/4.0"OD)
15m, 0.53mm ID, 1.00um 3.5"ID Coil Banded w/Copper Wire
15m, 0.53mm ID, 1.00um 5" Coil w/Copper Wire
30m, 0.25mm ID, 1.00um
30m, 0.25mm ID, 1.00um 4 1/2in OD w/out cage
30m, 0.25mm ID, 1.00um 2.5"OD Coil Banded w/Copper Wire
30m, 0.25mm ID, 1.00um 6"ID Coil, Banded with Copper Wire
30m, 0.53mm ID, 1.00um
30m, 0.53mmID, 1.00um Break 30m into 20m column
20m, 0.53mmID, 1.00um 3.5"OD w/o Cage
30m, 0.53mm ID, 1.00um 3.5"OD w/o Cage
30m, 0.53mm ID, 1.00um 3.5" inside diameter
60m, 0.53mm ID, 1.00um
60m, 0.53mmID, 1.0um 3.5" inside diameter
15m, 0.53mm ID, 1.50um
15m, 0.53mm ID, 1.50um No cage (no guarantee for breakage)
15m, 0.53mm ID, 1.50um 3.5"OD w/o Cage

