

75070	MXT-200 Cap. Column
75070-273	MXT-200 Cap. Column
75070-2730	MXT-200 Cap. Column
75073	MXT-200 Cap. Column
75073-273	MXT-200 Cap. Column
75073-2730	MXT-200 Cap. Column
75073-277	MXT-200 Cap. Column
75073-2770	MXT-200 Cap. Column
75082	MXT-200 Cap. Column
75082-10727	MXT-200 Cap. Column
75082-12327	MXT-200 Cap. Column
75082-273	MXT-200 Cap. Column
75082-2730	MXT-200 Cap. Column
75082-277	MXT-200 Cap. Column
75082-283	MXT-200 Cap. Column
75085	MXT-200 Cap. Column
75085-072	MXT-200 Cap. Column
75085-112	MXT-200 Cap. Column
75085-271	MXT-200 Cap. Column
75085-272	MXT-200 Cap. Column
75085-2720	MXT-200 Cap. Column
75085-273	MXT-200 Cap. Column
75085-283	MXT-200 Cap. Column
75085-6850M	MXT-200 Cap. Column
75088	MXT-200 Cap. Column
75088-078	MXT-200 Cap. Column
75088-109	MXT-200 Cap. Column
75088-138	MXT-200 Cap. Column
75088-271	MXT-200 Cap. Column
75088-272	MXT-200 Cap. Column
75088-273	MXT-200 Cap. Column
75088-277	MXT-200 Cap. Column
75088-283	MXT-200 Cap. Column
75091	MXT-200 Cap. Column
76020	MXT-1301 Cap. Column
76021	MXT-1301 Cap. Column
76022	MXT-1301 Cap. Column
76023	MXT-1301 Cap. Column
76024	MXT-1301 Cap. Column
76025	MXT-1301 Cap. Column
76026	MXT-1301 Cap. Column
76027	MXT-1301 Cap. Column
76028	MXT-1301 Cap. Column
76035	MXT-1301 Cap. Column
76036	MXT-1301 Cap. Column
76037	MXT-1301 Cap. Column
76038	MXT-1301 Cap. Column
76039	MXT-1301 Cap. Column
76040	MXT-1301 Cap. Column
76040-273	MXT-1301 Cap. Column
76041	MXT-1301 Cap. Column
76042	MXT-1301 Cap. Column
76042-273	MXT-1301 Cap. Column
76043	MXT-1301 Cap. Column
76050	MXT-1301 Cap. Column
76051	MXT-1301 Cap. Column
76052	MXT-1301 Cap. Column
76052-273	MXT-1301 Cap. Column
76053	MXT-1301 Cap. Column
76054	MXT-1301 Cap. Column
76055	MXT-1301 Cap. Column
76055-273	MXT-1301 Cap. Column
76055-283	MXT-1301 Cap. Column
76056	MXT-1301 Cap. Column
76057	MXT-1301 Cap. Column
76057-283	MXT-1301 Cap. Column

30m, 0.53mm ID, 1.50um
30m, 0.53mm ID, 1.5um 3.5"OD w/o Cage
30m, 0.53mm ID, 1.50um 3.5in OD banded w/copper wire
60m, 0.53mm ID, 1.50um
60m, 0.53mm ID, 1.50um 3.5"OD w/o Cage
60m, 0.53mm ID, 1.50um 3.5in OD banded w/copper wire
60m, 0.53mm ID, 1.50um Coil into 7.25"OD w/ out cage
60m, 0.53mm ID, 1.50um 7in coil banded w/copper wire
15m, 0.53mm ID, 3.00um
10m, 0.53mm ID, 3.00um 4 1/2"ID banded w/copper wire (4.5"ID,5.0"OD)
10m & 5m, 0.53mm ID, 3.00um 4 1/2"ID banded w/copper wire (4.5"ID,5.0"OD)
15m, 0.53mm ID, 3.00um 3.5"OD w/o Cage
15m, 0.53mm ID, 3.00um 3.5"OD banded w/copper wire 0.5m loose at each end
15m, 0.53mm ID, 3.00um 7.25"OD Coil without cage
15m, 0.53mm ID, 3.00um 3.5" ID w/o Cage
30m, 0.53mm ID, 3.00um
30m, 0.53mm ID, 3.00um Wind on a styrofoam reel
20m, 0.53mm ID, 3.00um
30m, 0.53mm ID, 3.00um 6"Coil
30m, 0.53mm ID, 3.00um 4.5"Coil
30m, 0.53mm ID, 3.00um 4 1/2"ID banded w/copper wire (4.5"ID,5.0"OD)
30m, 0.53mm ID, 3.00um 3.5"OD w/o Cage
30m, 0.53mm ID, 3.00um 3.5" Inside Diameter w/Cage
30m, 0.53mm ID, 3.00um 5.0"ID Coil Banded w/Copper Wire
60m, 0.53mm ID, 3.00um
2x2.5m, 2x5m, 1x10m, 1x15m, 1x20m, 0.53mm ID, 3.00um
50m and 10m, 0.53mm ID, 3.00um
45m and 15m, 0.53mm ID, 3.00um
60m, 0.53mm ID, 3.00um 6" Config w/o Cage
60m, 0.53mm ID, 3.00um 4.5"Coil
60m, 0.53mm ID, 3.00um 3.5"OD w/o Cage
60m, 0.53mm ID, 3.00um 7.25"OD Coil without cage
60m, 0.53mm ID, 3.00um 3.5" Inside Diameter w/Cage
105m, 0.53mm ID, 3.00um
15m, 0.25mm ID, 0.25um
15m, 0.28mm ID, 0.25um
15m, 0.53mm ID, 0.25um
30m, 0.25mm ID, 0.25um
30m, 0.28mm ID, 0.25um
30m, 0.53mm ID, 0.25um
60m, 0.25mm ID, 0.25um
60m, 0.28mm ID, 0.25um
60m, 0.53mm ID, 0.25um
15m, 0.25mm ID, 0.50um
15m, 0.28mm ID, 0.50um
15m, 0.53mm ID, 0.50um
30m, 0.25mm ID, 0.50um
30m, 0.28mm ID, 0.50um
30m, 0.53mm ID, 0.50um
30m, 0.53mm ID, 0.50um 3.5"OD w/o Cage
60m, 0.25mm ID, 0.50um
60m, 0.28mm ID, 0.50um
60m, 0.28mm ID, 0.50um 3.5"OD w/o Cage
60m, 0.53mm ID, 0.50um
15m, 0.25mm ID, 1.00um
15m, 0.28mm ID, 1.00um
15m, 0.53mm ID, 1.00um
15m, 0.53mm ID, 1.00um 3.5" Coil w/out cage
30m, 0.25mm ID, 1.00um
30m, 0.28mm ID, 1.00um
30m, 0.53mm ID, 1.00um
30m, 0.53mm ID, 1.00um 3.5"OD w/o Cage
30m, 0.53mm ID, 1.00um 3.5" ID Coil
60m, 0.25mm ID, 1.00um
60m, 0.28mm ID, 1.00um
60m, 0.28mm ID, 1.00um 3.5in ID w/out cage

(Ctrl F)
> Cat.#s

> Current System AUD Prices

