

76058	MXT-1301 Cap. Column	60m, 0.53mm ID, 1.00um
76066	MXT-1301 Cap. Column	15m, 0.28mm ID, 1.50um
76067	MXT-1301 Cap. Column	15m, 0.53mm ID, 1.50um
76067-283	MXT-1301 Cap. Column	15m, 0.53mm ID, 1.50um 3.5" ID Coil
76069	MXT-1301 Cap. Column	30m, 0.28mm ID, 1.50um
76070	MXT-1301 Cap. Column	30m, 0.53mm ID, 1.50um
76072	MXT-1301 Cap. Column	60m, 0.28mm ID, 1.50um
76073	MXT-1301 Cap. Column	60m, 0.53mm ID, 1.50um
76073-283	MXT-1301 Cap. Column	60m, 0.53mm ID, 1.50um 3.5" ID Coil
76082	MXT-1301 Cap. Column	15m, 0.53mm ID, 3.00um
76082-104	MXT-1301 Cap. Column	3x5m, 0.53mm ID, 3.00um
76082-107	MXT-1301 Cap. Column	10m, 0.53mm ID, 3.00um
76082-273	MXT-1301 Cap. Column	15m, 0.53mm ID, 3.00um 3.5in OD w/out cage
76082-283	MXT-1301 Cap. Column	15m, 0.53mm ID, 3.00um 3.5" ID Coil
76085	MXT-1301 Cap. Column	30m, 0.53mm ID, 3.00um
76085-273	MXT-1301 Cap. Column	30m, 0.53mm, 3.00um 3.5"OD w/o Cage
76085-283	MXT-1301 Cap. Column	30m, 0.53mm ID, 3.00um 3.5" ID Coil
76088	MXT-1301 Cap. Column	60m, 0.53mm ID, 3.00um
76088-105283	MXT-1301 Cap. Column	50m, 0.53mm ID, 3.00um 3.5" ID Coil
76088-273	MXT-1301 Cap. Column	60m, 0.53mm ID, 3.00um 3.5"OD w/o Cage
76088-283	MXT-1301 Cap. Column	60m, 0.53mm ID, 3.00um 3.5" ID Coil
76088-351	MXT-1301 Cap. Column	60m, 0.53mm ID, 3.00um w/5m, 0.53mm Guard&MXTLDV Con.
77005	MXT-65TG Cap. Column	15m, 0.25mm ID, 0.10um
77005-107	MXT-65TG Cap. Column	10m, 0.25mm ID, 0.10um
77007	MXT-65TG Cap. Column	15m, 0.53mm ID, 0.10um
77008	MXT-65TG Cap. Column	30m, 0.25mm ID, 0.10um
77008-112	MXT-65TG Cap. Column	20m, 0.25mm ID, 0.10um
77010	MXT-65TG Cap. Column	30m, 0.53mm ID, 0.10um
77010-273	MXT-65TG Cap. Column	30m, 0.53mm ID, 0.10um 3.5"OD w/o Cage
77020	MXT-65 Cap. Column	15m, 0.25mm ID, 0.25um
77023	MXT-65 Cap. Column	30m, 0.25mm ID, 0.25um
77035	MXT-65 Cap. Column	15m, 0.25mm ID, 0.50um
77038	MXT-65 Cap. Column	30m, 0.25mm ID, 0.50um
77050	MXT-65 Cap. Column	15m, 0.25mm ID, 1.00um
77053	MXT-65 Cap. Column	30m, 0.25mm ID, 1.00um
78000-272	MXT-BAC2 Cap. Column	30m, 0.53mm ID, 2.00um Recoil to 4 1/2 inch Diameter No Cage
78000-6850M	MXT-BAC2 Cap. Column	30m, 0.53mm ID, 2.00um 5" Coil Banded w/Copper Wire
78001	MXT-BAC1 Cap. Column	30m, 0.53mm ID, 3.00um
78001-273	MXT-BAC1 Cap. Column	30m, 0.53mm ID, 3.00um 3.5"OD w/o Cage
78001-2830	MXT-BAC1 Cap. Column	30m, 0.53mmID, 3.00um 3.5"ID Coil w/Copper Bands
78001-6850M	MXT-BAC1 Cap. Column	30m, 0.53mm ID, 3.00um 5" Coil, Banded w/ Copper Wire
79712	MXT-S-BOND Column	30m, 0.53mmID, 20um
79712-273	MXT-S-BOND Column	30m, 0.53mmID, 20um, w/3.5" Coil
79714	MXT-Alumina BOND/Na2SO4	30m, 0.53mm ID, 10um
79714-111273	MXT-Alumina BOND/Na2SO4	2 - 15m, 0.53mm ID, 10um SRI GCs 3.5" OD w/o Cage
79714-273	MXT-Alumina BOND / Na2SO4	30m, 0.53mm ID, 10um 3.5" Config
79716	MXT-Q-BOND Column	30m, 0.53mmID, 20um
79718	MXT-Q-BOND Column	15m, 0.25mm ID, 8um
79718-273	MXT-Q BOND Column	15m, 0.25mm ID, 8um 3.5" OD without cage
79723	MXT-Msieve 5A Plot Column	30m, 0.53mm ID, 50um CAN NOT RECONFIGURE/RECOIL
79723-273	MXT-Msieve 5A PLOT Column	30m, 0.53mm ID, 50um 3.5" Config
79728	MXT-Alumina BOND/MAPD	30m, 0.53mm ID, 10um
80000-800	Packed Column	Rtx-1HT SIMDIST 2887 PC 25", 2mmID Silco General Configuration, OnCol
80000-810	Packed Column	Rtx-1HT SIMDIST 2887 PC 25", 2mmID, Silco Hewlett Packard
80000-81090	Packed Column	Rtx-SIMDIST 2887PC 25", 2mm, Silco, NOC
80000-840	Packed Column	Rtx-1HT SIMDIST 2887 PC 25", 2mmID, Silco PE Autosys
80105-800	Packed Column	5% Carbowax 20M CBK B 80/120 2m, 2mmID, Silco General Configuration, OnCol
80105-80090	Packed Column	5% Carbowax 20M CBK B 80/120 2m, 2mmID, NOC, Silco
80105-810	Packed Column	5% Carbowax 20M CBK B 80/120 2m, 2mmID Hewlett Packard
80105-81090	Packed Column	5% Carbowax 20M CBK B 80/120 2m, 2mmID, HP, Preconditioned
80105-81090	Packed Column	5% Carbowax 20M CBK B 80/120 2m 2mm ID HP NOC
80105-811	Packed Column	5% Carbowax 20M CBK B 80/120 2m 2mmID Silco HP 6850
80105-820	Packed Column	5% Carbowax 20M CBK B 80/120 2m, 2mmID Varian 3700, Vista Series, FID
80105-821	Packed Column	5% Carbowax 20M CBK B 80/120 2m, 2mmID, Silco, OnCol, Varian 3800
80105-830	Packed Column	5% Carbowax 20M CBK B 80/120 2m, 2mmID PE 900-3920, Sigma 1,2,3
80105-83090	Packed Column	5% Carbowax 20M CBK B 80/120 2m, 2mm ID PE 900-3920 Sigma 1,2,3 NOC

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034

 <b>HROMalytic</b> +61(0)3 9762 2034 <b>ECHnology</b> Pty Ltd		<b>Australian Distributors</b> Importers & Manufacturers <a href="http://www.chromtech.net.au">www.chromtech.net.au</a>
Website NEW : <a href="http://www.chromalytic.net.au">www.chromalytic.net.au</a> E-mail : <a href="mailto:info@chromtech.net.au">info@chromtech.net.au</a> Tel: 03 9762 2034 . . . in AUSTRALIA		

[Ctrl F]  
> Cat.#s

> Current System AUD Prices

