



> Current System AUD Prices

80105-840	Packed Column	5% Carbowax 20M CBK B 80/120 2m
80105-850	Packed Column	5% Carbowax 20M CBK B 80/120 2m
80105-853	Packed Column	5% Carbowax 20M CBK B 80/120 2m, 2mmID SRI 8610C
80105-895	Packed Column	5% Carbowax 20M CBK B 80/120 2m, 2mmID SRI 8610C
80105-896	Packed Column	5% Carbowax 20m CarboBlack B
80106-800	Packed Column	5% Carbowax 20M CBK B 60/80 1.8m 2mmID General Configuration, OnCol
80106-810	Packed Column	5% Carbowax 20M CBK B 60/80 1.8m, 2mmID Hewlett Packard
80106-81090	Packed Column	5% Carbowax 20M Carbbk B 60/80 1.8m, 2mm, Silco, NOC, HP
80106-820	Packed Column	5% Carbowax 20M CBK B 60/80 1.8m, 2mmID Varian 3700, Vista Series, FID
80106-830	Packed Column	5% Carbowax 20M CBK B 60/80 1.8m, 2mmID PE 900-3920, Sigma 1,2,3
80106-840	Packed Column	5% Carbowax 20M CBK B 60/80 1.8m, 2mmID PE Autosys
80106-845	Packed Column	5% Carbowax 20M CBK B 60/80 1.8m, 2mm ID ABB 3100
80106-850	Packed Column	5% Carbowax 20M CBK B 60/80 1.8m, 2mmID Shimadzu 17A
80106-851	Packed Column	5% Carbowax 20M CBK B 60/80 1.8m 2mm ID Shimadzu 8A
80106-892	Packed Column	5% Carbowax 20M CBK B 60/80 1.8m, 2mmID Gow MAC 750
80106-894	Packed Column	5% Carbowax 20M, Carboblack B 60/80 1.8m, 2mmID, Silco, OC, Gow Mac 580
80107-800	Packed Column	6.6% Carbowax 20M CBK B 80/120 2m, 2mmID General Configuration, OnCol
80107-810	Packed Column	6.6% Carbowax 20M CBK B 80/120 2m, 2mmID Hewlett Packard
80107-811	Packed Column	6.6% Carbowax 20M Carboblack B 80/120 2m, 2mm, Silco, ONCOL, HP6850
80107-820	Packed Column	6.6% Carbowax 20M CBK B 80/120 2m, 2mmID Varian 3700, Vista Series, FID
80107-830	Packed Column	6.6% Carbowax 20M CBK B 80/120 2m, 2mmID PE 900-3920, Sigma 1,2,3
80107-840	Packed Column	6.6% Carbowax 20M CBK B 80/120 2m, 2mmID OC/PE Autosys
80107-850	Packed Column	6.6% Carbowax 20M CBK B 80/120 2m 2mm ID Shimadzu 14A
80107-895	Packed Column	6.6% Carbowax 20M CBK B 80/120 2m, 2mmID SRI 8610C OC
80111-800	Packed Column	0.3% Carbowax 20M, 0.1% H3PO4 60/80 CBK C/0.75m,3/16"OD General Configi
80111-810	Packed Column	0.3% Carbowax 20M, 0.1% H3PO4 60/80 CBK C/0.75m,3/16"OD,4mm 60/80 CBK
80111-820	Packed Column	0.3% Carbowax 20M, 0.1% H3PO4 60/80 CBK C/0.75m,3/16"OD,4mm 60/80 CBK
80111-830	Packed Column	0.3% Carbowax 20M, 0.1% H3PO4 60/80 CBK C/0.75m,3/16"OD,4mm 60/80 CBK
80116-800	Packed Column	4% Carbowax 20M, 0.8% KOH CBKB 60/80 2m, 2mmID General Configuration, C
80116-810	Packed Column	4% Carbowax 20M, 0.8% KOH CBKB 60/80 2m, 2mmID Hewlett Packard
80116-81090	Packed Column	4% Carbowax 20M, 0.8% KOH CBKB 60/80 2m, 2mm ID HP NOC
80116-820	Packed Column	4% Carbowax 20M, 0.8% KOH CBKB 60/80 2m, 2mmID Varian 3700, Vista Serie:
80116-830	Packed Column	4% Carbowax 20M, 0.8% KOH CBKB 60/80 2m, 2mmID PE 900-3920, Sigma 1,2
80116-840	Packed Column	4% Carbowax 20M, 0.8% KOH CBKB 60/80 2m, 2mmID PE Autosys
80116-852	Packed Column	4% Carbowax 20M, 0.8% KOH CBKB 60/80 2m, 2mmID Shimadzu 9A, OC
80116-895	Packed Column	4% Carbowax 20M, 0.8% KOH CBKB 60/80 2m, 2mmID OC/SRI8610C
80116-896	Packed Column	4% Carbowax 20M, 0.8% KOH, Carboblack B 60/80 2m, 2mm, Silco
80121-800	Packed Column	0.2% Carbowax 1500 60/80 CBK C 2m, 2mmID General Configuration, OnCol
80121-810	Packed Column	0.2% Carbowax 1500 60/80 CBK C 2m, 2mmID Hewlett Packard
80121-81090	Packed Column	0.2% Carbowax 1500 60/80 CBK C 2m, 2mmID HP NOC
80121-820	Packed Column	0.2% Carbowax 1500 60/80 CBK C 2m, 2mmID Varian 3700, Vista Series, FID
80121-830	Packed Column	0.2% Carbowax 1500 60/80 CBK C 2m, 2mmID PE 900-3920, Sigma 1,2,3
80121-840	Packed Column	0.2% Carbowax 1500 60/80 CBK C 2m, 2mmID PE Autosys
80121-84090	Packed Column	0.2% Carbowax 1500 60/80 CBK C 2m, 2mmID Not on Column PE 8700
80122-800	Packed Column	0.2% Carbowax1500 80/100 CBK C 2m, 1/8"OD, 2mmID, Silco, General Configur
80122-810	Packed Column	0.2% Carbowax1500 80/100 CBK C 2m, 2mmID Hewlett Packard
80122-81090	Packed Column	0.2% Carbowax 1500 Carboblack C 80/100 2m, 1/8", Silco, NOC, HP
80122-820	Packed Column	0.2% Carbowax1500 80/100 CBK C 2m, 2mmID Varian 3700, Vista Series, FID
80122-830	Packed Column	0.2% Carbowax1500 80/100 CBK C 2m, 2mmID PE 900-3920, Sigma 1,2,3
80122-840	Packed Column	0.2% Carbowax1500 80/100 CBK C 2m, 2mmID PE Autosys
80122-850	Packed Column	0.2% Carbowax 1500, 80/100, CBK C, 2m, 2mmID, SILCO, For Shimadzu 14A, 2i
80125-800	Packed Column	5% Rt-1200 1.75% Bentone 34 Silcoport W 100/120 2m, 2mmID Silco, General C
80125-80090	Packed Column	5% Rt-1200 1.75% Bentone 34 Silcoport W 100/120 2m, 2mmID, Silco, NOC
80125-810	Packed Column	5% Rt-1200 1.75% Bentone 34 Silcoport W 100/120 2m, 2mmID Hewlett Packard
80125-820	Packed Column	5% Rt-1200 1.75% Bentone 34 Silcoport W 100/120 2m, 2mmID Varian 3700, Vis
80125-830	Packed Column	5% Rt-1200 1.75% Bentone 34 Silcoport W 100/120 2m, 2mmID PE 900-3920, Si
80125-83090	Packed Column	5% Rt-1200 1.75% Bentone 34 Silcoport W 100/120 2m, 2mm ID, NOC PE 900-3
80125-840	Packed Column	5% Rt-1200 1.75% Bentone 34 Silcoport W 100/120 2m, 2mmID PE Autosys
80125-84090	Packed Column	5% Rt-1200 1.75% Bentone 34 Silcoport W 100/120 2m 2mmID PE Autosys NOC
80125-845	Packed Column	5% Rt-1200 1.75% Bentone 34, Silcoport W 100/120, 2m, 2.0mm ID, Silco, ABB 31
80125-850	Packed Column	5% Rt-1200 1.75% Bentone 34 Silcoport W 100/120 2m, 2mmID Silco Shimadzu
80126-800	Packed Column	10%TCEP 100/120 Chromosorb PAW 2.5m, 2mmID Silco, General Configuration
80126-810	Packed Column	10%TCEP 100/120 Chromosorb PAW 2.5m, 2mmID Hewlett Packard
80126-820	Packed Column	10%TCEP 100/120 Chromosorb PAW 2.5m, 2mmID Varian 3700, Vista Series, FI
80126-830	Packed Column	10%TCEP 100/120 Chromosorb PAW 2.5m, 2mmID PE 900-3920, Sigma 1,2,3
80126-840	Packed Column	10% TCEP 100/120 Chromsorb PAW 2.5m, 2mmID, PE

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034

		+61(0)3 9762 2034 ECH nology Pty Ltd	Australian Distributors Importers & Manufacturers www.chromtech.net.au
Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . IN AUSTRALIA			