

| | | |
|-------------|---------------|--|
| 80211-800 | Packed Column | 3% Rt-1500 80/120 CarboBlack B 3.0 |
| 80211-810 | Packed Column | 3% Rt-1500 80/120 CarboBlack B 3.0 |
| 80211-820 | Packed Column | 3% Rt-1500 80/120 CarboBlack B 3.0 |
| 80211-830 | Packed Column | 3% Rt-1500 80/120 CarboBlack B 3.05m, 2mmID PE 900-3920, Sigma 1,2,3 |
| 80211-840 | Packed Column | 3% Rt-1500 80/120 CarboBlack B 3.05m, 2mmID PE Autosys |
| 80211-850 | Packed Column | 3% Rt-1500 80/120 CarboBlack B 3.05m, 2mmID, Shimadzu 14A, 2014 |
| 80211-895 | Packed Column | 3% Rt-1500 80/120 CarboBlack B 3.05m, 2mmID, SRI 8610C |
| 80216-800 | Packed Column | 1% Rt-1510 60/80 CarboBlack B 3.05m, 2mmID General Configuration |
| 80216-810 | Packed Column | 1% Rt-1510 60/80 CarboBlack B 3.05m, 2mmID Hewlett Packard |
| 80216-81090 | Packed Column | 1% Rt-1510 60/80 CarboBlack B 3.05m, 2mm ID, HP, Pre-Conditioning |
| 80216-820 | Packed Column | 1% Rt-1510 60/80 CarboBlack B 3.05m, 2mmID Varian |
| 80216-830 | Packed Column | 1% Rt-1510 60/80 CarboBlack B 3.05m, 2mmID PE 900-3920 |
| 80220-800 | Packed Column | 1.5% Rt-608 2m, 3/16" General Configuration |
| 80220-810 | Packed Column | 1.5% Rt-608 2m, 4mmID Hewlett Packard |
| 80220-820 | Packed Column | 1.5% Rt-608 2m, 4mmID Varian |
| 80220-830 | Packed Column | 1.5% Rt-608 2m, 4mmID PE 900-3920 |
| 80220-840 | Packed Column | 1.5% Rt-608 2m 3/16" PE |
| 80220-870 | Packed Column | 1.5% Rt-608 2m, 4mmID ON COL/ Tracor 550 |
| 80221-800 | Packed Column | 1.5% Rt-608 2m, 2mmID, Silco General Configuration |
| 80221-810 | Packed Column | 1.5% Rt-608 2m, 2mmID Hewlett Packard |
| 80221-820 | Packed Column | 1.5% Rt-608 2m, 2mmID Varian |
| 80221-830 | Packed Column | 1.5% Rt-608 2m, 2mmID PE 900-3920 |
| 80221-840 | Packed Column | 1.5% Rt-608 2m, 2mmID PE Autosystem |
| 80221-852 | Packed Column | 1.5% Rt-608 2m 2mm ID Silco Shimadzu 9A |
| 80221-85390 | Packed Column | 1.5% Rt-608 2m, 2mm ID, Silco Shimadzu 17A NOC |
| 80250-800 | Packed Column | Rt-Sulfur (Packed) 2m, 3/16" General Configuration |
| 80250-810 | Packed Column | Rt-Sulfur (Packed) 2m, 3.2mm ID Hewlett Packard |
| 80250-820 | Packed Column | Rt-Sulfur (Packed) 2m, 4mmID Varian 3700, Vista Series, FID |
| 80250-830 | Packed Column | Rt-Sulfur (Packed) 2m, 4mmID PE 900-3920, Sigma 1,2,3 |
| 80250-840 | Packed Column | Rt-Sulfur (Packed) 2m, 4mmID PE Autosys |
| 80251-800 | Packed Column | Rt-Sulfur (Packed) 1m, 3/16" General Configuration |
| 80251-810 | Packed Column | Rt-Sulfur (Packed) 1m, 4mmID Hewlett Packard |
| 80251-820 | Packed Column | Rt-Sulfur (Packed) 1m, 4mmID Varian 3700, Vista Series, FID |
| 80251-830 | Packed Column | Rt-Sulfur (Packed) 1m, 4mmID PE 900-3920, Sigma 1,2,3 |
| 80252-800 | Packed Column | Rt-Sulfur (Packed) 2m, 2mmID, Silco General Configuration |
| 80252-80090 | Packed Column | Rt-Sulfur (Packed) 2m, 2mmID, Silco, PreCond General Configuration |
| 80252-80090 | Packed Column | Rt-Sulfur (Packed) 2m 2mmID Silco Gen. Config. NOC |
| 80252-810 | Packed Column | Rt-Sulfur (Packed) 2m, 2mmID Hewlett Packard |
| 80252-81090 | Packed Column | Rt-Sulfur (Packed) 2m, 2mmID, NOC |
| 80252-820 | Packed Column | Rt-Sulfur (Packed) 2m, 2mmID Varian 3700 |
| 80252-830 | Packed Column | Rt-Sulfur (Packed) 2m, 2mmID PE 900-3920 |
| 80252-840 | Packed Column | Rt-Sulfur (Packed) 2m, 2mmID PE Autosystem |
| 80252-850 | Packed Column | Rt-Sulfur (Packed) 2m, 2mmID, Silco Shimadzu 14A |
| 80252-85390 | Packed Column | Rt-Sulfur (Packed) 2m, 2mm ID, Silco, NOC |
| 80252-860 | Packed Column | Rt-Sulfur (Packed) 2m, 2mmID Finnigan |
| 80252-895 | Packed Column | Rt-Sulfur (Packed) 2m, 2mmID SRI w/3.5" coil |
| 80253-800 | Packed Column | Rt-Sulfur (Packed) 1m, 2mmID General Configuration |
| 80253-810 | Packed Column | Rt-Sulfur (Packed) 1m, 2mmID Hewlett Packard |
| 80253-820 | Packed Column | Rt-Sulfur (Packed) 1m, 2mmID Varian 3700 |
| 80253-830 | Packed Column | Rt-Sulfur (Packed) 1m, 2mmID PE 900-3920 |
| 80253-840 | Packed Column | Rt-Sulfur (Packed) 1m, 2mmID PE Autosys |
| 80253-851 | Packed Column | Rt-Sulfur (Packed) 1m, 2mmID Shimadzu 8A |
| 80253-895 | Packed Column | Rt-Sulfur (Packed) 1m, 2mm ID |
| 80254-800 | Packed Column | 1.5% Rt-2250/1.95% Rt-2401 100/120 Silcoprt 2m,3/16" General Configuration |
| 80254-810 | Packed Column | 1.5% Rt-2250/1.95% Rt-2401 100/120 Silcoprt 2m,4mmID Hewlett Packard |
| 80254-81090 | Packed Column | 1.5% Rt-2250/1.95% Rt-2401 Silcoport 100/120 2m, 3/16" Silco, NOC, HP |
| 80254-820 | Packed Column | 1.5% Rt-2250/1.95% Rt-2401 100/120 Silcoprt 2m,4mmID Varian 3700 |
| 80254-82090 | Packed Column | 1.5% Rt-2250/1.95% Rt-2401 100/120 Silcoprt 2m,4mmID Varian 3700, PreCond |
| 80254-830 | Packed Column | 1.5% Rt-2250/1.95% Rt-2401 100/120 Silcoprt 2m,4mmID PE 900-3920 |
| 80254-840 | Packed Column | 1.5% Rt-2250/1.95% Rt-2401 100/120 Silcoprt 2m,4mmID PE Autosystem |
| 80254-870 | Packed Column | 1.5% Rt-2250/1.95% Rt-2401 100/120 Silcoprt 2m,4mmID Tremetrics / Tracor |
| 80305-800 | Packed Column | 1.5% XE60, 1% H3PO4 60/80 CBK B 1.8m, 2mmID General Configuration |
| 80305-810 | Packed Column | 1.5% XE60, 1% H3PO4 60/80 CBK B 1.8m, 2mmID Hewlett Packard |
| 80305-820 | Packed Column | 1.5% XE60, 1% H3PO4 60/80 CBK B 1.8m, 2mmID Varian 3700 |
| 80305-830 | Packed Column | 1.5% XE60, 1% H3PO4 60/80 CBK B 1.8m, 2mmID PE900-3920 |
| 80305-840 | Packed Column | 1.5% XE60, 1% H3PO4 60/80 CBK B 1.8mm, 2mm ID |

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034

**HROMalytic** +61(0)3 9762 2034
ECHnology Pty Ltd
Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA

Australian Distributors
Importers & Manufacturers
www.chromtech.net.au

[Ctrl F]
> Cat.#s

> Current System AUD Prices

