

80305-895	Packed Column	1.5% XE60 1% H3PO4 60/80 CBK B
80305-89590	Packed Column	1.5% XE60 1% H3PO4 60/80 CBK B 1
80311-800	Packed Column	0.19% Picric Acid 80/100 CBK C 2m, 2mmID, Silco General Configuration
80311-810	Packed Column	0.19% Picric Acid 80/100 CBK C 2m, 2mmID Hewlett Packard
80311-820	Packed Column	0.19% Picric Acid 80/100 CBK C 2m, 2mmID Varian 3700
80311-830	Packed Column	0.19% Picric Acid 80/100 CBK C 2m, 2mmID PE 900-3920
80311-840	Packed Column	0.19% Picric Acid CarboBlack C 80/100 2m, 2mm ID, Silco
80311-841	Packed Column	0.19% Picric Acid 80/100 CBK C 2m, 2mmID, Silco PE Auto Sys XL
80400-800	Packed Column	3% Rt-101 Silcoport W 100/120 2m, 2mmID Silco, General Configuration
80400-810	Packed Column	3% Rt-101 Silcoport 100/120 2m, 2mmID Hewlett Packard
80400-81090	Packed Column	3% Rt-101 Silcoport 100/120 2m, 2mm, Silco, HP, NOC
80400-820	Packed Column	3% Rt-101 Silcoport 100/120 2m, 2mmID Varian 3700
80400-830	Packed Column	3% Rt-101 Silcoport 100/120 2m, 2mmID PE 900-3920
80400-840	Packed Column	3% Rt-101 Silcoport 100/120 2m, 2mmID PE Autosystem
80400-850	Packed Column	3% Rt-101 Silcoport 100/120 2m, 2mmID Shimadzu 14A
80401-800	Packed Column	3% Rtx-1 Silcoport W 100/120 2m, 2mmID, Silcosteel General Configuration
80401-80090	Packed Column	3% Rtx-1 Silcoport W 100/120 2m, 2mmID Silco Gen Conf NOC
80401-810	Packed Column	3% Rtx-1 Silcoport W 100/120 2m, 2mmID Hewlett Packard
80401-81090	Packed Column	3% Rtx-1 Silcoport W 100/120 2m, 2mmID Hewlett Packard NOC
80401-820	Packed Column	3% Rtx-1 Silcoport W 100/120 2m, 2mmID Varian 3700
80401-82090	Packed Column	3% Rtx-1 Silcoport W 100/120 2m, 2mm, Silco, NOC, Varian
80401-830	Packed Column	3% Rtx-1 Silcoport W 100/120 2m, 2mmID PE900-3920
80401-840	Packed Column	3% Rtx-1 Silcoport W 100/120 2m, 2mm, Silco, PE AutoSys
80401-845	Packed Column	3% Rtx-1 Silcoport 100/120 2m, 1/8", Silco, OC, ABB
80401-888	Packed Column	3% Rtx-1 Silcoport W 100/120 2m, 2mm, Silco, OC, Fig.7 X=10.5", Y=7", S=6"
80401-896	Packed Column	3% Rtx-1 Silcoport W 100/120 2m, 2mmID OC
80402-800	Packed Column	3% Rtx-1 Silcoport 100/120 3.05m, 2mmID General Configuration
80402-80090	Packed Column	3% Rtx-1 Silcoport 100/120 3.05m, 2mm ID Preconditioned
80402-810	Packed Column	3% Rtx-1 Silcoport 100/120 3.05m, 2mmID Hewlett Packard
80402-820	Packed Column	3% Rtx-1 Silcoport 100/120 3.05m, 2mmID Varian
80402-830	Packed Column	3% Rtx-1 Silcoport 100/120 3.05m, 2mmID PE 900
80402-840	Packed Column	3% Rtx-1 Silcoport 100/120 3.05m, 2mmID
80403-800	Packed Column	3% Rtx-1 Silcoport 100/120 2m, 4mmID General Configuration
80403-810	Packed Column	3% Rtx-1 Silcoport 100/120 2m, 4mmID Hewlett Packard
80403-820	Packed Column	3% Rtx-1 Silcoport 100/120 2m, 4mmID Varian 3700
80403-830	Packed Column	3% Rtx-1 Silcoport 100/120 2m, 4mmID PE 900-3920
80404-800	Packed Column	3% Rtx-1 Silcoport 100/120 3.05m, 4mmID General Configuration
80404-810	Packed Column	3% Rtx-1 Silcoport 100/120 3.05m, 4mmID Hewlett Packard
80404-820	Packed Column	3% Rtx-1 Silcoport 100/120 3.05m, 4mmID Varian
80404-830	Packed Column	3% Rtx-1 Silcoport 100/120 3.05m, 4mmID PE 900
80405-800	Packed Column	10% Rtx-1 Silcoport W 100/120 2m, 2mmID, Silco General Configuration
80405-80090	Packed Column	10% Rtx-1 Silcoport W 100/120 2m, 2mmID, Silco, NOC
80405-810	Packed Column	10% Rtx-1 Silcoport W 100/120 2m, 2mmID Hewlett Packard
80405-81090	Packed Column	10% Rtx-1 Silcoport W 100/120 2m, 2.0mm ID, SS, HP, NOC
80405-820	Packed Column	10% Rtx-1 Silcoport 100/120 2m, 2mmID Varian
80405-830	Packed Column	10% Rtx-1 Silcoport W 100/120 2m, 2mmID PE 900-3920
80405-840	Packed Column	10% Rtx-1 Silcoport 100/120 2m, 2mmID PE Auto Sys
80405-84090	Packed Column	10% Rtx-1 Silcoport W 100/120 2m 2mm ID PE Auto Sys NOC
80405-850	Packed Column	10% Rtx-1 Silcoport 100/120 2m 2mmID Silco Shimadzu 14A
80405-85390	Packed Column	10% Rtx-1 Silcoport 100/120 2m 2mmID Silco Shimadzu 17A NOC
80405-893	Packed Column	10% Rtx-1 Silcoport 100/120 2m, 2mm ID, Silco, GowMac 816
80405-894	Packed Column	10% Rtx-1 Silcoport 100/120 2m, 2mm, Silco/Gow Mac 580
80405-895	Packed Column	10% Rtx-1 Silcoport 100/120 2m, 2mm, Silco, SRI 8610C
80406-800	Packed Column	10% Rtx-1 Silcoport 100/120 3.05m, 2mmID General Configuration
80406-810	Packed Column	10% Rtx-1 Silcoport 100/120 3.05m, 2mmID Hewlett Packard
80406-820	Packed Column	10% Rtx-1 Silcoport 100/120 3.05m, 2mmID Varian
80406-830	Packed Column	10% Rtx-1 Silcoport 100/120 3.05m, 2mmID PE 900
80406-895	Packed Column	10% Rtx-1 Silcoport 100/120 3.05m, 2mmID SRI
80407-800	Packed Column	10% Rtx-1 Silcoport 100/120 2m, 4mmID General Configuration
80407-810	Packed Column	10% Rtx-1 Silcoport 100/120 2m, 4mmID Hewlett Packard
80407-820	Packed Column	10% Rtx-1 Silcoport 100/120 2m, 4mmID Varian 3700
80407-830	Packed Column	10% Rtx-1 Silcoport 100/120 2m, 4mmID PE 900-3920
80407-840	Packed Column	10% Rtx-1 Silcoport 100/120 2m, 4mmID PE Auto Sys
80408-800	Packed Column	10% Rtx-1 Silcoport 100/120 3.05m, 4mmID General Configuration
80408-810	Packed Column	10% Rtx-1 Silcoport 100/120 3.05m, 4mmID Hewlett Packard
80408-820	Packed Column	10% Rtx-1 Silcoport 100/120 3.05m, 4mmID Varian

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034



**HROMalytic** +61(0)3 9762 2034  
**ECH**nology Pty Ltd

**Australian Distributors**  
 Importers & Manufacturers  
[www.chromtech.net.au](http://www.chromtech.net.au)

Website NEW : [www.chromalytic.net.au](http://www.chromalytic.net.au) E-mail : [info@chromtech.net.au](mailto:info@chromtech.net.au) Tel: 03 9762 2034 . . . in AUSTRALIA

