

80408-830	Packed Column	10% Rtx-1 Silcoport 100/120 3.05m, 2mm ID HP NOC
80409-800	Packed Column	20% Rtx-1 Silcoport W 100/120 2m, 2mm ID HP NOC
80409-810	Packed Column	20% Rtx-1 Silcoport W 100/120 2m, 2mm ID HP NOC
80409-81090	Packed Column	20% Rtx-1 Silcoport W 100/120 2m 2mm ID HP NOC
80409-820	Packed Column	20% Rtx-1 Silcoport W 100/120 2m, 2mmID Varian 3700
80409-82090	Packed Column	20% Rtx-1 Silcoport W 100/120 2m, 2mm, Silco, NOC, Varian
80409-830	Packed Column	20% Rtx-1 Silcoport W 100/120 2m, 2mmID PE 900-3920
80409-840	Packed Column	20% Rtx-1 Silcoport W 100/120 2m, 2mmID PE
80409-85090	Packed Column	20% Rtx-1 Silcoport W 100/120 2m, 1/8", Silco, NOC
80409-895	Packed Column	20% Rtx-1 Silcoport W 100/120 2m, 2mm ID, Silco SRI 8610C
80410-800	Packed Column	20% Rtx-1 Silcoport 100/120 3.05m, 2mm General Configuration
80410-810	Packed Column	20% Rtx-1 Silcoport 100/120 3.05m, 2mmIDX Hewlett Packard
80410-820	Packed Column	20% Rtx-1 Silcoport 100/120 3.05m, 2mmID Varian
80410-830	Packed Column	20% Rtx-1 Silcoport 100/120 3.05m, 2mmID PE 900
80411-800	Packed Column	20% Rtx-1 Silcoport 100/120 2m, 4mmID General Configuration
80411-810	Packed Column	20% Rtx-1 Silcoport 100/120 2m, 4mmID Hewlett Packard
80411-820	Packed Column	20% Rtx-1 Silcoport 100/120 2m, 4mmID Varian 3700
80411-830	Packed Column	20% Rtx-1 Silcoport 100/120 2m, 4mmID PE 900-3920
80412-800	Packed Column	20% Rtx-1 Silcoport 100/120 3.05m, 4mmID General Configuration
80412-810	Packed Column	20% Rtx-1 Silcoport 100/120 3.05m, 4mmID Hewlett Packard
80412-820	Packed Column	20% Rtx-1 Silcoport 100/120 3.05m, 4mmID Varian
80412-830	Packed Column	20% Rtx-1 Silcoport 100/120 3.05m, 4mmID PE 900
80415-800	Packed Column	5% Rtx-Stabilwax Silcoport W 100/120 Silco, General Configuration 2m, 2mmID
80415-810	Packed Column	5% Stabilwax Silcoport W 100/120 2m, 2mm, Silco, HP, OC Hewlett Packard
80415-820	Packed Column	5% Stabilwax Silcoport 100/120 Varian
80415-830	Packed Column	5% Stabilwax Silcoport W 100/120 PE 900-3920Sig
80415-840	Packed Column	5% Stabilwax Silcoport W 100/120 PE Auto System
80415-851	Packed Column	5% Stabilwax Silcoport W 100/120 2m, 1/8", Silco, Shdzu 8A
80416-800	Packed Column	10% Rtx-Stabilwax Silcoprt W 100/120 Silco, General Configuration 2m, 2mmID
80416-80090	Packed Column	10% Rtx-Stabilwax Silcoport W 100/120, 2m, 2mm, Silco, NOC
80416-810	Packed Column	10% Stabilwax Silcoprt W 100/120 2m 2mm Silco HP
80416-81090	Packed Column	10% Rtx-Stabilwax Silcoport W 100/120 2m, 2mm ID, Silco, NOC, HP
80416-820	Packed Column	10% Stabilwax Silcoprt W 100/120 2m 2mm Silco Varian
80416-830	Packed Column	10% Stabilwax Silcoprt W 100/120 2m 2mm Silco PE 900-3920Sig
80416-840	Packed Column	10% Stabilwax Silcoprt W 100/120 2m 2mm Silco PE Auto System
80416-845	Packed Column	10% Rtx-Stabilwax Silcoprt W 100/120 Silco ABB 3100 2m, 2mm ID
80416-850	Packed Column	10% Stabilwax Silcoprt W 100/120 2m 2mm Silco Shimadzu 14A
80416-851	Packed Column	10% Rtx-Stabilwax Silcoport W 100/120 Silco, Shimadzu 8A, 2m, 2mm ID
80416-86090	Packed Column	10% Rtx-Stabilwax Silcoport W 100/120 Silco Finnigan-Trace 2000 NOC
80416-895	Packed Column	10% Rtx-Stabilwax Silcoport W 100/120 2m, 2mm, Silco, SRI 8610C
80417-800	Packed Column	20% Rtx-Stabilwax Silcoprt W 100/120 Silco, General Configuration 2m, 2mmID
80417-80090	Packed Column	20% Rtx-Stabilwax Silcoport W 100/120 Silco, Gen Conf 2m 2mmID NOC
80417-810	Packed Column	20% Stabilwax Silcoprt W 100/120 2m 2mm Silco Hewlett Packard
80417-81090	Packed Column	20% Stabilwax Silcoport W 100/120 2m 2mm Silco HP NOC
80417-820	Packed Column	20% Stabilwax Silcoprt W 100/120 2m 2mm Silco Varian
80417-830	Packed Column	20% Stabilwax Silcoprt W 100/120 2m 2mm Silco PE 900-3920Sig
80417-840	Packed Column	20% Stabilwax Silcoprt W 100/120 2m 2mm Silco PE Auto System
80417-85090	Packed Column	20% Stabilwax Silcoprt W 100/120 2m, 1/8", Silco, NOC
80420-800	Packed Column	3% Rt-2100 Silcoport W 100/120 2m, 2mmID Silco, General Configuration
80420-810	Packed Column	3% Rt-2100 Silcoport 100/120 2m, 2mmID Hewlett Packard
80420-820	Packed Column	3% Rt-2100 Silcoport 100/120 2m, 2mmID Varian 3700, Vista Series, FID
80420-830	Packed Column	3% Rt-2100 Silcoport 100/120 2m, 2mmID PE 900-3920, Sigma 1,2,3
80420-841	Packed Column	3% Rt-2100 Silcoport W 100/120 2m, 2mm ID, Silco, PE Auto System XL
80425-800	Packed Column	Porapak R 80/100 2m, 2mmID General Configuration
80425-80090	Packed Column	Porapak R 80/100 2m, 2mmID General Conf NOC
80425-810	Packed Column	Porapak R 80/100 2m, 2mmID Hewlett Packard
80425-820	Packed Column	Porapak R 80/100 2m, 2mmID Varian 3700, Vista Series, FID
80425-830	Packed Column	Porapak R 80/100 2m, 2mmID PE 900-3920, Sigma 1,2,3
80425-840	Packed Column	Porapak R 80/100 2m, 2mmID PE Autosys
80425-84090	Packed Column	Porapak R 80/100 2m, 2mm, Silco, NOC
80425-888	Packed Column	Porapak R 80/100 2m, 2mm ID, Figure 12
80426-800	Packed Column	Porapak QS 80/100 2m, 2mmID, Silco General Configuration
80426-80090	Packed Column	Porapak QS 80/100 2m 2mm ID Silco Gen Conf NOC
80426-810	Packed Column	Porapak QS 80/100 2m, 2mmID Hewlett Packard
80426-81090	Packed Column	Porapak QS, 80/100, 2m 2mm ID, SILCO, HP, NOC
80426-820	Packed Column	Porapak QS 80/100 2m, 2mmID Varian 3700, Vista Series, FID

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034



HROMalytic +61(0)3 9762 2034
ECHnology Pty Ltd
 Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA

Australian Distributors
 Importers & Manufacturers
www.chromtech.net.au

