

80434-800 Packed Column  
 80434-80090 Packed Column  
 80434-810 Packed Column  
 80434-820 Packed Column  
 80434-830 Packed Column  
 80434-840 Packed Column  
 80435-800 Packed Column  
 80435-810 Packed Column  
 80435-820 Packed Column  
 80435-830 Packed Column  
 80435-840 Packed Column  
 80435-84090 Packed Column  
 80435-853 Packed Column  
 80436-800 Packed Column  
 80436-80080 Packed Column  
 80436-80090 Packed Column  
 80436-80090 Packed Column  
 80436-810 Packed Column  
 80436-81090 Packed Column  
 80436-850 Packed Column  
 80436-85090 Packed Column  
 80436-85290 Packed Column  
 80436-888 Packed Column  
 80436-895 Packed Column  
 80436-89990 Packed Column  
 80437-800 Packed Column  
 80437-80090 Packed Column  
 80437-810 Packed Column  
 80437-811 Packed Column  
 80437-840 Packed Column  
 80437-84590 Packed Column  
 80437-84590 Packed Column  
 80437-850 Packed Column  
 80437-85090 Packed Column  
 80437-88890 Packed Column  
 80437-89990 Packed Column  
 80437-89990 Packed Column  
 80439-800 Packed Column  
 80439-80090 Packed Column  
 80439-80090 Packed Column  
 80439-810 Packed Column  
 80439-81090 Packed Column  
 80439-81090 Packed Column  
 80439-820 Packed Column  
 80439-821 Packed Column  
 80439-840 Packed Column  
 80439-885 Packed Column  
 80439-89090 Packed Column  
 80439-89090 Packed Column  
 80439-893 Packed Column  
 80439-89590 Packed Column  
 80440-800 Packed Column  
 80440-80090 Packed Column  
 80440-810 Packed Column  
 80440-81090 Packed Column  
 80440-820 Packed Column  
 80440-82090 Packed Column  
 80440-840 Packed Column  
 80440-850 Packed Column  
 80440-85190 Packed Column  
 80440-888 Packed Column  
 80440-895 Packed Column  
 80440-89590 Packed Column  
 80441-800 Packed Column  
 80441-810 Packed Column  
 80441-820 Packed Column

Page 178  
 Chromosorb 102 80/100 2m, 2mmID  
 Chromosorb 102 80/100 2m, 2mmID  
 Chromosorb 102 80/100 2m, 2mmID  
 Chromosorb 102 80/100 2m, 2mmID Varian 3700, Vista  
 Chromosorb 102 80/100 2m, 2mmID PE 900-3920 Sigma123  
 Chromosorb 102 80/100 2m, 2mmID PE Autosys  
 Chromosorb 101 80/100 2m, 2mmID General Config.  
 Chromosorb 101 80/100 2m, 2mmID HP GCs  
 Chromosorb 101 80/100 2m, 2mmID Varian 3700, Vista  
 Chromosorb 101 80/100 2m, 2mmID PE 900-3920 Sigma123  
 Chromosorb 101 80/100 2m, 2mmID PE Autosys  
 Chromosorb 101 80/100 2m, 2mm, Silco, NOC, PE  
 Chromosorb 101 80/100 2m, 1/8", Silco, OC, Shimadzu 17A  
 n-Octane on ResSil C 80/100 20', 2mmID, 1/8"OD, Silco  
 n-Octane on ResSil C 80/100 20', 2mmID, Silco, 1/8" Welded Column Extensions  
 n-Octane on ResSil C 80/100 20ft 2mmID, Silco Gen Conf NOC Pre Cond  
 n-Octane on ResSil C 80/100 20', 2mm, Silco, NOC  
 n-Octane ResSil C 80/100 20', 2mmID, 1/8"OD, Silco, HP  
 n-Octane, ResSil C 80/100 20', 2mmID, 1/8"OD, Silco, HP, NOC  
 n-Octane on ResSil C 80/100 20', 2mmID, 1/8"OD, Silco For Shimadzu 14A, 2014  
 n-Octane on ResSil C 80/100 20ft, 2mmID, Silco Shimadzu 14A NOC  
 n-Octane on ResSil C 80/100 20' 2mmID, Silco Shimadzu 9A Pre Cond  
 n-Octane on ResSil C 80/100 20', 1/8", Silco, Fig.1, B=4"Max, X&Y=5"  
 n-Octane ResSil C 80/100 20ft 2mm ID, Silco SRI 8610C  
 n-Octane ResSil C 80/100 20', 2mm, Silco, NOC, PreCond, Pancake Coil 6"OD Max  
 OPN on ResSil C 80/100 12', 2mmID, 1/8"OD Silco  
 OPN on ResSil C 80/100 12', 1/8", Silco, NOC  
 OPN on ResSil C 80/100 12', 2mmID, 1/8"  
 OPN on ResSil C 80/100 12ft 2mm ID Silco HP 6850  
 OPN on ResSil C 80/100 12' 2mmID Silco PE AutoSys  
 OPN on ResSil C 80/100 12', 2mmID, Silco, For ABB 3100 Precond.  
 opn ResSil C 80/100 12', 1/8", Silco, NOC, ABB  
 OPN on ResSil C 80/100 12', 2mmID, 1/8"OD, Silco For Shimadzu 14A, 2014  
 OPN on ResSil C 80/100 12', 1/8", Silco, NOC, Shdzu-14A  
 OPN on ResSil C 80/100 12' 2mmID, 1/8" Custom Conf NOC Fig11 X&Y = 15cm  
 OPN on ResSil C 80/100 12', 1/8", Silco, NOC, PreCond, Pancake Coil  
 OPN on ResSil C 80/100 12', 1/8", Silco, NOC, Pancake Coil  
 Molesieve 13X 80/100 2m 1/8", 2mmID/Silcosteel/Gen Config  
 Molesieve 13X 80/100 2m 1/8", 2mmID/Silcosteel/Gen Config/PreCond  
 Molesieve 13X 80/100 2m 2mm ID Silco Gen Conf NOC  
 Molesieve 13X 80/100 2m, 1/8", Silco, OC, HP  
 Molesieve 13X 80/100 2m 1/8" Silco OC HP Precondition  
 Molesieve 13X 80/100 2m 2mm ID Silco HP NOC  
 Molesieve 13X 80/100 2m 1/8" Silco Varian 3700  
 Molesieve 13X 80/100 2m 1/8", Silco, Varian 3800  
 Molesieve 13X 80/100 2m 1/8", 2mmID, Silco, PE  
 Molesieve 13X 80/100 2m, 1/8", Silco, Pye Unicam 4500  
 Molesieve 13X 80/100 2m 1/8" Silco Gow Mac 590 NOC Pre Condition  
 Molesieve 13X 80/100 2m 1/8" Silco Gow Mac 590 NOC  
 Molesieve 13X 80/100 2m, 1/8", Silco, GowMac 816  
 Molesieve 13X 80/100 2m 1/8" Silco SRI 8610C NOC  
 Molesieve 5A 80/100 1m 1/8", 2mmID/Silcosteel/Gen Config  
 Molesieve 5A 80/100 1m 2mm, Silco, NOC  
 Molesieve 5A 80/100 1m, 2mm Silco, HP  
 Molesieve 5A 80/100 1m, 2mm, Silco, NOC, HP  
 Molesieve 5A 80/100 1m 2mm ID Silco Varian 3700  
 Molesieve 5A 80/100 1m 2mm, Silco, NOC, Varian  
 Molesieve 5A 80/100 1m 1/8", 2mmID, SILCO, Config for PE Auto System 8300,8  
 Molesieve 5A 80/100 1m, 2mm Silco Shimadzu 14A  
 Molesieve 5A 80/100 1m, 2mm Silco Shimadzu 8A NOC  
 Molesieve 5A, 80/100, 1m 1/8", 2mm ID, Silco Customer Supplied Dimensions  
 Molesieve 5A 80/100 1m, 2mmID Silcosteel SRI 8610C  
 Molesieve 5A 80/100 1m 1/8", 2mmID/Silcosteel/NOC/HP  
 3% Rtx-1 Silcoport W 100/120 6ft, 2mm ID, Stainless  
 3% Rtx-1 Silcoport W 100/120 6', 1/8", SS, HP  
 3% Rtx-1 Silcoport 100/120 6', 1/8", SS, Var

