

80441-82090 Packed Column  
80442-800 Packed Column  
80442-810 Packed Column  
80442-81090 Packed Column  
80442-840 Packed Column  
80442-84090 Packed Column  
80442-85090 Packed Column  
80443-800 Packed Column  
80443-810 Packed Column  
80443-82090 Packed Column  
80443-850 Packed Column  
80443-851 Packed Column  
80444-800 Packed Column  
80444-810 Packed Column  
80444-82090 Packed Column  
80445-800 Packed Column  
80445-810 Packed Column  
80445-820 Packed Column  
80445-840 Packed Column  
80445-845 Packed Column  
80446-800 Packed Column  
80446-80090 Packed Column  
80446-810 Packed Column  
80446-84090 Packed Column  
80447-800 Packed Column  
80447-810 Packed Column  
80447-84090 Packed Column  
80448-800 Packed Column  
80448-810 Packed Column  
80448-81090 Packed Column  
80448-820 Packed Column  
80448-840 Packed Column  
80448-85090 Packed Column  
80449-800 Packed Column  
80449-810 Packed Column  
80449-851 Packed Column  
80450-800 Packed Column  
80450-810 Packed Column  
80450-81090 Packed Column  
80450-830 Packed Column  
80450-84090 Packed Column  
80451-800 Packed Column  
80451-80090 Packed Column  
80451-810 Packed Column  
80451-820 Packed Column  
80451-840 Packed Column  
80451-84590 Packed Column  
80451-85290 Packed Column  
80452-800 Packed Column  
80452-810 Packed Column  
80452-888 Packed Column  
80453-800 Packed Column  
80453-810 Packed Column  
80453-84090 Packed Column  
80454-800 Packed Column  
80454-810 Packed Column  
80454-81090 Packed Column  
80455-800 Packed Column  
80456-800 Packed Column  
80456-810 Packed Column  
80456-82190 Packed Column  
80457-800 Packed Column  
80457-810 Packed Column  
80457-820 Packed Column  
80457-830 Packed Column  
80457-840 Packed Column

3% Rtx-1 Silcoport W 100/120 6', 2mm  
10% Rtx-1 Silcoport W 100/120 6ft, 2mm  
10% Rtx-1 Silcoport W 100/120 6', 1/8", SS, HP, NOC  
10% Rtx-1 Silcoport W 100/120 6ft, 2mm ID, Stainless  
10% Rtx-1 Silcoport W 100/120 6ft, 2mm ID, SS, NOC  
10% Rtx-1 Silcoport 100/120 6', 1/8", SS, OC, PreCond, Shdzu-14A  
20% Rtx-1 Silcoport W 100/120 6ft, 2mm ID, Stainless  
20% Rtx-1 Silcoport W 100/120 6', 1/8", SS, HP  
20% Rtx-1 Silcoport W 100/120 6', 2mm, SS, NOC, Varian  
20% Rtx-1 Silcoport W 100/120 6ft, 2mm ID, SS, Shimadzu 14A, 2014  
20% Rtx-1 Silcoport W 100/120 6', 1/8", SS, Shdzu 8A  
3% Rtx-5 Silcoport W 100/120 6ft, 2mm ID, Stainless  
3% Rtx-5 Silcoport 100/120 6ft, 2mm ID, Stainless  
3% Rtx-5 Silcoport W 100/120 6', 2mm, SS, NOC, Varian  
10% Rtx-5 Silcoport W 100/120 6ft, 2mm ID, Stainless  
10% Rtx-5 Silcoport 100/120 6', 2mm, SS, HP  
10% Rtx-5 Silcoport 100/120 6ft, 2mm ID, Stainless  
10% Rtx-5 Silcoport W 100/120 6ft, 2mm ID, SS PE  
10% Rtx-5 Silcoport W 100/120 6ft 2mm ID SS ABB 3100  
20% Rtx-5 Silcoport W 100/120 6ft, 2mm ID, Stainless  
20% Rtx-5 Silcoport W 100/120 6ft, 2mm ID, SS, NOC  
20% Rtx-5 Silcoport W 100/120 6ft, 2mm ID, Stainless, Agilent  
20% Rtx-5 Silcoport W 100/120 6', 1/8", SS, NOC, PE AutoSys  
5% Rtx-Stabilwax Silcoport W 100/120 6ft, 2mm ID, Stainless  
5% Rtx-Stabilwax Silcoport 100/120 6', 2mm, SS, HP  
5% Rtx-Stabilwax Silcoport W 100/120 6', 2mm ID, SS, NOC, PE  
INDEFINITE BACKORDER 10% Rtx-Stabilwax Silcoport W 100/120 6ft, 2mm ID,  
INDEFINITE BACKORDER 10% Rtx-Stabilwax Silcoport W 100/120 6', 2mm, SS,  
10% Rtx-Stabilwax Silcoport W 100/120 6' 2mm SS NOC HP  
10% Rtx-Stabilwax Silcoport W 100/120 6', 2mm, SS, Varian  
10% Rtx-Stabilwax Silcoport W 100/120 6ft, 2mm ID, SS PE AutoSys  
10% Rtx-Stabilwax Silcoport 100/120 6', 1/8", SS, OC, PreCond, Shdzu-14A  
20% Rtx-Stabilwax Silcoport W 100/120 6ft, 2mm ID, Stainless  
20% Rtx-Stabilwax Silcoport W 100/120 6', 1/8", 2mm ID, SS, HP  
20% Rtx-Stabilwax Silcoport W 100/120 6ft, 2mm ID, Stainless for Shimadzu 8A  
Rtx-1HT SimDist 2887 Silcoport W 100/120 25" 2mm ID, Stainless  
Rtx-1HT SimDist 2887 Silcoport W 100/120 25", 2mm ID, SS, HP  
Rtx-1HT SimDist 2887 Silcoport W 100/120 25", 2mm ID, SS, HP NOC  
Rtx-1HT SimDist 2887 Silcoport W 100/120 25", 2mm ID, SS, For PE 900-3920  
Rtx-1HT SimDist 2887 Silcoport W 100/120 25" 2mm ID, SS ABB 3100 NOC  
6.6% Carbowax 20M CarboBlack 80/120 6ft, 2mm ID, Stainless  
6.6% Carbowax 20M CarboBlack 80/120 6ft, 2mm ID, Stainless, NOC  
6.6% Carbowax 20M CarboBlack 80/120 6' 1/8" SS HP  
6.6% Carbowax 20M Carbbk 80/120 6', 1/8", SS, Varian  
6.6% Carbowax 20M CarboBlack 80/120 6ft 2mm ID, SS PE Auto Sys  
6.6% Carbowax 20M, Carboblack B 80/120 6', 1/8", SS, NOC, AAI  
6.6% Carbowax 20M CarboBlack 80/120 6ft 2mm ID Shimadzu 9A NOC  
1% Rt-1000 CarboBlack 60/80 6ft, 2mm ID, Stainless  
1% Rt-1000 Carboblack 60/80 6', 1/8", SS, HP  
1% Rt-1000 Carboblack B 60/80 6', 1/8", SS, OC, Varian 2" Void at Inlet, 1" Void at  
3% Rt-1500 CarboBlack B 80/120 10ft, 2mm ID, Stainless  
3% Rt-1500 Carboblack 80/120 10', 1/8", SS  
3% Rt-1500 Carboblack 80/120 10', 1/8", SS, NOC, PE  
1% Rt-1510 CarboBlack 60/80 10ft, 2mm ID, Stainless  
1% Rt-1510 Cblk 60/80 10', 1/8", SS  
1% Rt-1510 CBlk 60/80 10', 1/8", SS, NOC  
1.5% XE-60/1% H3PO4 CarboBlack 60/80 6ft, 2mm ID, Stainless  
0.2% Carbowax 1500 CarboBlack C 60/80 6ft, 2mm ID, Stainless  
0.2% Carbowax 1500 CarboBlack C 60/80 6ft, 2mm ID SS HP 5890  
0.2% Carbowax 1500 CarboBlack C 60/80 6ft 2mm ID SS Varian 3800 NOC  
0.2% Carbowax 1500 CarboBlack C 80/100 6ft, 2mm ID, Stainless  
0.2% Carbowax 1500, Carboblack C 80/100 6', 1/8", SS, HP 5890  
0.2% Carbowax 1500 Cblk C 80/100 6' 2mm SS Varian  
0.2% Carbowax 1500 Carboblack C 80/100 6ft, 1/8", SS, PE 900-3920, Sigma 1,2  
0.2% C-1500 CarboBlack C 80/100 6' 1/8" SS PE

(Ctrl F)  
> Cat.#s

> Current System AUD Prices



Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034



**HROMalytic** +61(0)3 9762 2034  
**ECHnology** Pty Ltd

**Australian Distributors**  
Importers & Manufacturers  
[www.chromtech.net.au](http://www.chromtech.net.au)

Website NEW : [www.chromalytic.net.au](http://www.chromalytic.net.au) E-mail : [info@chromtech.net.au](mailto:info@chromtech.net.au) Tel: 03 9762 2034 . . . in AUSTRALIA