



**> Current System AUD Prices**

80457-894	Packed Column	0.2% Carbowax 1500 CarboBlk C 80/
80458-800	Packed Column	0.1% Rt-1000 CarboBlack C 80/100 6'
80458-810	Packed Column	0.1% Rt-1000 Carboblck C 80/100 6', 1/8", SS, HP
80458-820	Packed Column	0.1% Rt-1000 Carboblack C 80/100 6ft, 2mm ID, Stainless, Varian
80458-830	Packed Column	0.1% Rt-1000 Carboblack C 80/100 6ft, 1/8", SS, PE 900-3920, Sigma 1,2,3
80459-800	Packed Column	0.19% Picric Acid CarboBlack C 80/100 6ft, 2mm ID, Stainless
80459-810	Packed Column	0.19% Picric Acid CarboBlack C 80/100 6ft, 2mm ID, Stainless
80459-820	Packed Column	0.19% Picric Acid CarboBlack C 80/100 6' 2mmID SS Varian 3700
80459-853	Packed Column	0.19% Picric Acid CarboBlack C 80/100 6ft, 2mm ID, SS Shimadzu 17A, 2010
80460-800	Packed Column	0.3% Carbowax 20M/0.1% H3PO4 CarboBlack C 60/80 2.5ft, 3.2mm ID, Stainless
80460-810	Packed Column	0.3% Carbowax 20M, 0.1% H3PO4 Carboblack C 60/80 2.5', 3.2mm ID, SS, HP
80461-800	Packed Column	3% Rt-101 Silcoport W 100/120 6ft, 2mm ID, Stainless
80462-800	Packed Column	3% Rt-2100 Silcoport W 100/120 6ft, 2mm ID, Stainless
80463-800	Packed Column	5% Rt-1200/1.75% Bentone 34 Silcoport W 100/120 6ft, 2mm ID, Stainless
80463-80090	Packed Column	5% Rt-1200, 1.75% Bentone 34 Silcoport W 100/120 6', 1/8" SS, OC, PreCond
80463-810	Packed Column	5% Rt-1200/1.75% Bentone 34 Silcoport W 100/120 6', 1/8", SS
80463-888	Packed Column	5% Rt-1200, 1.75% Bentone 34 Silcoport W 100/120 6', 1/8", SS Config for SRI-3
80464-800	Packed Column	INDEFINITE BACKORDER 5% Rt-1200/5% Bentone 34 Silcoport W 100/120 6ft,
80464-845	Packed Column	INDEFINITE BACKORDER 5% Rt-1200/5% Bentone34 Silcoport W 100/120 6ft, :
80465-800	Packed Column	10% TCEP Chromosorb PAW 100/120 8ft, 2mm ID, Stainless
80465-810	Packed Column	10% TCEP Chromosorb PAW 100/120 8ft, 2mmID, SS HP
80465-84090	Packed Column	10% TCEP Chromosorb PAW 100/120 8', 2mm ID, SS, NOC, PE 8700
80465-895	Packed Column	10% TCEP Chrmsrb PAW 100/120 8', 2mm ID, SS
80466-800	Packed Column	23% Rt-1700 Chromosorb PAW 80/100 30ft, 2mm ID, Stainless
80466-810	Packed Column	23% Rt-1700 Chromosorb PAW 80/100 30', 2mm ID, Stainless
80466-895	Packed Column	23% Sebaconitrile (Rt-1700) Chromosorb PAW 80/100 30ft 2mm ID SS SRI 8610
80467-800	Packed Column	HayeSep Q 80/100 6ft, 2mm ID, Stainless
80467-80090	Packed Column	HayeSep Q 80/100 6ft, 2mm ID SS NOC Pre Cond
80467-80090	Packed Column	HayeSep Q 80/100 6ft 2mm ID SS NOC
80467-810	Packed Column	Hayesep Q 80/100 6', 1/8", SS, HP
80467-81090	Packed Column	Hayesep Q 80/100 6', 1/8", SS,HP NOC
80467-820	Packed Column	HayeSep Q 80/100 6ft 2mmID SS Varian 3700
80467-821	Packed Column	HayeSep Q 80/100 6ft, 2mm ID, Stainless Varian 3800
80467-840	Packed Column	Hayesep Q 80/100 6', 2mm ID, Stainless
80467-84090	Packed Column	Hayesep Q 80/100 6', 2mm ID, SS, NOC
80467-841	Packed Column	HayeSep Q 80/100, 6ft, 2mm ID SS, Config for PE Auto Sys XL
80467-84590	Packed Column	Hayesep Q 80/100 6', 1/8", SS, NOC, AAI
80467-850	Packed Column	Hayesep Q 80/100 6', 1/8", SS, Shimadzu 14A, 2014
80467-851	Packed Column	HayeSep Q 80/100 6ft 2mm ID SS Shimadzu 8A
80467-893	Packed Column	HS-Q, 80/100, 6ft, 2mm ID SS, Gow Mac 816
80468-800	Packed Column	Porapak Q 80/100 6ft, 2mm ID, Stainless
80468-80090	Packed Column	Porapak Q 80/100 6', 2mm ID, SS, NOC Precondition
80468-80090	Packed Column	Porapak Q 80/100 6', 1/8", SS, NOC
80468-810	Packed Column	Porapak Q 80/100 6ft, 2mm ID, SS
80468-81090	Packed Column	Porapak Q 80/100 6ft 2mm ID SS HP 5890 Pre Cond
80468-81090	Packed Column	Porapak Q 80/100 6', 1/8", SS, NOC
80468-820	Packed Column	Porapak Q 80/100 6ft, 2mmID, SS Varian 3700
80468-82090	Packed Column	Porapak Q 80/100 6ft, 2mm ID, Stainless, NOC, Varian 3700
80468-840	Packed Column	Porapak Q 80/100 6ft, 2mm ID, Stainless, PE
80468-84090	Packed Column	Porapak Q 80/100 6' 1/8" SS PE NOC
80468-850	Packed Column	Porapak Q 80/100 6ft, 2mmID, SS Shimadzu 14A, 2014
80468-851	Packed Column	Porapak Q 80/100 6 ft, 2mm ID, SS, Shimadzu 8A,
80468-853	Packed Column	Porapak Q, 80/100, 6ft 2mm ID, SS, Shimadzu 17A 2010
80468-888	Packed Column	Porapak Q 80/100 6', 2mm SS, Varian 3700 Inlet = 5cm Outlet = 1cm
80468-894	Packed Column	Porapak Q, 80/100, 6ft 2mmID, SS, For Gow Mac 580
80468-89490	Packed Column	Porapak Q 80/100 6', 1/8", SS, NOC, GM-580
80468-895	Packed Column	Porapak Q 80/100 6ft, 2mm ID, Stainless
80468-895R	Packed Column	Porapak Q 80/100 6' 1/8" SS SRI 8610C Dual GC Right Side
80469-800	Packed Column	Porapak QS 80/100 6ft, 2mm ID, Stainless
80469-810	Packed Column	Porapak QS 80/100 6', 1/8", SS, HP
80469-81090	Packed Column	Porapak QS, 80/100, 6ft 1/8" OD, SS, HP, NOC
80469-820	Packed Column	Porapak QS 80/100 6', 2mm, SS
80469-830	Packed Column	Porapak QS 80/100 6ft, 2mm ID, SS, PE
80469-840	Packed Column	Porapak QS 80/100 6ft, 2mm ID, Stainless, PE Auto System
80469-860	Packed Column	Porapak QS 80/100 6ft, 2mm ID, Stainless Finnigan
80470-800	Packed Column	Porapak R 80/100 6ft, 2mm ID, Stainless