

80470-80090 Packed Column
80470-810 Packed Column
80470-81090 Packed Column
80470-840 Packed Column
80470-84090 Packed Column
80471-800 Packed Column
80471-810 Packed Column
80471-81090 Packed Column
80471-81090 Packed Column
80471-820 Packed Column
80471-821 Packed Column
80471-84090 Packed Column
80471-895R Packed Column
80472-800 Packed Column
80472-80090 Packed Column
80472-810 Packed Column
80472-81090 Packed Column
80472-820 Packed Column
80473-800 Packed Column
80473-80090 Packed Column
80473-810 Packed Column
80473-81090 Packed Column
80473-820 Packed Column
80473-821 Packed Column
80473-840 Packed Column
80473-850 Packed Column
80473-88890 Packed Column
80473-893 Packed Column
80473-895 Packed Column
80473-895R Packed Column
80474-800 Packed Column
80474-80090 Packed Column
80474-810 Packed Column
80474-81090 Packed Column
80474-820 Packed Column
80474-830 Packed Column
80474-840 Packed Column
80474-84090 Packed Column
80474-845 Packed Column
80474-84590 Packed Column
80474-850 Packed Column
80474-875 Packed Column
80474-89090 Packed Column
80474-895 Packed Column
80474-89590 Packed Column
80475-800 Packed Column
80475-80090 Packed Column
80475-810 Packed Column
80475-81090 Packed Column
80475-820 Packed Column
80475-821 Packed Column
80475-840 Packed Column
80475-84090 Packed Column
80475-85090 Packed Column
80476-800 Packed Column
80476-80090 Packed Column
80476-810 Packed Column
80476-81090 Packed Column
80476-820 Packed Column
80476-821 Packed Column
80476-840 Packed Column
80476-84590 Packed Column
80476-88890 Packed Column
80476-89490 Packed Column
80476-895L Packed Column

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034

**HROMalytic** +61(0)3 9762 2034
ECHnology Pty Ltd
Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA

Australian Distributors
Importers & Manufacturers
www.chromtech.net.au

Page 181

Porapak R 80/100 6ft, 2mm ID SS NC
Porapak R 80/100 6', 1/8", SS, HP
Porapak R 80/100 6ft 1/8in SS HP NC
Porapak R 80/100 6', 1/8", SS, PE
Porapak R 80/100 6', 1/8", SS, NOC, PE
Chromosorb 101 80/100 6ft, 2mm ID, Stainless
Chromosorb 101 80/100 6ft, 2mm ID, SS, HP
Chromosorb 101 80/100 6ft 2mm ID SS HP PreCond NOC
Chromosorb 101 80/100 6ft 2mm ID SS HP NOC
Chromosorb 101 80/100 6ft, 2mm ID, Stainless
Chromosorb 101 80/100 6ft, 2mm ID, SS Config for Varian 3800
Chromsorb 101 80/100 6', 1/8" SS, NOC, PE AutoSys
Chromosorb 101 80/100 6ft, 2mm ID, Stainless, SRI 8610C Right
Chromosorb 102 80/100 6ft, 2mm ID, Stainless
Chromosorb 102 80/100 6' 2mmID SS NOC
Chromsorb 102 80/100 6', 1/8", SS, OC, HP
Chromosorb 102 80/100 6ft, 2mm ID, Stainless, NOC, HP
Chromosorb 102 80/100 6ft 2mm ID, Stainless, Varian
Molesieve 5A 60/80 6ft, 2mm ID, Stainless
Molesieve 5A 60/80 6ft 2mm ID SS NOC
Molesieve 5A 60/80 6', 2mm ID, SS, HP
Molesieve 5A 60/80 6', 2mm ID, SS, NOC (Pack Full to Ends)
Molesieve 5A, 60/80 6ft, 2mm ID, Stainless Config for Varian 3700 GC
Molesieve 5A 60/80 6ft, 2mmID, SS, Varian 3800
Molesieve 5A 60/80 6ft, 2mm ID SS AutoSys
Molesieve 5A, 60/80 6ft, 2mm ID, SS For Shimadzu 14A, 2014
Molesieve 5A 60/80, 6ft, 2mm ID, SS, Special Config, NOC
Molesieve 5A 60/80 6', 2mm, SS, GM-816 1" Voids at Ends
Molesieve 5A, 60/80, 6ft 2mm ID, SS, For SRI 8610 GC
Molesieve 5A 60/80 6', 1/8", 2mm, SS, SRI8610C Dual GC Right Side
MoleSieve 5A 80/100 6ft, 2mm ID, Stainless
MoleSieve 5A 80/100 6ft, 2mm ID, Stainless, NOC
Molesieve 5A 80/100 6', 1/8" SS, HP
Molesieve 5A 80/100 6', 2mm ID, SS, NOC
MoleSieve 5A 80/100 6ft, 2mm ID SS Varian 3700
Molesieve 5A 80/100 6', 1/8", SS, PE
MoleSieve 5A 80/100 6ft, 2mm ID, Stainless PE AutoSys 8300,8400,8700
MoleSieve 5A 80/100 6', 1/8", SS, NOC, PE Auto
Molesieve 5A 80/100 6ft, 2mm ID, Stainless, ABB 3100
Molesieve 5A 80/100 6', 1/8" SS, NOC, ABB
MoleSieve 5A 80/100 6ft 2mm ID SS Shimadzu 14A
MoleSieve 5A 80/100 6ft, 2mm ID, Stainless, AC
Molesieve 5A 80/100 6', 1/8", SS, NOC, Gow Mac 590
MoleSieve 5A 80/100 6ft, 1/8", SS, SRI8610C
MoleSieve 5A 80/100 6ft 2mm ID SS SRI 8610C NOC
MoleSieve 13X 60/80 6ft, 2mm ID, Stainless
Molesieve 13X 60/80 6', 1/8", SS, NOC
Molesieve 13X 60/80 6', 2mm ID, SS, HP
Molesieve 13X 60/80 6', 2mm ID, SS, HP, NOC, PreCond
Molesieve 13X 60/80 6', 1/8", SS, OC, Var
MoleSieve 13X, 60/80, 6ft, 2mm ID, SS, Varian 3800
MoleSieve 13X 60/80 6ft, 2mm ID, Stainless, PE 8300
MoleSieve 13X 60/80 6ft, 2mm ID, SS, PE8300 Preconditioning
MoleSieve 13X, 60/80, 6ft, 2mm ID, SS, NOC, for Shimadzu 2014 and 14A GCs
MoleSieve 13X 80/100 6ft, 2mm ID, Stainless
MoleSieve 13X 80/100 6', 2mm ID, SS, NOC Preconditioned
MoleSieve 13X 80/100 6ft, 2mm ID SS NOC
MoleSieve 13X 80/100 6ft, 2mm ID, Stainless, HP
MoleSieve 13X 80/100 6ft, 2mm ID, Stainless, HP, NOC
MoleSieve 13X 80/100 6' 2mmID SS Varian 3700
MoleSieve 13X 80/100 6f, 2mmID, SS, Varian 3800
MoleSieve 13X 80/100 6ft, 2mm ID, Stainless, PE Config
MoleSieve 13X 80/100 6', 1/8", SS, ABB, NOC
MoleSieve 13X 80/100, 6ft, 2mm ID SS, Special Config., NOC
MoleSieve 13X 80/100 6', 1/8", SS, GowMac 580, NOC
MoleSieve 13X 80/100 6ft 2mm ID SS SRI 8610C Left Side

(Ctrl F)

> Cat.#s

> Current System AUD Prices

