



80486-82090	Packed Column	ShinCarbon ST 80/100, 2m 2mmID, €
80486-821	Packed Column	ShinCarbon ST 80/100 2m 1/8" Silco
80486-82190	Packed Column	ShinCarbon ST 80/100 2m 2mm ID Silco
80486-840	Packed Column	ShinCarbon ST 80/100 2m,2mmID, 1/8"OD, Silco, PE
80486-841	Packed Column	ShinCarbon ST 80/100 2m, 2mmID, 1/8"OD, Silco For PE Auto Sys XL
80486-850	Packed Column	ShinCarbon ST 80/100 2m 2mmID Silco Shimadzu 14A
80486-851	Packed Column	ShinCarbon ST 80/100 2m,2mm, 1/8", Silco, Shdzu-8A
80486-85190	Packed Column	ShinCarbon ST 80/100 2m 1/8" Silco Shdzu-8A Pre Cond
80486-85190	Packed Column	ShinCarbon ST 80/100 2m, 2mm 1/8" Silco Shdzu-8A NOC
80486-853	Packed Column	ShinCarbon ST 80/100, 2m, 2mm ID, Silco, For Shimadzu 17A, 2010
80486-85390	Packed Column	ShinCarbon ST 80/100 2m, 2mm ID Silco Shimadzu 17A NOC
80486-860	Packed Column	ShinCarbon ST 80/100 2m 2mmID 1/8"OD Silco Trace 2000 or Finnigan
80486-890	Packed Column	ShinCarbon ST 80/100 2m 2mm ID Silco Gow Mac 590
80486-89090	Packed Column	ShinCarbon ST 80/100 2m, 2mmID 1/8"OD Silco Gow Mac 590 NOC
80486-894	Packed Column	ShinCarbon ST, 80/100, 2m 2mmID, Silco, Gow Mac 580
80486-89490	Packed Column	ShinCarbon ST 80/100 2m, 2mm ID Silco Gow Mac 580 NOC
80486-895	Packed Column	ShinCarbon ST 80/100 2m, 2mmID, Silco SRI 8610C
80486-895L	Packed Column	ShinCarbon ST 80/100 2m, 2mm ID Silco SRI 8610 Duel GC left side
80486-896	Packed Column	ShinCarbon ST 80/100 2m, 2mmID, 1/8"OD, Silco, SRI 9300
83606-800	D3606 Column Set	Rt-D3606-1, 1.8m 2mmID Rt-D3606-2, 4.9m 2mmID Sulfinert Gen Config
83606-80090	D3606 Column Set	Rt-D3606-1, 1.8m 2mmID Rt-D3606-2, 4.9m 2mmID Sulfinert Gen Config NOC In
83606-810	D3606 Column Set	Rt-D3606-1, 1.8m 2mmID Rt-D3606-2, 4.9m 2mmID HP
83606-81090	D3606 Column Set	Rt-D3606, 1.8m 2mm ID Rt-D3606, 4.9 2mm ID Sulfinert, HP Conf
83606-821	D3606 Column Set	Rt-D3606-1, 1.8m, 2mm ID Rt-D3606-2, 4.9m, 2mm ID Sulfinert, Varian 3800
83606-840	D3606 Column Set	Rt-D3606-1, 1.8m 2mmID Rt-D3606-2, 4.9m 2mmID Sulfinert PE Auto Sys
83606-841	D3606 Column Set	Rt-D3606-1, 1.8m 2mm ID Rt-D3606-2, 4.9m 2mm ID PE Auto Sys XL
83606-850	D3606 Column Set	Rt-D3606-1, 1.8m 2mmID Rt-D3606-2, 4.9m 2mmID Sulfinert Shimadzu 14A
83606-888	D3606 Column Set	Rt-D3606-1, 1.8m 2mmID Rt-D3606-2, 4.9m 2mm ID Sulfinert Special Configurati
88000-800	Packed Column	Phase 2a, 2b, 2c on Silcosteel Tubing Gen Conf
88000-810	Packed Column	Phase 2a, 2b, 2c on Silcosteel Tubing
88000-81090	Packed Column	Phase 2a, 2b, 2c on Silcosteel Tubing NOC
88000-841	Packed Column	Phase 2a,2b,2c on Silcosteel Tubing PE Auto Sys XL
88000-875	Packed Column	Phase 2a 2b 2c on Silcosteel Tubing
88000-880	Packed Column	Phase 2a, 2b, 2c on Silcosteel Tubing
88000-895	Packed Column	Phase 2a, 2b, 2c on Silcosteel Tubing SRI 8610C
88004-810	Packed Column	2.1% Carbowax 1540 Porasil C 80/100 2', 2mm ID, Silco, NOC, HP Config
88004-875	Packed Column	2.1% Carbowax 1540 Porasil C 80/100 2' 2mmID/Silco/ NOC/AC
88005-810	Packed Column	Hayesep Q, 60/80, 9', 2mm ID, Silco, NOC, HP Config
88005-875	Packed Column	HAYESEP Q 60/80 9', 2mmID, Silco NOC/AC
88006-810	Packed Column	Molesieve 13X, 45/60, 9', 2mm ID, Silco, NOC, HP Config
88006-875	Packed Column	Molesieve 13X 45/60 9' 2mmID /Silco/ NOC/AC
88007-810	Packed Column	Hayesep Q, 60/80, 4', 2mm ID, NOC, HP Config
88007-875	Packed Column	HAYESEP Q 60/80 4' 2mmID NOC/AC
88008-875	Packed Column	Molesieve 5A 45/60 9' 2mmID/ NOC/AC
88009-810	Packed Column	Chromosorb PAW 60/80 3' 2mmID, Silco, NOC, HP Config
88009-81090	Packed Column	Chromsorb PAW 60/80 3', 1/8", Silco, NOC, HP
88009-875	Packed Column	Chromosorb PAW 60/80 3' 2mmID, Silco NOC/AC
88010-800	Packed Column	HAYESEP T 80/100 6' 1/8" Silco NOC Gen Conf
88010-810	Packed Column	HS-T, 80/100, 6', 1/8" Silco, HP Config
88010-875	Packed Column	HAYESEP T 80/100 Silco 6' 1/8" NOC/AC
88012-800	Packed Column	5% Carbowax 20m on CarboBlack B 60/80, 6ftx1/8in, 2.1mm ID, Stainless
88012-810	Packed Column	5% Carbowax 20m on CarboBlack B 60/80, 6ftx1/8in, 2.1mm ID, Stainless, HP
88012-820	Packed Column	5% Carbowax 20m on CarboBlack B 60/80 6ft 2.1mm ID, SS, Varian 3700 Vista S
88012-840	Packed Column	5% Carbowax 20M Carboblack B 60/80 6', 1/8", SS, OC
88012-84090	Packed Column	5% Carbowax 20m on CarboBlack B 60/80 6ft, 2mmID SS PE AutoSys NOC
88012-893	Packed Column	5% Carbowax 20m on CarboBlack B 60/80, 6ft, 1/8in, 2.1mmID, SS For Gow Mac
88012-895R	Packed Column	5% Carbowax 20M CarboBlack B 60/80 6' 1/8" SS SRI 8610C Dual GC Right Side
88013-800	Packed Column	1% Rt-1000 on CarboBlack B 60/80, 8ftx1/8in, 2.1mm ID, Stainless
88013-810	Packed Column	1% Rt-1000 Carboblk B 60/80 8', 1/8", SS, HP
88013-888	Packed Column	1% Rt-1000 Carboblack B 60/80 8', 1/8", SS, Config for SRI-310 Notch 1/4" from €
88013-895	Packed Column	1% Rt-1000 on CarboBlack B 60/80, 8ftx1/8in, 2.1mm ID, Stainless, SRI 8610C
88014-800	Packed Column	Molesieve 5A 80/100 10ftx1/8in 2.1mm ID SS
88014-80090	Packed Column	Molesieve 5A, 80/100 10ftx1/8in, 2.1mm ID, SS, NOC
88014-810	Packed Column	Molesieve 5A 80/100 10', 1/8", SS
88014-81090	Packed Column	Molesieve 5A 80/100 10', 1/8", SS, NOC
88014-820	Packed Column	Molesieve 5A 80/100 10'x 1/8" 2.1mmID SS

Chromalytic Technology Pty Ltd

AUSTRALIAN Distributors

03 9762 2034

		+61(0)3 9762 2034 ECH nology Pty Ltd	Australian Distributors Importers & Manufacturers www.chromtech.net.au
Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA			