

405 [Ctrl "F"] to SEARCH for Item > Description/Cat# etc Go To www.chromtech.net.au/flip/catalogs/"SUPPLIER" THEN add "/index.php" to URL

VALUE PLASTICS : 2014 PRODUCT LIST v.016

see FlipPAGE Catalog
www.chromtech.net.au/flip/catalogs/valueplastics/

[Ctrl F]
> Cat.#s

> Current System AUD Prices



p10

DESIGN CENTER CUSTOM LUERS:

CF104 (-6005)	Male Luer Integral Lock Ring Plug, O.033 Orifice at Luer Tip
CF210 (-6005)	Male Luer to Female Luer Thread Style Coupler (O.125 Center Bond-in Port)
CF213 (-3)	Male Luer Integral Lock Ring Plug, Closed at Grip (O.055 to O.060 Core)
CF224 (-9)	Male Luer Integral Lock Ring to 500 Series Barb, 5/32" (4 mm) ID Tubing (O.076 bore)
CF233 (-6005)	Female Extended Luer Thread Style to 200 Series Barb, 1/16" (1.6 mm) ID Tubing
CF235 (-9 -91)	Male Luer to Female Luer Thread Style Coupler (O.023 Thru Bore with O.033 Male Side Bond-in Port)
CF239 (-6005)	Male Luer Integral Lock Ring to Female Luer Thread Style Extended Coupler
CF322 (-1)	Female Luer Lug Style Flare to 1/4-32 UNF Thread
CF226 (-6005)	High Flow Connector to 500 Series Barb, 1/4" (6.4 mm) ID Tubing (May be used with separate rotating lock ring)
CF015 (-1)	Female Luer Lug Style Flare to M6x.75 Thread
CF131 (-1)	Male Luer Integral Lock Ring Plug, Closed at Grip (Short Luer)
CF141 (-9)	Male Luer to Female Luer Thread Style Coupler (O.045 Thru Bore with O.055 Male Side Bond-in Port)
CF148 (-9002)	Male Luer to Female Luer Thread Style Coupler (O.045 Thru Bore with O.080 Male Side Bond-in Port)

p11

DESIGN CENTER

CUSTOM TUBE-TO-TUBE FITTINGS: CUSTOM THREADED:

CF001 (-6005)	Bottom Sealing 1/4-28 UNF Thread To Classic Series Barb, 1/16" (1.6 mm) ID Tubing
CF165 (-6005)	1/4-28 UNF Thread with O-Ring Seal and 5/16" Hex to Classic Series Barb 1/16" (1.6 mm) ID Tubing
CF166 (-6005)	1/4-28 UNF Thread Plug with O-Ring Seal and 5/16" Hex
CF173 (-6005)	Bottom Sealing 1/4-28 UNF To 200 Series Barb, 3/16" (4.8 mm) ID Tubing
CF202 (-J1A)	10-32 UNF To Tube Elbow With Custom Thread Orientation and 400 Series Barb, 3/32" (2.4 mm) ID Tubing
CF079 (-1)	1/8" Tee With Blank Single Leg to 200 Series Barb, for 1/8" (3.2 mm) ID Tubing
CF128 (-1)	Straight Through Connector for Orifice Insert, 200 Series Barbs, 1/8" (3.2 mm) ID Tubing
CF302 (-1)	Tee Reduction Connector with 400 Series Barbs, 1/16" (1.6 mm) and 3/32" (2.4 mm) ID Tubing

CUSTOM ASSEMBLIES:

CA072	Custom Assembly LE230 and FSLLR
CA210	Custom Assembly FTL220-9, MTL220-9 and UR00-2047 Tube

QUICK CONNECTS

p13

MQCF230 (-1 -2 -3 -4 -5 -8)	Dual Latch Quick Connect Female 200 Series Barb 1/8" (3.2 mm) ID Tubing
MQCF240 (-1 -2 -3 -4 -5 -8)	Dual Latch Quick Connect Female 200 Series Barb 5/32" (4.0 mm) ID Tubing
MQCF250 (-1 -2 -3 -4 -5 -8)	Dual Latch Quick Connect Female 200 Series Barb 3/16" (4.8 mm) ID Tubing
MQCRM230 (-001 -002 -003 -04 -05 -08B)	Nylon, Buna-N O-Ring Dual Latch Quick Connect Male 200 Series Barb 1/8" (3.2 mm) ID Tubing
MQCRM240 (-001 -002 -003 -04 -05 -08B)	Nylon, Buna-N O-Ring Dual Latch Quick Connect Male 200 Series Barb 5/32" (4.0 mm) ID Tubing
MQCRM250 (-001 -002 -003 -04 -05 -08B)	Nylon, Buna-N O-Ring Dual Latch Quick Connect Male 200 Series Barb 3/16" (4.8 mm) ID Tubing
-001 White Nylon,-005 Blue Nylon,-001 White Nylon,-005 Blue Nylon,-001 White Nylon,-005 Blue Nylon	
MQC SERIES:	
Male Open Flow }	
MQCMF230-901	Bag of 50 Dual Latch Quick Connect Male and Female Sets, 200 Series Barb 1/8" (3.2 mm) ID Tubing, Blue Female and White Male
MQCMF240-901	Bag of 50 Dual Latch Quick Connect Male and Female Sets, 200 Series Barb 5/32" (4.0 mm) ID Tubing, Blue Female and White Male
MQCMF250-901	Bag of 50 Dual Latch Quick Connect Male and Female Sets, 200 Series Barb 3/16" (4.8 mm) ID Tubing, Blue Female and White Male

MQC SERIES:

Male and Female Sets

MQC SERIES: Female Open Flow

Quick Connect Series SBL

Quick Connect Series XQ

QUICK CONNECTS

p14

SBLF013 (-1 -2 -8B -CM030)	Side Latch Quick Connect Female 500 Series Barb, 1/8" (3.2 mm) ID Tubing
SBLF035 (-1 -2 -8B -CM030)	Side Latch Quick Connect Female 500 Series Barb, 3/16" (4.8 mm) ID Tubing
SBL SERIES:	
Female Open Flow	
SBLM013 (-001 -002 -004 -005)	Side Latch Quick Connect Male 500 Series Barb, 1/8" (3.2 mm) ID Tubing
SBL SERIES:	
Male Open Flow	
-001 Gray Nylon	
-002 Blue Nylon	
SBLM035 (-001 -002 -004 -005)	Side Latch Quick Connect Male 500 Series Barb, 3/16" (4.8 mm) ID Tubing
-001 Gray Nylon	
-002 Blue Nylon	
SBLMFBG013 (-002)	
SBL SERIES:	

**HROMalytic** +61(0)3 9762 2034
ECHnology Pty Ltd
Website NEW : www.chromalytic.net.au E-mail : info@chromtech.net.au Tel: 03 9762 2034 . . . in AUSTRALIA

Australian Distributors
Importers & Manufacturers
www.chromtech.net.au