

Male and Female Sets
SBLMFBG035 (-004)
SBLMFBG013 (-001)
SBLMFBG035 (-003)

Bag of 50 Side Latch Quick Connect Male and Female Sets, 500 Series Barb 1/8" (3.2 mm) ID Tubing, Blue Male and Grey Female

[Ctrl F]
> Cat.#s

> Current System AUD Prices



QUICK CONNECTS

p15

XQ SERIES:Female Open Flow Straight

XQSF755 (-1006) XQ Series Female Open Flow Connector, 700 Series Barb, 1/4" (6.4 mm) ID Tubing

XQSF770 (-1006 -1007) XQ Series Female Open Flow Connector, 700 Series Barb, 3/8" (9.5 mm) ID Tubing

XQ SERIES:Female Valved Straight

XQSVF755 (-1006-B -1007-B -6) XQ Series Female Valved Connector, 700 Series Barb, 1/4" (6.4 mm) ID Tubing

XQSVF765 (-1006-B -1007-B) XQ Series Female Valved Connector, 700 Series Barb, 5/16" (8.0 mm) ID Tubing

XQSVF770 (-1006-B -1007-B -6) XQ Series Female Valved Connector, 700 Series Barb, 3/8" (9.5 mm) ID Tubing

XQSBF755 (-1006) XQ Series Female Open Flow Panel Mount Connector with 11/16-24 UNEF Thread, 700 Series Barb, 1/4" (6.4 mm) ID Tubing, Nickel-Plated Brass Hex Nut (included)

XQSBF770 (-1006) XQ Series Female Open Flow Panel Mount Connector with 11/16-24 UNEF Thread, 700 Series Barb, 3/8" (9.5 mm) ID Tubing, Nickel-Plated Brass Hex Nut (included)

XQ SERIES:Female Open Flow Panel Mount

XQSVBF755 (-1006-B) XQ Series Female Valved Panel Mount Connector with 11/16-24 UNEF Thread, 700 Series Barb, 1/4" (6.4 mm) ID Tubing, Nickel-Plated Brass Hex Nut (included)

XQSVBF770 (-1006-B) XQ Series Female Valved Panel Mount Connector with 11/16-24 UNEF Thread, 700 Series Barb, 3/8" (9.5 mm) ID Tubing, Nickel-Plated Brass Hex Nut (included)

XQ SERIES:Female Valved Panel Mount

QUICK CONNECTS

p16

XQCV770 (-1006-B -1007-B -6) XQ Series Male Valved Connector, 700 Series Barb, 3/8" (9.5 mm) ID Tubing

XQCM755 (-1006-B) XQ Series Male Open Flow Connector, 700 Series Barb, 1/4" (6.4 mm) ID Tubing

XQCM770 (-1006-B) XQ Series Male Open Flow Connector, 700 Series Barb, 3/8" (9.5 mm) ID Tubing

XQCV755 (-1006-B -6006-EP) XQ Series Male Valved Connector, 700 Series Barb, 1/4" (6.4 mm) ID Tubing

XQCV765 (-1006-B -1007-B) XQ Series Male Valved Connector, 700 Series Barb, 5/16" (7.9 mm) ID Tubing

XQ SERIES:

Male Open Flow Straight

XQ SERIES:

Male Valved Straight

QUICK CONNECTS

XQCLM755 (-1006-B) XQ Series Male Open Flow Elbow Connector, 700 Series Barb, 1/4" (6.4 mm) ID Tubing

XQCLM770 (-1006-B) XQ Series Male Open Flow Elbow Connector, 700 Series Barb, 3/8" (9.5 mm) ID Tubing

XQ SERIES:

Male Open Flow Elbow

XQCVLM755 (-1006-B) XQ Series Elbow Male Valved Connector, 700 Series Barbs, 1/4" (6.4 mm) ID Tubing

XQ SERIES:

Male Valved Elbow

PM4N

(Nickel-Plated Brass) XQ Series 11/16-24 UNEF Panel Mount Nut

XQ SERIES:

Panel Mount Nut

XQCBM755 (-1006-B) XQ Series Male Open Flow Panel Mount Connector with 11/16-24 UNEF Thread, 700 Series Barb, 1/4" (6.4 mm) ID Tubing, Nickel-Plated Brass Hex Nut (included)

XQCVBM755 (-1006-B) XQ Series Male Valved Panel Mount Connector with 11/16-24 UNEF Thread, 700 Series Barb, 1/4" (6.4 mm) ID Tubing, Nickel-Plated Brass Hex Nut (included)

XQCVBM770 (-1006-B) XQ Series Male Valved Panel Mount Connector with 11/16-24 UNEF Thread, 700 Series Barb, 3/8" (9.5 mm) ID Tubing, Nickel-Plated Brass Hex Nut (included)

XQCBM770 (-1006-B) XQ Series Male Open Flow Panel Mount Connector with 11/16-24 UNEF Thread, 700 Series Barb, 3/8" (9.5 mm) ID Tubing, Nickel-Plated Brass Hex Nut (included)

XQ SERIES:

Male Valved Panel Mount

XQ SERIES:Male Open Flow Panel Mount

CHECK VALVES

SCV03052: (Clear and Blue MABS w/Silicone Diaphragm) Check Valve, Pocket for .165" (4.2 mm) OD Tubing to Socket Fitting .122" (3.1 mm) ID x .165" (4.2 mm) OD Tubing Cracking Pressure: 1.450-4.351 psig Max. Back Pressure: 304.579 psig, max 30 sec. Flow Rate: max 200 ml/min Flow Direction: Left to right

SCV04052 (Clear and Blue SAN w/Silicone Diaphragm) Check Valve, Female Locking Luer to Male Locking Luer Cracking Pressure: 1.450-4.351 psig

Max. Back Pressure: 304.579 psig, max 30 sec. Flow Rate: max 200 ml/min Flow Direction: Left to right

SCV05052 (Blue SAN and Clear MABS w/Silicone Diaphragm) Check Valve, Pocket for .165" (4.2 mm) OD Tubing to Male Locking Luer Cracking Pressure: 1.450-4.351 psig Max. Back Pressure: 304.579 psig, max 30 sec. Flow Rate: max 200 ml/min Flow Direction: Left to right