

Cracking Pressure: = .087 psig Max. Back Pressure: 116.030 psig Flow Rate: = 150 ml/min Flow Direction: Left to right
SCV06265 (Blue and Clear Polycarbonate w/Silicone Diaphragm) Check Valve, Autoclave
OD Tubing x 2

(Ctrl F)
> Cat.#s

> Current System AUD Prices



nm)

Cracking Pressure: = .087 psig Max. Back Pressure: 87.023 psig Flow Rate: = 150 ml/min Flow Direction: Left to right

CHECK VALVES

Check Valve Series DCV

DCV114 (-001) Radiation-Stable Polycarbonate Double Check Valve, Tubing Pocket Chimney Port Cracking Pressure: 2-5 psi
DCV118 (-001) Radiation-Stable Polycarbonate Double Check Valve, Female Luer Chimney Port Cracking Pressure: 2-5 psi
DCV125 (-001) Radiation-Stable Polycarbonate Double Check Valve, Female Luer Chimney Port, Rotating Luer Lock Exit Port Cracking Pressure: 2-5 psi
DCV115 (-001) Radiation-Stable Polycarbonate Double Check Valve, Tubing Pocket Chimney Port, Rotating Luer Lock Exit Port Cracking Pressure: 2-5 psi

DCV SERIES:

Double Check Valve, Female Luer Chimney Port

LUER FITTINGS MALE LUER: Integral Lock Ring

MTLL004 (-1 -2 -3 -4 -5 -06 -60) Male Luer Integral Lock Ring to 500 Series Barb, 1/16" (1.6 mm) ID Tubing
MTLL210 (-1 -2 -3 -4 -5 -06 -60) Male Luer Integral Lock Ring to 200 Series Barb, 1/16" (1.6 mm) ID Tubing
MTLL410 (-1 -6005 -9 -9002 -J1) Male Luer Integral Lock Ring to 400 Series Barb, 1/16" (1.6 mm) ID Tubing
MTLL007 (-1 -2 -3 -4 -5 -6005 -60) Male Luer Integral Lock Ring to 500 Series Barb, 3/32" (2.4 mm) ID Tubing
MTLL220 (-1 -2 -3 -4 -5 -06 -60) Male Luer Integral Lock Ring to 200 Series Barb, 3/32" (2.4 mm) ID Tubing
MTLL420 (-1 -6005 -9 -9002 -J1) Male Luer Integral Lock Ring to 400 Series Barb, 3/32" (2.4 mm) ID Tubing
MTLL013 (-1 -2 -3 -4 -5 -06 -60) Male Luer Integral Lock Ring to 500 Series Barb, 1/8" (3.2 mm) ID Tubing
MTLL230 (-1 -2 -3 -4 -5 -06 -60) Male Luer Integral Lock Ring to 200 Series Barb, 1/8" (3.2 mm) ID Tubing
MTLL430 (-1 -3 -6005 -9 -9002 -J1) Male Luer Integral Lock Ring to 400 Series Barb, 1/8" (3.2 mm) ID Tubing
MTLL025 (-1 -2 -3 -4 -5 -6005 -60) Male Luer Integral Lock Ring to 500 Series Barb, 5/32" (4.0 mm) ID Tubing
MTLL240 (-1 -2 -3 -4 -5 -6005 -60) Male Luer Integral Lock Ring to 200 Series Barb, 5/32" (4.0 mm) ID Tubing
MTLL445 (-1 -6005 -9 -9002 -J1) Male Luer Integral Lock Ring to 400 Series Barb, 1/70" (4.3 mm) ID Tubing
MTLL035 (-1 -2 -3 -4 -5 -06 -60) Male Luer Integral Lock Ring to 500 Series Barb, 3/16" (4.8 mm) ID Tubing
MTLL250 (-1 -2 -3 -4 -5 -06 -60) Male Luer Integral Lock Ring to 200 Series Barb, 3/16" (4.8 mm) ID Tubing
MTLL450 (-1 -6005 -9 -9002 -J1) Male Luer Integral Lock Ring to 400 Series Barb, 3/16" (4.8 mm) ID Tubing
MTLL055 (-1 -2 -3 -4 -06 -6005 -60) Male Luer Integral Lock Ring to 500 Series Barb, 1/4" (6.4 mm) ID Tubing
MTLL360 (-1 -2 -6005 -9 -9002 -J1) Male Luer Integral Lock Ring to 300 Series Barb, 1/4" (6.4 mm) ID Tubing

p36

LUER FITTINGS

MLRL004 (-1 -6005 -9) Male Luer to 500 Series Barb, 1/16" (1.6 mm) ID Tubing (May be used with separate rotating lock ring FSLLR)
MLRL007 (-1 -6005 -9) Male Luer to 500 Series Barb, 3/32" (2.4 mm) ID Tubing (May be used with separate rotating lock ring FSLLR)
MLRL013 (-1 -6005 -9) Male Luer to 500 Series Barb, 1/8" (3.2 mm) ID Tubing (May be used with separate rotating lock ring FSLLR)
MLRL025 (-1 -6005 -9) Male Luer to 500 Series Barb, 5/32" (4.0 mm) ID Tubing (May be used with separate rotating lock ring FSLLR)
MLRL035 (-1 -6005 -9 -9002) Male Luer to 500 Series Barb, 3/16" (4.8 mm) ID Tubing (May be used with separate rotating lock ring FSLLR)
MLRL055 (-1 -6005 -9) Male Luer to 500 Series Barb, 1/4" (6.4 mm) ID Tubing (May be used with separate rotating lock ring FSLLR)
MLSL004 (-1 -6005 -9) Male Luer to 500 Series Barb, 1/16" (1.6 mm) ID Tubing (May be used with separate stationary lock ring FSLLR)
MLSL007 (-1 -6005 -9) Male Luer to 500 Series Barb, 3/32" (2.4 mm) ID Tubing (May be used with separate stationary lock ring FSLLR)
MLSL013 (-1 -6005 -9) Male Luer to 500 Series Barb, 1/8" (3.2 mm) ID Tubing (May be used with separate stationary lock ring FSLLR)
MLSL025 (-1 -6005 -9) Male Luer to 500 Series Barb, 5/32" (4.0 mm) ID Tubing (May be used with separate stationary lock ring FSLLR)
MLSL035 (-1 -6005 -9) Male Luer to 500 Series Barb, 3/16" (4.8 mm) ID Tubing (May be used with separate stationary lock ring FSLLR)
MLSL055 (-1 -6005 -9) Male Luer to 500 Series Barb, 1/4" (6.4 mm) ID Tubing (May be used with separate stationary lock ring FSLLR)
FSLLR (-1 -2 -3 -4 -5 -06 -6005 -60) Female Luer Lock Ring

MALE LUER:

DCV SERIES:

MTLS210 (-1 -6005 -9 -J1A) Male Luer Slip to 200 Series Barb, 1/16" (1.6 mm) ID Tubing
MSL004 (-1 -6005 -9 -9002) Male Luer Slip to 500 Series Barb, 1/16" (1.6 mm) ID Tubing
MTLS220 (-1 -3 -5 -6005 -81 -9) Male Luer Slip to 200 Series Barb, 3/32" (2.4 mm) ID Tubing
MSL007 (-1 -6005 -9 -9002) Male Luer Slip to 500 Series Barb, 3/32" (2.4 mm) ID Tubing
MTLS230 (-1 -3 -5 -6005 -81 -9) Male Luer Slip to 200 Series Barb, 1/8" (3.2 mm) ID Tubing
MSL013 (-1 -6005 -9 -9002) Male Luer Slip to 500 Series Barb, 1/8" (3.2 mm) ID Tubing
MTLS240 (-1 -2 -5 -6005 -81 -9) Male Luer Slip to 200 Series Barb, 5/32" (4.0 mm) ID Tubing
MSL025 (-1 -6005 -9 -9002) Male Luer Slip to 500 Series Barb, 5/32" (4.0 mm) ID Tubing
MSL035 (-1 -6005 -9 -9002 -J1A) Male Luer Slip to 500 Series Barb, 3/16" (4.8 mm) ID Tubing
MSL055 (-1 -6005 -9 -9002) Male Luer Slip to 500 Series Barb, 1/4" (6.4 mm) ID Tubing

MALE LUER: Slip

FEMALE LUER: Thread Style

FTLL004 (-1 -2 -3 -4 -5 -06 -600) Female Luer Thread Style to 500 Series Barb, 1/16" (1.6 mm) ID Tubing
FTLL210 (-1 -2 -3 -4 -5 -6005 -9) Female Luer Thread Style to 200 Series Barb, 1/16" (1.6 mm) ID Tubing
FTLL410 (-1 -6005 -9 -9002 -J1) Female Luer Thread Style to 400 Series Barb, 1/16" (1.6 mm) ID Tubing
FTLL007 (-1 -2 -3 -4 -5 -06 -600) Female Luer Thread Style to 500 Series Barb, 3/32" (2.4 mm) ID Tubing
FTLL013 (-1 -2 -3 -4 -5 -06 -600) Female Luer Thread Style to 500 Series Barb, 1/8" (3.2 mm) ID Tubing
FTLL420 (-1 -6005 -9 -9002 -J1) Female Luer Thread Style to 400 Series Barb, 3/32" (2.4 mm) ID Tubing
FTLL230 (-1 -2 -3 -5 -6005 -9 -9) Female Luer Thread Style to 200 Series Barb, 1/8" (3.2 mm) ID Tubing