

FTLL220 (-1 -2 -3 -5 -6005 -9 -9 Female Luer Thread Style to 200 Series Barb, 3/32" (2.4 mm) ID Tubing  
FTLL430 (-1 -6005 -9 -9002 -J1) Female Luer Thread Style to 400 Series Barb, 1/8" (3.2 mm) ID Tubing

(Ctrl F)  
> Cat.#s

> Current System AUD Prices



p38

#### LUER FITTINGS

##### FEMALE LUER: Thread Style

##### FEMALE LUER: Smooth Bore Thread Style

FTLL025 (-1 -2 -3 -4 -5 -06 -600 Female Luer Thread Style to 500 Series Barb, 5/32" (4.0 mm) ID Tubing  
FTLL240 (-1 -2 -3 -5 -6005 -9 -9 Female Luer Thread Style to 200 Series Barb, 5/32" (4.0 mm) ID Tubing  
FTLL445 (-1 -6005 -9 -9002 -J1) Female Luer Thread Style to 400 Series Barb, .170" (4.3 mm) ID Tubing  
FTLL035 (-1 -2 -3 -4 -5 -06 -600 Female Luer Thread Style to 500 Series Barb, 3/16" (4.8 mm) ID Tubing  
FTLL250 (-1 -3 -5 -6005 -9 -900 Female Luer Thread Style to 200 Series Barb, 3/16" (4.8 mm) ID Tubing  
FTLL450 (-1 -6005 -9 -9002 -J1) Female Luer Thread Style to 400 Series Barb, 3/16" (4.8 mm) ID Tubing  
FTLL055 (-1 -2 -3 -4 -5 -06 -600 Female Luer Thread Style to 500 Series Barb, 1/4" (6.4 mm) ID Tubing  
FTLL360 (-1 -3 -5 -6005 -9 -900 Female Luer Thread Style to 300 Series Barb, 1/4" (6.4 mm) ID Tubing  
FTLLSB004 (-1 -6005 -9) Female Luer Thread Style Smooth Bore to 500 Series Barb, 1/16" (1.6 mm) ID Tubing  
FTLLSB007 (-1 -4 -6005 -9) Female Luer Thread Style Smooth Bore to 500 Series Barb, 3/32" (2.4 mm) ID Tubing  
FTLLSB013 (-1 -6005 -9) Female Luer Thread Style Smooth Bore to 500 Series Barb, 1/8" (3.2 mm) ID Tubing  
FTL210 (-1 -6005 -9 -J1A) Female Luer Lug Style to 200 Series Barb, 1/16" (1.6 mm) ID Tubing  
FTL20 (-1 -6005 -07 -81 -9 -J1A) Female Luer Lug Style to Classic Series Barb, 3/32" (2.4 mm) ID Tubing  
FTL220 (-1 -3 -5 -6005 -9 -J1A) Female Luer Lug Style to 200 Series Barb, 3/32" (2.4 mm) ID Tubing  
FTL30 (-1 -6005 -9 -J1A) Female Luer Lug Style to Classic Series Barb, 1/8" (3.2 mm) ID Tubing  
FTL10 (-1 -6005 -9 -J1A) Female Luer Lug Style to Classic Series Barb, 1/16" (1.6 mm) ID Tubing

##### FEMALE LUER:

p39

#### LUER FITTINGS

##### FEMALE LUER:Lug Style

FTL230 (-1 -3 -5 -6005 -9 -J1A) Female Luer Lug Style to 200 Series Barb, 1/8" (3.2 mm) ID Tubing  
FTL240 (-1 -6005 -9 -J1A) Female Luer Lug Style to 200 Series Barb, 5/32" (4.0 mm) ID Tubing  
MLRLC (-1 -6005 -9) Male Luer Coupler (May be used with separate rotating lock rings FSLLR)  
MTLCS (-1 -6005 -9 -J1A) Male Luer Slip Coupler  
FTLLC (-1 -6005 -9 -9002 -J1A) Female Luer Thread Style Coupler  
LUER: Adapters, Couplers, and Lock Rings  
FSLLR (-1 -2 -3 -4 -5 -06 -6005) Finger Snap Luer Lock Ring  
LT878 (-1 -6005 -9 -9002) Female Luer Thread Style (2) to Male Luer Tee (May be used with separate rotating lock ring FSLLR)  
FTLC (-1 -6005 -9 -9002 -J1A) Female Luer Lug Style Coupler  
LC34 (-1 -6005 -9 -9002 -J1A) Male Luer Integral Lock Ring to Female Luer Thread Style Coupler  
LT787 (-1 -6005 -8012 -9 -9002) Male Luer (2) to Female Luer Thread Style Tee (May be used with separate rotating lock ring FSLLR)  
FTLT (-1 -6005 -9 -J1A) Female Luer Lug Style Tee  
FTLLE (-1 -6005 -9 -J1A) Female Luer Thread Style Elbow  
LC78 (-1 -6005 -9 -9002 -J1A) Male Luer to Female Luer Thread Style Coupler (May be used with separate rotating lock ring FSLLR)  
FTLE (-1 -6005 -9 -J1A) Female Luer Lug Style Elbow  
LE87 (-1 -6005 -8003 -9 -9002) Male Luer to Female Luer Thread Style Elbow (May be used with separate rotating lock ring FSLLR)  
LE7220 (-1 -2 -9) Male Luer to 200 Series Barb Elbow, 3/32" (2.4 mm) ID Tubing (May be used with separate rotating lock ring FSLLR)

p40

#### LUERFITTINGS

##### LUER: Adapters, Couplers, and Lock Rings

##### LUER: Plugs and Caps

LE7230 (-1 -2 -6005 -9 -9010) Male Luer to 200 Series Barb Elbow 1/8" (3.2 mm) ID Tubing (May be used with separate rotating lock ring FSLLR)  
CA091 (-001) Gamma Stable P Male Luer Elbow to 3/16" Classic Series Barb, (CF361-9002) with Rotating Lock Ring (FSLLR-9002)  
MTLLP (-1 -2 -3 -6005 -07 -9 -J) Male Luer Integral Lock Ring Plug, Closed at Luer Tip  
LP4 (-1 -2 -3 -4 -5 -6005 -9 -900) Male Luer Integral Lock Ring Plug, Closed at Grip  
VLP4 (-1 -3 -6005 -81 -J1A) Male Luer Integral Lock Ring Vented Plug, Closed at Grip  
MLRPL (-1 -6005 -9) Male Luer Plug (May be used with separate rotating lock ring FSLLR)  
MLSLP (-1 -6005 -9) Male Luer Plug (May be used with separate stationary lock ring FSLLR)  
MTLP (-1 -6005 -9 -J1A) Male Luer Plug, Closed at Tether Loop (May be used with separate stationary lock ring FSLLR)  
MTLSP (-1 -6005 -81 -9 -J1A) Male Luer Slip Plug, Closed at Grip  
FTLP (-1 -6005 -9 -J1A) Female Luer Lug Style Cap with Tether Loop  
FTLLP (-1 -2 -3 -5 -6005 -07 -81) Female Luer Thread Style Cap  
LP34 (-1 -3 -5 -6005 -9 -9002 -J1A)

p41

##### LUER FITTINGS LUER TO THREAD:

##### Male

XMLRL (-1 -6005 -9 -9002) Male Luer with 1/4" Hex to 10-32 Special Tapered Thread (May be used with separate rotating lock ring FSLLR)  
SMLRL (-1 -6005 -9 -J1A) Male Luer with 5/16" Hex to 1/4-28 UNF Thread (May be used with separate rotating lock ring FSLLR)  
BSMLRL (-6005 -J1A) Male Luer with 5/16" Hex to 1/4-28 Bottom-Sealing Thread (May be used with separate