



rotating lock ring FSLLR)
ABSML-6005 UNDER (-1 -2 -3 - Male Luer with Rotating Lock Ring and 5/16" Hex to 1/4-28 UNF Bottom Sea
ABSML-J1A UNDER (-1 -2 -3 -4 Male Luer with Rotating Lock Ring and 5/16" Hex to 1/4-28 UNF Bottom Sea
XMTLL (-1 -6005 -9 -J1A) Male Luer Integral Lock Ring to 10-32 Special Tapered Thread
SMTLL (-1 -6005 -9 -J1A) Male Luer Integral Lock Ring to 1/4-28 UNF Thread
18MTLL (-1 -2 -6005 -J1A) Male Luer Integral Lock Ring with 7/16" Hex to 1/8-27 NPT Thread
14MTLL (-1 -2 -6005) Male Luer Integral Lock Ring with 9/16" Hex to 1/4-18 NPT Thread

p42

LUER FITTINGS

FTLLBMLRL (-1 -6005) Female Luer Thread Style Panel Mount 1/4-28 UNF to Male Luer (May be used with separate rotating lock ring FSLLR)

PANEL MOUNTS:

Female Thread Style

LUER TO THREAD:Female

KFTL (-1 -6005 -9 -J1A) Female Luer Lug Style with 1/4" Hex to 10-32 UNF Thread

18FTLL (-1 -6005 -J1A) Female Luer Thread Style with 7/16" Hex to 1/8-27 NPT Thread

SFTL (-1 -6005 -9) Female Luer Lug Style with 5/16" Hex to 1/4-28 UNF Thread

18LFTLL (-1 -4 -5 -6005 -J1A) Female Luer Thread Style Elbow with 7/16" Hex to 1/8-27 NPT Thread

FTLLB210 (-1 -2 -6005 -9 -J1A) Female Luer Thread Style Panel Mount 1/4-28 UNF to 200 Series Barb, 1/16" (1.6 mm) ID Tubing

FTLLB230 (-1 -2 -6005 -9 -J1A) Female Luer Thread Style Panel Mount 1/4-28 UNF to 200 Series Barb, 1/8" (3.2 mm) ID Tubing

FTLLB220 (-1 -2 -6005 -9 -J1A) Female Luer Thread Style Panel Mount 1/4-28 UNF to 200 Series Barb, 3/32" (2.4 mm) ID Tubing

BSFTLL (-1 -6005 -J1A) Female Luer Thread Style with 5/16" Hex to 1/4-28 UNF Bottom Sealing Thread

KFTLL (-1 -6005 -9 -J1A) Female Luer Thread Style with 1/4" Hex to 10-32 UNF Thread

XFTLL (-1 -6005 -9 -J1A) Female Luer Thread Style with 1/4" Hex to 10-32 Special Tapered Thread

SFTLL (-1 -2 -4 -06 -6005 -9 -J1) Female Luer Thread Style with 5/16" Hex to 1/4-28 UNF Thread

XFTL (-1 -6005 -9 -J1A) Female Luer Lug Style with 1/4" Hex to 10-32 Special Tapered Thread

p43

LUER FITTINGS PANEL MOUNTS:

Female Lug Style and Male Luer

PANEL MOUNT ACCESSORIES: Lock Nuts and Color Coding Rings

FTLB210 (-1 -6005 -9 -J1A) Female Luer Lug Style Panel Mount 1/4-28 UNF to 200 Series Barb, 1/16" (1.6 mm) ID Tubing

CCR (-1 -2 -3 -4 -5 -06 -07) Color Coded Ring (For use with PMS, PMK, FTLLB or FTLB panel mount fittings)

CCLR (-1 -2 -3 -4 -5 -06 -07) Color Coded Lock Ring (For use with PMS, PMK, FTLLB or FTLB panel mount fittings)

PMKN (-XO) Panel Mount Nut 10-32 UNF with 3/8" Hex (For use with PMK panel mount fittings)

PMSN (-XO) Panel Mount Nut 1/4-28 UNF with 7/16" Hex (For use with PMS, FTLB, and FTLLB panel mount fittings)

LNS (-1 -2 -3 -4 -5 -06 -07 -6005) 1/4-28 UNF Panel Mount Lock Nut (For use with PMS, FTLLB or FTLB panel mount fittings)

FTLB220 (-1 -6005 -9 -J1A) Female Luer Lug Style Panel Mount 1/4-28 UNF to 200 Series Barb, 3/32" (2.4 mm) ID Tubing

FTLB230 (-1 -6005 -9 -J1A) Female Luer Lug Style Panel Mount 1/4-28 UNF to 200 Series Barb, 1/8" (3.2 mm) ID Tubing

MLRLB210 (-1 -6005) Male Luer Panel Mount 10-32 UNF to 200 Series Barb, 1/16" (1.6 mm) ID Tubing, (May be used with separate rotating lock ring FSLLR)

MLRLB220 (-1 -6005) Male Luer Panel Mount 10-32 UNF to 200 Series Barb, 3/32" (2.4 mm) ID Tubing, (May be used with separate rotating lock ring FSLLR)

MLRLB230 (-1 -6005) Male Luer Panel Mount 1/4-28 UNF to 200 Series Barb, 1/8" (3.2 mm) ID Tubing, (May be used with separate rotating lock ring FSLLR)

PRESSURE

BPLF230 (-8012) Quarter-turn Female Blood Pressure Cuff Connector to 200 Series Barb, 1/8" (3.2 mm) Tubing ID

BPLF240 (-8012) Quarter-turn Female Blood Pressure Cuff Connector to 200 Series Barb, 5/32" (4.0 mm) Tubing ID

BPL SERIES:1/4 Turn Cuff Connectors

BPLM230 (-001) White ABS, White Acetal, Buna-N O-Ring Quarter-turn Male Blood Pressure Cuff Connector to 200 Series Barb, 1/8" (3.2 mm) Tubing ID

BPLM240 (-001) White ABS, White Acetal, Buna-N O-Ring Quarter-turn Male Blood Pressure Cuff Connector to 200 Series Barb, 5/32" (4.0 mm) Tubing ID

BPF SERIES:Female Bayonet Style Quick Connect

BPF220 (-001) Black ABS Housing Bayonet-Style Female Quick Connect Fitting, 200 Series Barb, 3/32" (2.4 mm) ID Tubing

BPF230 (-001) Black ABS Housing Bayonet-Style Female Quick Connect Fitting, 200 Series Barb, 1/8" (3.2 mm) ID Tubing

BPF240 (-001) Black ABS Housing Bayonet-Style Female Quick Connect Fitting, 200 Series Barb, 5/32" (4.0 mm) ID Tubing

BPF250 (-001) Black ABS Housing Bayonet-Style Female Quick Connect Fitting, 200 Series Barb, 3/16" (4.8 mm) ID Tubing

p46

BLOOD PRESSURE

BLOOD PRESSURE: Panel Mount Nuts

BPA035 (-001) Black Nylon over White Nylon Blood Pressure Adapter with Internal 5/16-24 UNF Thread and O-Ring to 500 Series Barb, 3/16" (4.8 mm) ID Tubing

BPA055 (-001) Black Nylon over White Nylon Blood Pressure Adapter with Internal 5/16-24 UNF Thread and O-Ring to 500 Series Barb, 1/4" (6.4 mm) ID Tubing

BPA013 (-001) Black Nylon over White Nylon Blood Pressure Adapter with Internal 5/16-24 UNF Thread and O-Ring to 500 Series Barb, 1/8" (3.2 mm) ID Tubing

BPA025 (-001) Black Nylon over White Nylon Blood Pressure Adapter with Internal 5/16-24 UNF Thread and O-Ring to 500 Series Barb, 5/32" (4.0 mm) ID Tubing