

3PF220 (-1 -6005)
 3PF230 (-1 -6005)
 4PX210 (-1 -6005)
 4PX220 (-1 -6005)
 4PX230 (-1 -6005)
 4PDL210 (-1 -6005)
 TUBE-TO-TUBE:Y
 Y055 (-6005)
 Y070 (-0 -6005 -9)
 Y670 (-6005 -9 -J1A)
 Y080 (-0 -6005 -9)
 Y680 (-6005 -9 -J1A)
 Y090 (-0 -6005 -J1A)
 Y100 (-0 -6005 -J1A)
 Y110 (-0 -6005)
 Reference part shown: Y070
LARGE TUBE-TO-TUBE: Y

Three-Port F Style Manifold with 200 Series Barbs for 3/32" (2.4 mm) ID Tubi
 Three-Port F Style Manifold with 200 Series Barbs for 1/8" (3.2 mm) ID Tubin
 Four-Port Cross Style Manifold with 200 Series Barbs for 1/16" (1.6 mm) ID T
 Four-Port Cross Style Manifold with 200 Series Barbs for 3/32" (2.4 mm) ID Tubing
 Four-Port Cross Style Manifold with 200 Series Barbs for 1/8" (3.2 mm) ID Tubing
 Four-Port Double Elbow Style Manifold with 200 Series Barbs, 1/16" (1.6 mm) ID Tubing
 Y Connector with 500 Series Barbs, 1/4" (6.4 mm) ID Tubing
 Y Connector with 500 Series Barbs, 3/8" (9.5 mm) ID Tubing
 Y Connector with 600 Series Barbs, 3/8" (9.5 mm) ID Tubing
 Y Connector with 500 Series Barbs, 1/2" (12.7 mm) ID Tubing
 Y Connector with 600 Series Barbs, 1/2" (12.7 mm) ID Tubing
 Y Connector with 500 Series Barbs, 5/8" (16.0 mm) ID Tubing
 Y Connector with 500 Series Barbs, 3/4" (19.0 mm) ID Tubing
 Y Connector with 500 Series Barbs, 1" (25.4 mm) ID Tubing

[Ctrl F]
 > Cat.#s

> Current System AUD Prices



p63

TUBE-TO-TUBE FITTINGS Multiport

6PDT230 (-1 -6005) Six-Port Double T Style Manifold with 200 Series Barbs for 1/8" (3.2 mm) ID Tubing
 6PTT210 (-1 -6005) Six-Port Thru Flow Double T Style Manifold with 200 Series Barbs for 1/16" (1.6 mm) ID Tubing
 6PTT220 (-1 -6005) Six-Port Thru Flow Double T Style Manifold with 200 Series Barbs for 3/32" (2.4 mm) ID Tubing
 6PTT230 (-1 -6005) Six-Port Thru Flow Double T Style Manifold with 200 Series Barbs for 1/8" (3.2 mm) ID Tubing
 4PDL220 (-1 -6005) Four-Port Double Elbow Style Manifold with 200 Series Barbs, 3/32" (2.4 mm) ID Tubing
 4PDL230 (-1 -6005) Four-Port Double Elbow Style Manifold with 200 Series Barbs, 1/8" (3.2 mm) ID Tubing
 4PLL210 (-1 -6005) Four-Port Thru Flow Double Elbow Style Manifold with 200 Series Barbs, 1/16" (1.6 mm) ID Tubing
 4PLL220 (-1 -6005 -9) Four-Port Thru Flow Double Elbow Style Manifold with 200 Series Barbs, 3/32" (2.4 mm) ID Tubing
 4PLL230 (-1 -2 -6005) Four-Port Thru Flow Double Elbow Style Manifold with 200 Series Barbs, 1/8" (3.2 mm) ID Tubing
 6PDT210 (-1 -6005) Six-Port Double T Style Manifold with 200 Series Barbs for 1/16" (1.6 mm) ID Tubing
 6PDT220 (-1 -6005) Six-Port Double T Style Manifold with 200 Series Barbs for 3/32" (2.4 mm) ID Tubing

p64

TUBE-TO-TUBE FITTINGS Press-In Plugs

PIP230 (-1 -2 -6005 -J1A) Press-In Plug with 200 Series Barb, 1/8" (3.2 mm) ID Tubing
 PIP30 (-1 -2 -6005 -J1A) Press-In Plug with Classic Series Barb, 1/8" (3.2 mm) ID Tubing
 PIP240 (-1 -2 -6005 -J1A) Press-In Plug with 200 Series Barb, 5/32" (4.0 mm) ID Tubing
 PIP40 (-1 -2 -6005 -J1A) Press-In Plug with Classic Series Barb, 5/32" (4.0 mm) ID Tubing
 PIP50 (-1 -2 -6005 -J1A) Press-In Plug with Classic Series Barb, 3/16" (4.8 mm) ID Tubing
 PIP60 (-1 -2 -6005 -J1A) Press-In Plug with Classic Series Barb, 1/4" (6.4 mm) ID Tubing
 PIP670 (-6005) Press-In Plug with 600 Series Barb, 3/8" (9.5 mm) ID Tubing
 PIP680 (-6005) Press-In Plug with 600 Series Barb, 1/2" (12.7 mm) ID Tubing
 PIP070 (-0 -6005) Press-In Plug with 500 Series Barb, 3/8" (9.5 mm) ID Tubing
 PIP080 (-6005) Press-In Plug with 500 Series Barb, 1/2" (12.7 mm) ID tubing
 PIP20 (-1 -2 -6005 -J1A) Press-In Plug with Classic Series Barb, 3/32" (2.4 mm) ID Tubing
 PIP10 (-1 -2 -6005 -J1A) Press-In Plug with Classic Series Barb, 1/16" (1.6 mm) ID Tubing
 PIP210 (-1 -2 -6005 -J1A) Press-In Plug with 200 Series Barb, 1/16" (1.6 mm) ID Tubing
 PIP220 (-1 -2 -6005 -J1A) Press-In Plug with 200 Series Barb, 3/32" (2.4 mm) ID Tubing
 PIP090 (-6005) Press-In Plug with 500 Series Barb, 5/8" (16.0 mm) ID Tubing
 PIP6100 (-6005) Press-In Plug with 600 Series Barb, 3/4" (19.0 mm) ID Tubing

p65

TUBE-TO-TUBE FITTINGS

TUBE-TO-TUBE PANEL MOUNT ACCESSORIES:

Lock Nuts and Color Coding Rings

TUBE-TO-TUBE: Ultrasonically Weldable Barb

CCR (-1 -2 -3 -4 -5 -06 -07) Color Coded Ring (For use with PMS, PMK, FTLLB or FTLB panel mount fittings)
 CCLR (-1 -2 -3 -4 -5 -06 -07) Color Coded Lock Ring (For use with PMS, PMK, FTLLB or FTLB panel mount fittings)
 PMKN (-XO) Panel Mount Nut 10-32 UNF with 3/8" Hex (For use with PMK panel mount fittings)
 PMSN (-XO) Panel Mount Nut 1/4-28 UNF with 7/16" Hex (For use with PMS, FTLB, and FTLLB panel mount fittings)
 LNS (-1 -2 -3 -4 -5 -06 -6005 -07) 1/4-28 UNF Panel Mount Lock Nut (For use with PMS, FTLLB or FTLB panel mount fittings)
 PMK220 (-1 -6005) Panel Mount Connector 10-32 UNF to 200 Series Barbs, 3/32" (2.4 mm) ID Tubing
 PMS230 (-1 -6005) Panel Mount Connector 1/4-28 UNF to 200 Series Barbs, 1/8" (3.2 mm) ID Tubing
 PMK220-210 (-1 -6005) Panel Mount Reduction Connector 10-32 UNF to 200 Series Barbs, 3/32" (2.4 mm) and 1/16" (1.6 mm) ID Tubing
 PMS230-210 (-1 -6005 -J1A) Panel Mount Reduction Connector 1/4-28 UNF to 200 Series Barbs, 1/8" (3.2 mm) and 1/16" (1.6 mm) ID Tubing
 PMS230-220 (-1 -6005) Panel Mount Reduction Connector 1/4-28 UNF to 200 Series Barbs, 1/8" (3.2 mm) and 3/32" (2.4 mm) ID Tubing
 PMK210 (-1 -6005) Panel Mount Connector 10-32 UNF to 200 Series Barbs, 1/16" (1.6 mm) ID Tubing

TUBE-TO-TUBE PANEL MOUNTS: Straight Through and Reducer

U10 (-1 -2 -7 -9) Ultrasonically Weldable Fitting to Classic Series Barb, 1/16" (1.6 mm) ID Tubing
 U20 (-1 -2 -7) Ultrasonically Weldable Fitting to Classic Series Barb, 3/32" (2.4 mm) ID Tubing
 U30 (-1 -2 -7) Ultrasonically Weldable Fitting to Classic Series Barb, 1/8" (3.2 mm) ID Tubing