



p71

THREADED FITTINGS

S30 (-1 -2 -6005 -J1A)	1/4-28 UNF Thread with 5/16" Hex to Classic Series Barb, 1/8" (3.2 mm) ID Tubing
ABR004-6005 UNDER (-1 -2 -3 -1/4-28 UNF Bottom Sealing Rotating Thread with 5/16" Hex to 500 Series Barb, 1/16" (1.6 mm) ID Tubing	
ABR004-J1A UNDER (-1 -2 -3 -1/4-28 UNF Bottom Sealing Rotating Thread with 5/16" Hex to 500 Series Barb, 1/16" (1.6 mm) ID Tubing	
ABR007-6005 UNDER (-1 -2 -3 -1/4-28 UNF Bottom Sealing Rotating Thread with 5/16" Hex to 500 Series Barb, 3/32" (2.4 mm) ID Tubing	
ABR007-J1A UNDER (-1 -2 -3 -1/4-28 UNF Bottom Sealing Rotating Thread with 5/16" Hex to 500 Series Barb, 3/32" (2.4 mm) ID Tubing	
ABR013-6005 UNDER (-1 -2 -3 -1/4-28 UNF Bottom Sealing Rotating Thread with 5/16" Hex to 500 Series Barb, 1/8" (3.2 mm) ID Tubing	
ABR013-J1A UNDER (-1 -2 -3 -1/4-28 UNF Bottom Sealing Rotating Thread with 5/16" Hex to 500 Series Barb, 1/8" (3.2 mm) ID Tubing	
TECS116 (-6005 -J1A)	1/4-28 UNF Bottom Sealing Thread Tube End Coupler with 5/16" Hex, 1/16" (1.6 mm) OD Tubing
TECS118 (-6005 -J1A)	1/4-28 UNF Bottom Sealing Thread Tube End Coupler with 5/16" Hex, 1/8" (3.2 mm) OD Tubing
S240 (-1 -2 -6005 -J1A)	1/4-28 UNF Thread with 5/16" Hex to 200 Series Barb, 5/32" (4.0 mm) ID Tubing
S40 (-1 -2 -6005 -J1A)	1/4-28 UNF Thread with 5/16" Hex to Classic Series Barb, 5/32" (4.0 mm) ID Tubing
S445 (-1 -2 -6005 -J1A)	1/4-28 UNF Thread with 5/16" Hex to 400 Series Barb, .170" (4.3 mm) ID Tubing
S250 (-1 -2 -6005 -J1A)	1/4-28 UNF Thread with 5/16" Hex to 200 Series Barb, 3/16" (4.8 mm) ID Tubing
S450 (-1 -2 -6005 -J1A)	1/4-28 UNF Thread with 5/16" Hex to 400 Series Barb, 3/16" (4.8 mm) ID Tubing
S50 (-1 -2 -6005 -J1A)	1/4-28 UNF Thread with 5/16" Hex to Classic Series Barb, 3/16" (4.8 mm) ID Tubing
SP (-1 -2 -6005 -J1A)	1/4-28 UNF Thread Plug with 5/16" Hex

THREAD:1/4-28 UNF

THREAD:1/4-28 UNF Bottom Sealing

p72

THREADED FITTINGS

M6210 (-1 -2 -6005)	M6x1 Thread with 5/16" Hex to 200 Series Barb, 1/16" (1.6 mm) ID Tubing
M6250 (-1 -2 -6005 -J1A)	M6x1 Thread with 5/16" Hex to 200 Series Barb, 3/16" (4.8 mm) ID Tubing
M6450 (-1 -2 -6005 -J1A)	M6x1 Thread with 5/16" Hex to 400 Series Barb, 3/16" (4.8 mm) ID Tubing
M6P (-1 -2 -6005 -J1A)	M6x1 Thread Plug with 5/16" Hex
M5220 (-1 -2 -6005)	M5x.8 Thread with 1/4" Hex to 200 Series Barb, 3/32" (2.4 mm) ID Tubing
M5230 (-1 -2 -6005)	M5x.8 Thread with 1/4" Hex to 200 Series Barb, 1/8" (3.2 mm) ID Tubing
M5240 (-1 -2 -6005)	M5x.8 Thread with 1/4" Hex to 200 Series Barb, 5/32" (4.0 mm) ID Tubing
M6410 (-1 -2 -6005 -J1A)	M6x1 Thread with 5/16" Hex to 400 Series Barb, 1/16" (1.6 mm) ID Tubing
M6220 (-1 -2 -6005 -J1A)	M6x1 Thread with 5/16" Hex to 200 Series Barb, 3/32" (2.4 mm) ID Tubing
M6420 (-1 -2 -6005 -J1A)	M6x1 Thread with 5/16" Hex to 400 Series Barb, 3/32" (2.4 mm) ID Tubing
M6230 (-1 -2 -6005 -J1A)	M6x1 Thread with 5/16" Hex to 200 Series Barb, 1/8" (3.2 mm) ID Tubing
M6430 (-1 -2 -6005 -J1A)	M6x1 Thread with 5/16" Hex to 400 Series Barb, 1/8" (3.2 mm) ID Tubing
M6240 (-1 -2 -6005 -J1A)	M6x1 Thread with 5/16" Hex to 200 Series Barb, 5/32" (4.0 mm) ID Tubing
M5210 (-1 -2 -6005)	M5x.8 Thread with 1/4" Hex to 200 Series Barb, 1/16" (1.6 mm) ID Tubing

THREAD:M5x.8

M6445 (-1 -2 -6005 -J1A)	M6x1 Thread with 5/16" Hex to 400 Series Barb, .170" (4.3 mm) ID Tubing
--------------------------	---

p73

THREADED FITTINGS

THREAD:1/16-27 NPT

16210 (-1 -2 -6005 -J1A)	1/16-27 NPT Thread with 5/16" Hex to 200 Series Barb, 1/16" (1.6 mm) ID Tubing
1630 (-1 -2 -6005 -J1A)	1/16-27 NPT Thread with 5/16" Hex to Classic Series Barb, 1/8" (3.2 mm) ID Tubing
16240 (-1 -2 -6005 -J1A)	1/16-27 NPT Thread with 5/16" Hex to 200 Series Barb, 5/32" (4.0 mm) ID Tubing
1640 (-1 -2 -6005 -J1A)	1/16-27 NPT Thread with 5/16" Hex to Classic Series Barb, 5/32" (4.0 mm) ID Tubing
16445 (-1 -2 -6005 -J1A)	1/16-27 NPT Thread with 5/16" Hex to 400 Series Barb, .170" (4.3 mm) ID Tubing
16250 (-1 -2 -6005 -J1A)	1/16-27 NPT Thread with 5/16" Hex to 200 Series Barb, 3/16" (4.8 mm) ID Tubing
16450 (-1 -2 -6005 -J1A)	1/16-27 NPT Thread with 5/16" Hex to 400 Series Barb, 3/16" (4.8 mm) ID Tubing
1650 (-1 -2 -6005 -J1A)	1/16-27 NPT Thread with 5/16" Hex to Classic Series Barb, 3/16" (4.8 mm) ID Tubing
1600 (-1 -2 -6005 -J1A)	1/16-27 NPT Thread Plug with 5/16" Hex
16410 (-1 -2 -6005 -J1A)	1/16-27 NPT Thread with 5/16" Hex to 400 Series Barb, 1/16" (1.6 mm) ID Tubing
1610 (-1 -2 -6005 -J1A)	1/16-27 NPT Thread with 5/16" Hex to Classic Series Barb, 1/16" (1.6 mm) ID Tubing
16220 (-1 -2 -6005 -J1A)	1/16-27 NPT Thread with 5/16" Hex to 200 Series Barb, 3/32" (2.4 mm) ID Tubing
16420 (-1 -2 -6005 -J1A)	1/16-27 NPT Thread with 5/16" Hex to 400 Series Barb, 3/32" (2.4 mm) ID Tubing
1620 (-1 -2 -6005 -J1A)	1/16-27 NPT Thread with 5/16" Hex to Classic Series Barb, 3/32" (2.4 mm) ID Tubing
16230 (-1 -2 -6005 -J1A)	1/16-27 NPT Thread with 5/16" Hex to 200 Series Barb, 1/8" (3.2 mm) ID Tubing
16430 (-1 -2 -6005 -J1A)	1/16-27 NPT Thread with 5/16" Hex to 400 Series Barb, 1/8" (3.2 mm) ID Tubing

p74

THREADED FITTINGS

THREAD:1/8-27 NPT

18210 (-1 -2 -6005 -J1A)	1/8-27 NPT Thread with 7/16" Hex to 200 Series Barb, 1/16" (1.6 mm) ID Tubing
18430 (-1 -2 -6005 -J1A)	1/8-27 NPT Thread with 7/16" Hex to 400 Series Barb, 1/8" (3.2 mm) ID Tubing
1830 (-1 -2 -6005 -J1A)	1/8-27 NPT Thread with 7/16" Hex to Classic Series Barb, 1/8" (3.2 mm) ID Tubing
18240 (-1 -2 -6005 -J1A)	1/8-27 NPT Thread with 7/16" Hex to 200 Series Barb, 5/32" (4.0 mm) ID Tubing
1840 (-1 -2 -6005 -J1A)	1/8-27 NPT Thread with 7/16" Hex to Classic Series Barb, 5/32" (4.0 mm) ID Tubing
18445 (-1 -2 -6005 -J1A)	1/8-27 NPT Thread with 7/16" Hex to 400 Series Barb, .170" (4.3 mm) ID Tubing
1850 (-1 -2 -6005 -J1A)	1/8-27 NPT Thread with 7/16" Hex to Classic Series Barb, 3/16" (4.8 mm) ID Tubing