

HPLC Detector & Spectrometer UV Lamps 2014

[Ctrl F]
> Cat.#s

> Current System AUD Prices



ABI (APPLIED BIOSYSTEMS)		
ANALYST	LH-13	D2
ANALYST	LH-13X2	D2
ANALYST	L-850	W
BIOCAD 20, 60, 250, 700E, SPRINT, VISION	LH-40	D2
INTEGRAL 700E, 250	LH-40	D2
120A, 130A	LH-98	D2
270A-HT, 1000S	LH-98	D2
FS970, FS980	LH-98	D2
PEPTIDE SYNTHESIZER 433A	LH-98	D2
PROSICE HT, C, CLC, 492, 494	LH-98	D2
785	LH-98	D2
SF757, 773, 783, 759A, 783A, 785A	LH-98	D2
SF759A, 785A	LH-98	D2
SF769, SF770	LH-98	D2
AGILENT/HEWLETT-PACKARD		
1037, 1047A	L-610	W
1046	L-890	PXE
SPECTROPHOTOMETERS		
8450A	LH-16	D2
8451A	LH-11	D2
8452A	LH-12	D2
8453A, 8453E	LH-15	D2
8453A, 8453E	LH-15X2	D2
8453A, 8453E	LH-13X2	D2
8453A, 8453E	L-850	W
1040 SERIES		
1040A, 1040M, 79881A	LH-10	D2
1050 SERIES		
79853A	L-295	D2
79853C, 79854A	LH-10	D2
G1306A	LH-10	D2
1090 SERIES		
79880A, 79881A	LH-10	D2
SERIES I & II	LH-10	D2
1100 SERIES		
G1314A, G1314B	LH-14	D2
G1315A, G1315B, G1365A, G1365B	LH-13	D2
G1315A, G1315B, G1365A, G1365B	LH-13X2	D2
G1315A, G1315B	L-850	W
G1321A	L-870	P/XE
HP3D/CE	LH-14	D2
1120/1200 SERIES (contact for free tech support)		
G1314 B, C, D, E, F	LH-14	D2
G1315 C, D, G1365 C, D	LH-13 x2	D2
1220 SERIES (contact for free tech support)		
G1314 C, D, E, F	LH-14	D2
1260, 1290 INFINITY SERIES (contact for free tech support)		
G4212 A/B	LH-19X2	D2
G1315A, G1315B, G1365A, G1365B	LH-13	D2
G1315A, G1315B, G1365A, G1365B	LH-13X2	D2
G1315A, G1315B	L-850	W
G1315 C, D, G1365 C, D	LH-13 x2	D2
G1315 C, D, G1365 C, D	LH-13	D2
G7100A	LH-19X2	D2

200, 201, 205	LH-40	D2	\$460
200	LH-760	W	\$275
305	LH-910	P/XE	\$550
AMERSHAM /SEE G/E HEALTHCARE AMINCO/ATI/SEE THERMO SCIENTIFIC			
AVIV/ PROTERION/RHEOMETRIC SCIENTIFIC/WYATT TECH			
14D			INQUIRE
62DS, 202, 215 (CD)	L-995	XE	
BAS			
FL45	LH-910	P/XE	
UV116A, UV200	LH-40	D2	
BAUSCH & LOMB (B&L) /SEE THERMO SCIENTIFIC			
BECKMAN/ALTEX			
20,24,25,26,34,35,36	L-250	D2	
20,24,25,26,34,35,36	L-860	W	
25	L-200	D2	
153	L-885	HG	
160	L-710	HG	
163	L-205	D2	
166	LHA-70	D2 Lamp Ass'y	
166	LH-70	Cartridge Only	
168	LHA-75	D2 Lamp Ass'y	
168	LH-75	Cartridge Only	
5200, ACTA	L-250	D2	
5200, ACTA	L-865	W	
AD340	L-275	W	
5240	L-840	W	
DB, DBG, DBG, DK, DU	L-305	D2	
DB, DBG, DK-2A	L-860	W	
DU2	L-860	W	
DU-6, 7, 8, 20, 30, 37, 40, 50	L-250	D2	
DU-6, 7, 8, 20, 30, 40, 50	L-840	W	
DU-60, 62, 63, 64, 65, 68, 70	L-835	W	
DU-70	LH-73	D2	
DU-500, 520, 530	LH-110	D2	
DU-500, 520, 530	L-730	W	
DU-600, 640, 650, 800	LH-72	D2	
DU-600, 640, 650, 800	L-835	W	
DU-700, 720, 730	LH-78	D2	
DU-700, 720, 730	L-780	W	
DU-7000, 7400, 7500	LH-72	D2	
DU-7000, 7400, 7500	L-835	W	
P/ACE 2000, 2050, 2100, 2200, 2210	LH-77	D2	
P/ACE 5000/477170, 5010/477171	LH-76	D2	
P/ACE 5500/477172, 5510/477173	LH-76	D2	
P/ACE MDQ	LH-76	D2	
P/ACE 800	LH-76	D2	
BEIJING PURKINJE GENERAL INSTRUMENT CO/ GENTECH			
UV 1100, 9100, 1200, 1300, 1400	L-265	D2	
VIS-7220, 9100, 1200, 1300, 1400	L-165	W	