

HITACHI (CONTINUED)		
U-1800, 1900, 2800, 2810	LH-57	D2
U-1800, 2800, 2810	L-935	W
U-2900, 2910	LH-57	D2
U-1900, 2900, 2910	L-815	W
U-2000, 2001, 2010	LH-51	D2
U-2000, 2001, 2010	L-815	W
U-3000, 3010, 3110, 3210, 3300	LH-51	D2
U-3000, 3010, 3110, 3300	L-815	W
U-3310, 3400, 3410, 3501, 4100	LH-51	D2
U-3310, 4100	L-815	W
U-3410, 3501	LH-55	W
U-3500	LH-56	D2
U-4001, 4100	LH-51	D2

HORIBA JOBIN YVON/SEE JY

IBM		
9420	L-200	D2
9523, 9563, 9565	L-205	D2
ISCO/TELEDYNE		
205	LH-40	D2
205	LH-760	W
3850	L-205	D2
COMBIFLASH COMPANION, TS, 4X, XL	LH-61	D2
COMBIFLASH RF 75, RF 200	LH-62	D2
COMBIFLASH SYSTEM SQ16X	L-205	D2
V4/1840	L-205	D2

HPLC Detector & Spectrometer UV Lamps 2014

JASCO		
870, 875	L-295	D2
FP-750, 777, 820, 821, 920, 921	L-800	XE
FP-1520, 1570, 1575, 2020, 3120	L-800	XE
FP-6200, 6300, 6500, 6600	L-800	XE
J-810 CD, J-815 CD	L-960	XE
CD-995, 2095, OR-2090	L-790	XE-HG
UVIDEC 100 THRU UVIDEC 100-VI	L-200	D2
UVIDEC 320, 340, 420, 430, 505	L-200	D2
UVIDEC 510, 610, 650, 710	L-200	D2
V-530, V-560	L-265	D2
V-530, V-550, V-560	L-835	W
UV-970A, UV975A	L-295	D2
V-650, V-660, V-7100	L-265	D2

JENWAY		
6105, 6405, 6505	LH-650	D2
6105, 6300, 6400	L-835	W
6405, 6500, 6505	L-835	W

06/2014

JY(JC)			
FLUOROLOG-2/F111XI, > Current System AUD Prices			
FLUOROLOG-2/F212I, F222I	L-855	XE	
FLUOROLOG-3, TAU-3	L-855	XE	
FLUOROMAX-2, 3, 4	L-955	XE	
SYSTEM 5000	L-60	P/XE	
KNAUER/SONNTEK			
AZURA SERIES			
UVD 2.1S, 2.1L	A5193	D2	INQUIRE
BLUE SHADOW SERIES			
40D, 50D	A5193	D2	INQUIRE
SMARTLINE SERIES			
200	A4142	HG	INQUIRE
2500, 2600	A4071	D2	INQUIRE
2500	A4073	W	INQUIRE
2520, 2550	A5193	D2	INQUIRE
2550	A5195	W	INQUIRE
2800	A4447	D2	INQUIRE
2800	A4448	W	INQUIRE
WELLCHROM SERIES			
200	A4142	HG	INQUIRE
2000, 2001, 2500, 2501, 2600, 2650	A4071	D2	INQUIRE
2001, 2500, 2501, 2600	A4073	W	INQUIRE
6700, 8700, 9700, D871	A0877	D2	INQUIRE
KONTRON/BIOTEK/NORTH STAR SCIENTIFIC			
440	LHA-34	W	
720, 810, 820, 860, 900, 930, 940	L-205	D2	
820, 860, 900, 930, 940	L-110	W	
UVIKON	L-205	D2	
UVIKON XL, XS			INQUIRE
ALL SPECTROPHOTOMETERS	L-205	D2	
KRATOS/SEE ABI, PERKIN-ELMER			
LABALLIANCE/SCIENTIFIC SYSTEMS (SSI)			
200,201, 500, 504, 506, V520, 525	LH-40	D2	
200,201, 500, 504, 506, V520, 525	LH-760	W	
1200 SERIES			
AGG1314B	LH-14	D2	
AGG1315D	LH-13	D2	
AGG1321A	L-870	P/XE	
LC PACKINGS/DIONEX			
ULT-UVD, UVD-3000	LH-25	D2	
ULT-UVD	LHA-23	W	
LDC/SEE THERMO SCIENTIFIC			
LKB/SEE GE HEALTHCARE			
MCPHERSON			
FL-750/A & B	LH-101	XE	
FL-750/A & B	LH-100	D2	
FL-750/A & B	LH-102	XE-HG	