

THERMO SCIENTIFIC (CONTINUED)		
LDC		
SC100-234	LH-40	D2
SC100-234	LH-760	W
SM I, II, III, D	L-205	D2
SM 3000, 3100, 4000	L-205	D2
SM 3100X, 4100	LH-42	D2
SM 5000	LH-47	D2
UV100-411, UV150-511	LH-40	D2
UV100-411, UV150-511	LH-760	W
LINEAR		
100, 200, 203, 204, 205, 206PHD	LH-40	D2
100, 200, 201, 203, 204, 205	LH-760	W
304, 305	LH-910	P/XE
NICOLET		
EVOLUTION 100, 500, 600	LH-54	D2
EVOLUTION 100	L-910	W
EVOLUTION 500, 600	L-940	W
SPECTRA-PHYSICS/FINNIGAN		
CE500, 1000, 2000	LH-40	D2
CE500, 1000, 2000	LH-760	W
FL2000, 3000	LH-910	P/XE
SC100, 200, SF100, 200	LH-40	D2
SC100, 200, SF100, 200	LH-760	W
SF770, 970	LHA-1	D2 Lamp Ass'y
	LH-1	Cartridge Only
SP8400, 8440, 8440XR, SP8450, 8490	L-215	D2
SP8480XR	LHA-3	D2 Lamp D2
	LH-1	Cartridge Only
SP8773XR	LH-1	Cartridge Only
UV100, 150, 1000, 2000, 3000	LH-40	D2
UV100, 150, 1000, 2000, 3000	LH-760	W
UV3000HR	LH-40	D2
SURVEYOR		
UV6000LP, 6057-60030, 60040	LH-46	D2
UV6000LP, 6057-60030, 60040	L-765	W
PDA1P, 5P, UV1P, 5P	LH-46	D2
PDA1P, 5P, UV1P, 5P	L-765	W
FL PLUS DETECTOR	L-800	XE
TURNER/BARNSTEAD		
110, 111, 112	L-185	HG
SP-830 PLUS, 850, 870 PLUS	W	INQUIRE
UNICAM		
UV 1-100	LH-54	D2
UV 1-100	L-910	W
UV 2-100, 200, 300, 400	LH-54	D2
UV 2-100, 200, 300, 400	L-940	W
UV 3-100, 200, UV 4-100, 200	LH-54	D2
UV 3-100, 200, UV 4-100, 200, 500	L-940	W
UV 300, 500, 550	LH-54	D2
UV 300, 500, 550	L-940	W
4225	LH-40	D2
HELIOS ALPHA, BETA, DELTA	LH-54	D2
HELIOS ALPHA BETA, DELTA	L-910	W

THERMO SCIENTIFIC		
HELIOS EPSILON		
HELIOS GAMMA	LH-54	D2
HELIOS GAMMA	L-910	W
TRANSGENOMIC		
FDX-99-2100	L-800	XE
WAVE 3500, 3500A, 3500HT	LH-56	D2
WAVE 4500, 4500 HT, HT-HS	LH-56	D2
WAVE HS, 4500, HT-HS	L-800	XE
WAVE OLIGO, DNS	LH-56	D2
TURNER/BARNSTEAD /UNICAM SEE THERMO SCIENTIFIC		
VARIAN/CARY/RAININ/AGILENT		
1, 3, 5, 14, 15, 16, 17	L-230	D2
1, 3, 14, 15, 16, 17	L-930	W
50	L-1045	P/XE
87/8700, 8700	LH-20	D2
100, 210, 219, 220, 300, 400, 500	L-230	D2
100, 210, 219, 220, 300	L-930	W
400	L-110	W
500	L-1015	W
2050	L-290	D2
2200, 2300, 2400,	L-205	D2
2550	L-295	D2
9070, 9075	LH-910	P/XE
AA200, 240, 275, 280,300, 400	L-230	D2
AA600, 640, 775, 800, 875	L-230	D2
AA975, 1275, 1475, 3000	L-230	D2
DMS 70 THRU DMS 300	L-230	D2
FL-1, 2	LH-910	P/XE
LC-5000, 5500	L-305	D2
PDA-1		D2
PDA-2	LH-82	D2
PRO-STAR, PRO-STAR 320	LH-950	P/XE
PRO STAR 310	L-305	D2
PRO STAR 325, 335	LH-325	D2
PRO STAR 330	LH-56	D2
PRO STAR 340, 345	LH-40	D2
PRO STAR 340, 345	LH-760	W
PRO STAR 360	LH-910	P/XE
PRO STAR 363	L800	XE
SPECTRA A10, A20, A30, A40	L-230	D2
SPECTRA A640, A880	L-230	D2
STAR 9050	L-305	D2
UV-1, UV-1A	LH-950	P/XE
UV 50, 100, 200	L-305	D2
UV- C, DII, M	LH-40	D2
VISTA 5000, 5500	L-305	D2
WATERS		
420	L-770	HG
440, 441	L-820	HG
450	LHA-1	D2 Lamp Ass'y
	LH-1	Cartridge Only
470, 474	L-800	XE
2420. 2424 ELSD	L-120	W